





RECOMMENDED P.C. BOARD LAYOUT



NOTES:

- PIN PUSHOUT FORCE: 4 LBS. MINIMUM (IN EITHER DIRECTION)
- FOR ILLUSTRATION PURPOSES, 20 (DUAL 10) CIRCUIT SIZE IS SHOWN.
- PINS MUST MEET MOLEX SOLDERABILITY SPECIFICATION ES-152, EXCEPT VOIDS ARE PERMISSIBLE AT BANDOLIER PIN FAYING SURFACE (APPROX. .025 LONG X .006 WIDE REF.- 2 LOCATIONS).
- MEASURE POINT FOR PLATING THICKNESS.
- THIS PART CONFORMS TO MOLEX PRODUCT SPECIFICATION PS-8624.
- PACKAGING INFORMATION: (UNLESS OTHERWISE NOTED IN TABLES) PER PACKAGING DRAWING NO. PK-70873-0353 BULK PACKAGED IN BAGS

MATERIAL:

WAFER - GLASS FILLED POLYESTER; UL94V-0; COLOR: BLACK
PIN - PHOSPHOR BRONZE

PLATING:

- TIN - .000150 MINIMUM TIN PLATE OVER .000050 MINIMUM NICKEL PLATE.
- 15 GOLD - .000015 MINIMUM GOLD PLATE IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER .000050 MINIMUM NICKEL PLATE OVERALL.
- 30 GOLD - .000030 MINIMUM GOLD PLATE IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER .000050 MINIMUM NICKEL PLATE OVERALL.
- D30 GOLD - .000030 MINIMUM GOLD PLATE IN SELECT AREAS OVER .000050 MINIMUM NICKEL PLATE OVERALL.
- 5 GOLD - .000005 MINIMUM GOLD FLASH IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER .000050 MINIMUM NICKEL PLATE OVERALL.

*THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.

CKT. SIZE	DIMENSION A		DIMENSION B	
	(MM)	INCH	(MM)	INCH
4	(2.54)	.100	(4.83)	.190
6	(5.08)	.200	(7.37)	.290
8	(7.62)	.300	(9.91)	.390
10	(10.16)	.400	(12.45)	.490
12	(12.70)	.500	(14.99)	.590
14	(15.24)	.600	(17.53)	.690
16	(17.78)	.700	(20.07)	.790
18	(20.32)	.800	(22.61)	.890
20	(22.86)	.900	(25.15)	.990
22	(25.40)	1.000	(27.69)	1.090
24	(27.94)	1.100	(30.23)	1.190
26	(30.48)	1.200	(32.77)	1.290
28	(33.02)	1.300	(35.31)	1.390
30	(35.56)	1.400	(37.85)	1.490
32	(38.10)	1.500	(40.39)	1.590
34	(40.64)	1.600	(42.93)	1.690
36	(43.18)	1.700	(45.47)	1.790
38	(45.72)	1.800	(48.01)	1.890
40	(48.26)	1.900	(50.55)	1.990
42	(50.80)	2.000	(53.09)	2.090
44	(53.34)	2.100	(55.63)	2.190
46	(55.88)	2.200	(58.17)	2.290
48	(58.42)	2.300	(60.71)	2.390
50	(60.96)	2.400	(63.25)	2.490
52	(63.50)	2.500	(65.79)	2.590
54	(66.04)	2.600	(68.33)	2.690
56	(68.58)	2.700	(70.87)	2.790
58	(71.12)	2.800	(73.41)	2.890
60	(73.66)	2.900	(75.95)	2.990
62	(76.20)	3.000	(78.49)	3.090
64	(78.74)	3.100	(81.03)	3.190
66	(81.28)	3.200	(83.57)	3.290
68	(83.82)	3.300	(86.11)	3.390
70	(86.36)	3.400	(88.65)	3.490
72	(88.90)	3.500	(91.19)	3.590
74	(91.44)	3.600	(93.73)	3.690
76	(93.98)	3.700	(96.27)	3.790
78	(96.52)	3.800	(98.81)	3.890
80	(99.06)	3.900	(101.35)	3.990

DIMENSIONS SHOWN (METRIC) INCH		UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°	
INCH		METRIC	
3 PLACE ± .005			
2 PLACE ± .01 ± 0.13			
1 PLACE ± 0.25			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
DRWG. BY: EIK	CHK'D. BY: AAB		
APP'D. BY: WAZ	SCALE: 4 : 1		
FILE NAME: 58624X1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

SALES ASSY-DUAL ROW WAFER W/BREAK-OFF OPTION .025 SQ. PINS/.100 GRID	
MOLEX INCORPORATED	SHEET NO. 1 OF 7
DATE: 11/30/88	
SEE CHARTS: SDA-8624-0001-5000	

7	P	
6	P	
5	P	
4	P	
3	P	
2	P	
1	P	

MFG.	SH.	REV.	LTR.	REVISIONS

I3		I2		I1		I0		9		8		7		6		8624		4		3		2		1	
ENGINEERING NUMBER A-8624		RELEASE FOR MANUFACTURE						C ± (0.38) .015		E ± (0.25) .010		F ± (0.25) .010		PLATING PER NOTES SHEET 1		CONNECTOR END PLATING		P.C. BOARD END PLATING				FOR PACKAGING INFORMATION, SEE NOTE 6, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)			
																TYPE		H MEAS.		TYPE		K MEAS.			
-0001/-0040		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		TIN		TIN		(2.54) .100		TIN		(1.27) .050			
-0041/-0080		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		15 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
-0081/-0120		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		30 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
-0121/-0160		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		TIN		TIN		(2.54) .100		TIN		(1.27) .050			
-0161/-0200		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240		TIN		TIN		(2.54) .100		TIN		(1.27) .050			
-0201/-0240		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240		15 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
-0241/-0280		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240		30 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	CKTS	
02	N.A.	A-8624-0001	N.A.	A-8624-0041	N.A.	A-8624-0081	N.A.	A-8624-0121	N.A.	A-8624-0161	N.A.	A-8624-0201	N.A.	A-8624-0241	N.A.	A-8624-0281	N.A.	A-8624-0321	N.A.	A-8624-0361	N.A.	A-8624-0401	N.A.	02	
04	10-88-1041	A-8624-0002	10-89-1041	A-8624-0042	10-89-2041	A-8624-0082		A-8624-0122	10-88-1042	A-8624-0162	10-89-1042	A-8624-0202	10-89-2042	A-8624-0242	04									04	
06	10-88-1061	A-8624-0003	10-89-1061	A-8624-0043	10-89-2061	A-8624-0083	10-89-3064	A-8624-0123	10-88-1062	A-8624-0163	10-89-1062	A-8624-0203	10-89-2062	A-8624-0243	06									06	
08	10-88-1081	A-8624-0004	10-89-1081	A-8624-0044	10-89-2081	A-8624-0084		A-8624-0124	10-88-1082	A-8624-0164	10-89-1082	A-8624-0204	10-89-2082	A-8624-0244	08									08	
10	10-88-1101	A-8624-0005	10-89-1101	A-8624-0045	10-89-2101	A-8624-0085	10-89-3104	A-8624-0125	10-88-1102	A-8624-0165	10-89-1102	A-8624-0205	10-89-2102	A-8624-0245	10									10	
12	10-88-1121	A-8624-0006	10-89-1121	A-8624-0046	10-89-2121	A-8624-0086		A-8624-0126	10-88-1122	A-8624-0166	10-89-1122	A-8624-0206	10-89-2122	A-8624-0246	12									12	
14	10-88-1141	A-8624-0007	10-89-1141	A-8624-0047	10-89-2141	A-8624-0087		A-8624-0127	10-88-1142	A-8624-0167	10-89-1142	A-8624-0207	10-89-2142	A-8624-0247	14									14	
16	10-88-1161	A-8624-0008	10-89-1161	A-8624-0048	10-89-2161	A-8624-0088		A-8624-0128	10-88-1162	A-8624-0168	10-89-1162	A-8624-0208	10-89-2162	A-8624-0248	16									16	
18	10-88-1181	A-8624-0009	10-89-1181	A-8624-0049	10-89-2181	A-8624-0089		A-8624-0129	10-88-1182	A-8624-0169	10-89-1182	A-8624-0209	10-89-2182	A-8624-0249	18									18	
20	10-88-1201	A-8624-0010	10-89-1201	A-8624-0050	10-89-2201	A-8624-0090		A-8624-0130	10-88-1202	A-8624-0170	10-89-1202	A-8624-0210	10-89-2202	A-8624-0250	20									20	
22	10-88-1221	A-8624-0011	10-89-1221	A-8624-0051	10-89-2221	A-8624-0091		A-8624-0131	10-88-1222	A-8624-0171	10-89-1222	A-8624-0211	10-89-2222	A-8624-0251	22									22	
24	10-88-1241	A-8624-0012	10-89-1241	A-8624-0052	10-89-2241	A-8624-0092		A-8624-0132	10-88-1242	A-8624-0172	10-89-1242	A-8624-0212	10-89-2242	A-8624-0252	24									24	
26	10-88-1261	A-8624-0013	10-89-1261	A-8624-0053	10-89-2261	A-8624-0093		A-8624-0133	10-88-1262	A-8624-0173	10-89-1262	A-8624-0213	10-89-2262	A-8624-0253	26									26	
28	10-88-1281	A-8624-0014	10-89-1281	A-8624-0054	10-89-2281	A-8624-0094		A-8624-0134	10-88-1282	A-8624-0174	10-89-1282	A-8624-0214	10-89-2282	A-8624-0254	28									28	
30	10-88-1301	A-8624-0015	10-89-1301	A-8624-0055	10-89-2301	A-8624-0095		A-8624-0135	10-88-1302	A-8624-0175	10-89-1302	A-8624-0215	10-89-2302	A-8624-0255	30									30	
32	10-88-1321	A-8624-0016	10-89-1321	A-8624-0056	10-89-2321	A-8624-0096		A-8624-0136	10-88-1322	A-8624-0176	10-89-1322	A-8624-0216	10-89-2322	A-8624-0256	32									32	
34	10-88-1341	A-8624-0017	10-89-1341	A-8624-0057	10-89-2341	A-8624-0097		A-8624-0137	10-88-1342	A-8624-0177	10-89-1342	A-8624-0217	10-89-2342	A-8624-0257	34									34	
36	10-88-1361	A-8624-0018	10-89-1361	A-8624-0058	10-89-2361	A-8624-0098		A-8624-0138	10-88-1362	A-8624-0178	10-89-1362	A-8624-0218	10-89-2362	A-8624-0258	36									36	
38	10-88-1381	A-8624-0019	10-89-1381	A-8624-0059	10-89-2381	A-8624-0099		A-8624-0139	10-88-1382	A-8624-0179	10-89-1382	A-8624-0219	10-89-2382	A-8624-0259	38									38	
40	10-88-1401	A-8624-0020	10-89-1401	A-8624-0060	10-89-2401	A-8624-0100		A-8624-0140	10-88-1402	A-8624-0180	10-89-1402	A-8624-0220	10-89-2402	A-8624-0260	40									40	
42	10-88-1421	A-8624-0021	10-89-1421	A-8624-0061	10-89-2421	A-8624-0101		A-8624-0141	10-88-1422	A-8624-0181	10-89-1422	A-8624-0221	10-89-2422	A-8624-0261	42									42	
44	10-88-1441	A-8624-0022	10-89-1441	A-8624-0062	10-89-2441	A-8624-0102		A-8624-0142	10-88-1442	A-8624-0182	10-89-1442	A-8624-0222	10-89-2442	A-8624-0262	44									44	
46	10-88-1461	A-8624-0023	10-89-1461	A-8624-0063	10-89-2461	A-8624-0103		A-8624-0143	10-88-1462	A-8624-0183	10-89-1462	A-8624-0223	10-89-2462	A-8624-0263	46									46	
48	10-88-1481	A-8624-0024	10-89-1481	A-8624-0064	10-89-2481	A-8624-0104		A-8624-0144	10-88-1482	A-8624-0184	10-89-1482	A-8624-0224	10-89-2482	A-8624-0264	48									48	
50	10-88-1501	A-8624-0025	10-89-1501	A-8624-0065	10-89-2501	A-8624-0105		A-8624-0145	10-88-1502	A-8624-0185	10-89-1502	A-8624-0225	10-89-2502	A-8624-0265	50									50	
52	10-88-1521	A-8624-0026	10-89-1521	A-8624-0066	10-89-2521	A-8624-0106		A-8624-0146	10-88-1522	A-8624-0186	10-89-1522	A-8624-0226	10-89-2522	A-8624-0266	52									52	
54	10-88-1541	A-8624-0027	10-89-1541	A-8624-0067	10-89-2541	A-8624-0107		A-8624-0147	10-88-1542	A-8624-0187	10-89-1542	A-8624-0227	10-89-2542	A-8624-0267	54									54	
56	10-88-1561	A-8624-0028	10-89-1561	A-8624-0068	10-89-2561	A-8624-0108		A-8624-0148	10-88-1562	A-8624-0188	10-89-1562	A-8624-0228	10-89-2562	A-8624-0268	56									56	
58	10-88-1581	A-8624-0029	10-89-1581	A-8624-0069	10-89-2581	A-8624-0109		A-8624-0149	10-88-1582	A-8624-0189	10-89-1582	A-8624-0229	10-89-2582	A-8624-0269	58									58	
60	10-88-1601	A-8624-0030	10-89-1601	A-8624-0070	10-89-2601	A-8624-0110		A-8624-0150	10-88-1602	A-8624-0190	10-89-1602	A-8624-0230	10-89-2602	A-8624-0270	60									60	
62	10-88-1621	A-8624-0031	10-89-1621	A-8624-0071	10-89-2621	A-8624-0111		A-8624-0151	10-88-1622	A-8624-0191	10-89-1622	A-8624-0231	10-89-2622	A-8624-0271	62									62	
64	10-88-1641	A-8624-0032	10-89-1641	A-8624-0072	10-89-2641	A-8624-0112		A-8624-0152	10-88-1642	A-8624-0192															