


LIGHT PIPE


PREPARATION/INSTALLATION:

1.5±.5 [.06±.02]




NOTES:

1. ROHS COMPLIANT
2. UL 94V-2 FLAMMABILITY RATING
3. -40°C TO 85°C OPERATING TEMPERATURE
4. SUITABLE FOR LIGHT PIPE WITH Ø3.0mm JACKET AND OPTICAL CORE NO GREATER THAN Ø1.5mm
5. DO NOT WAVE SOLDER WITH THIS DEVICE
6. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED LEDS WITH OUTPUT POWER GREATER THAN 100mcd
7. NOT RECOMMENDED FOR DATA COMMUNICATIONS



METRIC

REVISIONS				
REV	DESCRIPTION	ECO	DATE	APVD
C	REVISED STRIP LENGTH FROM 1.0±.05	0034	09/17/09	BB KS



UNLESS OTHERWISE SPECIFIED		INDUSTRIAL FIBER OPTICS	
DIMENSIONS MILLIMETERS [IN.]		TEMPE, AZ 85281	
TOLERANCES		NAME	
0 PLC: ±1	SURFACE 3/2	MOUNT, RIGHT-ANGLE LED TO LIGHT PIPE	
1 PLC: ±.25	TEXTURE: V		
2 PLC: ±.127			
3 PLC: ±.025			
4 PLC: ±.013		SIZE SCALE	
ANGLE: ±1/2°		2:1	
REMOVE BURRS AND SHARP EDGES		PART NUMBER	
FLATNESS .005 MM PER MM		51 0332	
ALL DIMENSIONS AFTER FINISH		REV	
		C	

PRODUCT	
LIGHT PIPE	
MATERIAL	
NYLON 66	
FINISH	
NONE	
DRAWN BY	
B. BIDWELL	
DATE	
11/12/08	
CHECKED BY	
K. STOTZ	
DATE	
09/17/09	

DO NOT SCALE		SHEET	
DRAWING		1 OF 1	