


SuperServer 8017R-TF+

Products ▸ Systems ▸ 1U ▸ [8017R-TF+]



Integrated Board



Super X9QRI-F+

Available Colors:

Black

▸ Drivers & Utilities

▸ BIOS

▸ IPMI

▸ Tested Memory

▸ Tested HDD

▸ Manuals

▸ OS Certification Matrix

Key Features

1. Quad socket R (LGA 2011) supports Intel® Xeon® processor E5-4600 v2 (12-Core)** or E5-4600 (8-Core) family, w / QPI up to 8.0 GT/s

2. Up to 1TB* DDR3 1866MHz ECC Registered DIMM; 32x DIMM sockets
* Depends on memory configuration

3. 1x PCI-E 3.0 x16 Low-profile Slot

4. Intel® i350 Dual port GbE LAN

5. I/O ports: 2x GbE LAN, 1x Dedicated LAN for IPMI Remote Management, 1x VGA, 1x COM port, 4x USB 2.0

6. 3x 3.5" Hot-sw ap SATA2 Drive Bays

7. 7x 4cm Counter Rotating Fans with speed control

8. 1400W High Efficiency Digital PS Platinum Level (94%)

Note: Image above may show a varied configuration or optional parts, Please refer to parts list for standard parts included.

Specifications																																																																																																																																									
<table><tr><th colspan="2">Product SKUs</th></tr><tr><td>SYS-8017R-TF+</td><td>SuperServer 8017R-TF+ (Black)</td></tr><tr><th colspan="2">Motherboard</th></tr><tr><td colspan="2">Super X9QRI-F+</td></tr><tr><th colspan="2">Processor/Cache</th></tr><tr><td>CPU</td><td> Intel® Xeon® processor E5-4600 v2 (12-Core)** or E5-4600 (8-Core) family (up to 130W CPU at 35°C) Quad Socket R (LGA 2011) ** BIOS rev. 3.0 or above is needed to support Ivy Bridge-EP 4S. </td></tr><tr><td>Cache</td><td>Up to 30MB</td></tr><tr><td>System Bus</td><td>QPI up to 8 GT/s</td></tr><tr><th colspan="2">System Memory</th></tr><tr><td>Memory Capacity</td><td> 32x 240-pin DDR3 DIMM sockets Supports up to 1TB DDR3 ECC Registered memory (RDIMM) in 32 DIMM sockets </td></tr><tr><td>Memory Type</td><td>1866/1600/1333/1066/800MHz ECC DDR3 SDRAM 72-bit, 240-pin gold-plated DIMMs</td></tr><tr><td>DIMM Sizes</td><td>32GB, 16GB, 8GB, 4GB, 2GB, 1GB</td></tr><tr><td>Memory Voltage</td><td>1.5 V, 1.35 V</td></tr><tr><td>Error Detection</td><td> Corrects single-bit errors Detects double-bit errors (using ECC memory) </td></tr><tr><th colspan="2">On-Board Devices</th></tr><tr><td>Chipset</td><td>Intel® C602 chipset</td></tr><tr><td>SATA</td><td> SATA 2.0 3Gbps with RAID 0, 1, 5 SATA 3.0 6Gbps with RAID 0, 1 </td></tr><tr><td>IPMI</td><td> Support for Intelligent Platform Management Interface v.2.0 IPMI 2.0 with virtual media over LAN and KVM-over-LAN support Nuvoton WPCM450 BMC </td></tr><tr><td>Network Controllers</td><td> Intel® i350 Dual port GbE LAN Virtual Machine Device Queues reduce I/O overhead Supports 10BASE-T, 100BASE-TX, and 1000BASE-T, RJ45 output 1x Realtek RTL8201F PHY (dedicated IPMI) </td></tr><tr><td>Graphics</td><td>Matrox G200eW (Nuvoton WPCM450 BMC)</td></tr><tr><td>Super I/O</td><td>Nuvoton W83527HG</td></tr><tr><th colspan="2">Input / Output</th></tr><tr><td>SATA</td><td> 2x SATA 3.0 ports (6Gbps) 4x SATA 2.0 ports (3Gbps) </td></tr><tr><td>LAN</td><td> 2x RJ45 Gigabit Ethernet LAN ports 1x dedicated LAN port for IPMI </td></tr><tr><td>USB</td><td>4x USB 2.0 rear ports</td></tr><tr><td>Video</td><td>1x VGA Port</td></tr><tr><td>Serial Port / Header</td><td>1 Fast UART 16550 serial port</td></tr><tr><th colspan="2">System BIOS</th></tr><tr><td>BIOS Type</td><td>16MB SPI Flash EEPROM with AMI® BIOS</td></tr><tr><td>BIOS Features</td><td> Plug and Play (PnP) PCI 2.2 ACPI up to 3.0 USB Keyboard support </td></tr></table>	Product SKUs		SYS-8017R-TF+	SuperServer 8017R-TF+ (Black)	Motherboard		Super X9QRI-F+		Processor/Cache		CPU	Intel® Xeon® processor E5-4600 v2 (12-Core)** or E5-4600 (8-Core) family (up to 130W CPU at 35°C) Quad Socket R (LGA 2011) ** BIOS rev. 3.0 or above is needed to support Ivy Bridge-EP 4S.	Cache	Up to 30MB	System Bus	QPI up to 8 GT/s	System Memory		Memory Capacity	32x 240-pin DDR3 DIMM sockets Supports up to 1TB DDR3 ECC Registered memory (RDIMM) in 32 DIMM sockets	Memory Type	1866/1600/1333/1066/800MHz ECC DDR3 SDRAM 72-bit, 240-pin gold-plated DIMMs	DIMM Sizes	32GB, 16GB, 8GB, 4GB, 2GB, 1GB	Memory Voltage	1.5 V, 1.35 V	Error Detection	Corrects single-bit errors Detects double-bit errors (using ECC memory)	On-Board Devices		Chipset	Intel® C602 chipset	SATA	SATA 2.0 3Gbps with RAID 0, 1, 5 SATA 3.0 6Gbps with RAID 0, 1	IPMI	Support for Intelligent Platform Management Interface v.2.0 IPMI 2.0 with virtual media over LAN and KVM-over-LAN support Nuvoton WPCM450 BMC	Network Controllers	Intel® i350 Dual port GbE LAN Virtual Machine Device Queues reduce I/O overhead Supports 10BASE-T, 100BASE-TX, and 1000BASE-T, RJ45 output 1x Realtek RTL8201F PHY (dedicated IPMI)	Graphics	Matrox G200eW (Nuvoton WPCM450 BMC)	Super I/O	Nuvoton W83527HG	Input / Output		SATA	2x SATA 3.0 ports (6Gbps) 4x SATA 2.0 ports (3Gbps)	LAN	2x RJ45 Gigabit Ethernet LAN ports 1x dedicated LAN port for IPMI	USB	4x USB 2.0 rear ports	Video	1x VGA Port	Serial Port / Header	1 Fast UART 16550 serial port	System BIOS		BIOS Type	16MB SPI Flash EEPROM with AMI® BIOS	BIOS Features	Plug and Play (PnP) PCI 2.2 ACPI up to 3.0 USB Keyboard support	<table><tr><th colspan="2">Chassis</th></tr><tr><td>Form Factor</td><td>1U Rackmount</td></tr><tr><td>Model</td><td>CSE-818A-1K43LPB</td></tr><tr><th colspan="2">Dimensions</th></tr><tr><td>Height</td><td>1.7" (43mm)</td></tr><tr><td>Width</td><td>17.2" (437mm)</td></tr><tr><td>Depth</td><td>27.75" (705mm)</td></tr><tr><td>Weight</td><td>Gross: 48.5 lbs / Net: 27 lbs</td></tr><tr><td>Available Colors</td><td>Black</td></tr><tr><th colspan="2">Front Panel</th></tr><tr><td>Buttons</td><td> Power On/Off button System Reset button </td></tr><tr><td>LEDs</td><td> Power LED Hard drive activity LED 2x Network activity LEDs System Overheat LED </td></tr><tr><th colspan="2">Expansion Slots</th></tr><tr><td>PCI-Express</td><td>1x PCI-E 3.0 x16 Low-profile Slot</td></tr><tr><th colspan="2">Drive Bays</th></tr><tr><td>Hot-swap</td><td>3x 3.5" Hot-sw ap SATA3 HDD Bays with RAID 0, 1, 5 (Software RAID)</td></tr><tr><th colspan="2">Backplane</th></tr><tr><td colspan="2">SAS/SATA HDD Backplane (SAS support requires optional SAS controller)</td></tr><tr><th colspan="2">Peripheral Drives</th></tr><tr><td>DVD-ROM</td><td>1x Slim DVD-ROM (Optional)</td></tr><tr><th colspan="2">System Cooling</th></tr><tr><td>Fans</td><td>7x 4cm Counter-rotating fans with optimal fan speed control</td></tr><tr><td>Shroud</td><td>1x Air Shroud</td></tr><tr><th colspan="2">Power Supply</th></tr><tr><td colspan="2">1400W High-efficiency AC power supply with Digital Switching Control & PMBus 1.2</td></tr><tr><td>AC Voltage</td><td> 1200W: 100-140 V, 14.7-10.5A, 50-60 Hz 1400W: 180-240 V, 10.5-8.0A, 50-60 Hz </td></tr><tr><td>+5V standby</td><td>6 Amp</td></tr><tr><td>+12V</td><td> 100 Amp/115 Vac 117 Amp/230 Vac </td></tr><tr><td>With Power Distributor</td><td> +5V: 30 Amp +3.3V: 25 Amp -12V: 0.6 Amp </td></tr><tr><td>Certification</td><td>  Platinum Certified </td></tr><tr><th colspan="2">PC Health Monitoring</th></tr><tr><td>CPU</td><td> Monitors for CPU Cores, +1.2V, 1.5V, +3.3V, +12V, (+3V, 1.0V, 1.2V, 1.8V, 1.1V) Standby, VBAT, Memory, Chipset Voltages. 4-Phase-switching voltage regulator with auto-sense from 0.6V-1.35V </td></tr><tr><td>FAN</td><td> 4-pin fan headers with tachometer status monitoring Low noise fan speed control mode </td></tr><tr><td>Temperature</td><td> Monitoring for CPU and system environment Thermal Control for 10x fan connectors </td></tr><tr><td>Other Features</td><td>Chassis intrusion detection</td></tr><tr><th colspan="2">Operating Environment / Compliance</th></tr><tr><td>RoHS</td><td>RoHS Compliant</td></tr><tr><td>Environmental Spec.</td><td> Operating Temperature: 10°C to 35°C (50°F to 95°F) Non-operating Temperature: -40°C to 70°C (-40°F to 158°F) Operating Relative Humidity: 8% to 90% (non-condensing) Non-operating Relative Humidity: 5% to 95% (non-condensing) </td></tr></table>	Chassis		Form Factor	1U Rackmount	Model	CSE-818A-1K43LPB	Dimensions		Height	1.7" (43mm)	Width	17.2" (437mm)	Depth	27.75" (705mm)	Weight	Gross: 48.5 lbs / Net: 27 lbs	Available Colors	Black	Front Panel		Buttons	Power On/Off button System Reset button	LEDs	Power LED Hard drive activity LED 2x Network activity LEDs System Overheat LED	Expansion Slots		PCI-Express	1x PCI-E 3.0 x16 Low-profile Slot	Drive Bays		Hot-swap	3x 3.5" Hot-sw ap SATA3 HDD Bays with RAID 0, 1, 5 (Software RAID)	Backplane		SAS/SATA HDD Backplane (SAS support requires optional SAS controller)		Peripheral Drives		DVD-ROM	1x Slim DVD-ROM (Optional)	System Cooling		Fans	7x 4cm Counter-rotating fans with optimal fan speed control	Shroud	1x Air Shroud	Power Supply		1400W High-efficiency AC power supply with Digital Switching Control & PMBus 1.2		AC Voltage	1200W: 100-140 V, 14.7-10.5A, 50-60 Hz 1400W: 180-240 V, 10.5-8.0A, 50-60 Hz	+5V standby	6 Amp	+12V	100 Amp/115 Vac 117 Amp/230 Vac	With Power Distributor	+5V: 30 Amp +3.3V: 25 Amp -12V: 0.6 Amp	Certification	 Platinum Certified	PC Health Monitoring		CPU	Monitors for CPU Cores, +1.2V, 1.5V, +3.3V, +12V, (+3V, 1.0V, 1.2V, 1.8V, 1.1V) Standby, VBAT, Memory, Chipset Voltages. 4-Phase-switching voltage regulator with auto-sense from 0.6V-1.35V	FAN	4-pin fan headers with tachometer status monitoring Low noise fan speed control mode	Temperature	Monitoring for CPU and system environment Thermal Control for 10x fan connectors	Other Features	Chassis intrusion detection	Operating Environment / Compliance		RoHS	RoHS Compliant	Environmental Spec.	Operating Temperature: 10°C to 35°C (50°F to 95°F) Non-operating Temperature: -40°C to 70°C (-40°F to 158°F) Operating Relative Humidity: 8% to 90% (non-condensing) Non-operating Relative Humidity: 5% to 95% (non-condensing)
Product SKUs																																																																																																																																									
SYS-8017R-TF+	SuperServer 8017R-TF+ (Black)																																																																																																																																								
Motherboard																																																																																																																																									
Super X9QRI-F+																																																																																																																																									
Processor/Cache																																																																																																																																									
CPU	Intel® Xeon® processor E5-4600 v2 (12-Core)** or E5-4600 (8-Core) family (up to 130W CPU at 35°C) Quad Socket R (LGA 2011) ** BIOS rev. 3.0 or above is needed to support Ivy Bridge-EP 4S.																																																																																																																																								
Cache	Up to 30MB																																																																																																																																								
System Bus	QPI up to 8 GT/s																																																																																																																																								
System Memory																																																																																																																																									
Memory Capacity	32x 240-pin DDR3 DIMM sockets Supports up to 1TB DDR3 ECC Registered memory (RDIMM) in 32 DIMM sockets																																																																																																																																								
Memory Type	1866/1600/1333/1066/800MHz ECC DDR3 SDRAM 72-bit, 240-pin gold-plated DIMMs																																																																																																																																								
DIMM Sizes	32GB, 16GB, 8GB, 4GB, 2GB, 1GB																																																																																																																																								
Memory Voltage	1.5 V, 1.35 V																																																																																																																																								
Error Detection	Corrects single-bit errors Detects double-bit errors (using ECC memory)																																																																																																																																								
On-Board Devices																																																																																																																																									
Chipset	Intel® C602 chipset																																																																																																																																								
SATA	SATA 2.0 3Gbps with RAID 0, 1, 5 SATA 3.0 6Gbps with RAID 0, 1																																																																																																																																								
IPMI	Support for Intelligent Platform Management Interface v.2.0 IPMI 2.0 with virtual media over LAN and KVM-over-LAN support Nuvoton WPCM450 BMC																																																																																																																																								
Network Controllers	Intel® i350 Dual port GbE LAN Virtual Machine Device Queues reduce I/O overhead Supports 10BASE-T, 100BASE-TX, and 1000BASE-T, RJ45 output 1x Realtek RTL8201F PHY (dedicated IPMI)																																																																																																																																								
Graphics	Matrox G200eW (Nuvoton WPCM450 BMC)																																																																																																																																								
Super I/O	Nuvoton W83527HG																																																																																																																																								
Input / Output																																																																																																																																									
SATA	2x SATA 3.0 ports (6Gbps) 4x SATA 2.0 ports (3Gbps)																																																																																																																																								
LAN	2x RJ45 Gigabit Ethernet LAN ports 1x dedicated LAN port for IPMI																																																																																																																																								
USB	4x USB 2.0 rear ports																																																																																																																																								
Video	1x VGA Port																																																																																																																																								
Serial Port / Header	1 Fast UART 16550 serial port																																																																																																																																								
System BIOS																																																																																																																																									
BIOS Type	16MB SPI Flash EEPROM with AMI® BIOS																																																																																																																																								
BIOS Features	Plug and Play (PnP) PCI 2.2 ACPI up to 3.0 USB Keyboard support																																																																																																																																								
Chassis																																																																																																																																									
Form Factor	1U Rackmount																																																																																																																																								
Model	CSE-818A-1K43LPB																																																																																																																																								
Dimensions																																																																																																																																									
Height	1.7" (43mm)																																																																																																																																								
Width	17.2" (437mm)																																																																																																																																								
Depth	27.75" (705mm)																																																																																																																																								
Weight	Gross: 48.5 lbs / Net: 27 lbs																																																																																																																																								
Available Colors	Black																																																																																																																																								
Front Panel																																																																																																																																									
Buttons	Power On/Off button System Reset button																																																																																																																																								
LEDs	Power LED Hard drive activity LED 2x Network activity LEDs System Overheat LED																																																																																																																																								
Expansion Slots																																																																																																																																									
PCI-Express	1x PCI-E 3.0 x16 Low-profile Slot																																																																																																																																								
Drive Bays																																																																																																																																									
Hot-swap	3x 3.5" Hot-sw ap SATA3 HDD Bays with RAID 0, 1, 5 (Software RAID)																																																																																																																																								
Backplane																																																																																																																																									
SAS/SATA HDD Backplane (SAS support requires optional SAS controller)																																																																																																																																									
Peripheral Drives																																																																																																																																									
DVD-ROM	1x Slim DVD-ROM (Optional)																																																																																																																																								
System Cooling																																																																																																																																									
Fans	7x 4cm Counter-rotating fans with optimal fan speed control																																																																																																																																								
Shroud	1x Air Shroud																																																																																																																																								
Power Supply																																																																																																																																									
1400W High-efficiency AC power supply with Digital Switching Control & PMBus 1.2																																																																																																																																									
AC Voltage	1200W: 100-140 V, 14.7-10.5A, 50-60 Hz 1400W: 180-240 V, 10.5-8.0A, 50-60 Hz																																																																																																																																								
+5V standby	6 Amp																																																																																																																																								
+12V	100 Amp/115 Vac 117 Amp/230 Vac																																																																																																																																								
With Power Distributor	+5V: 30 Amp +3.3V: 25 Amp -12V: 0.6 Amp																																																																																																																																								
Certification	 Platinum Certified																																																																																																																																								
PC Health Monitoring																																																																																																																																									
CPU	Monitors for CPU Cores, +1.2V, 1.5V, +3.3V, +12V, (+3V, 1.0V, 1.2V, 1.8V, 1.1V) Standby, VBAT, Memory, Chipset Voltages. 4-Phase-switching voltage regulator with auto-sense from 0.6V-1.35V																																																																																																																																								
FAN	4-pin fan headers with tachometer status monitoring Low noise fan speed control mode																																																																																																																																								
Temperature	Monitoring for CPU and system environment Thermal Control for 10x fan connectors																																																																																																																																								
Other Features	Chassis intrusion detection																																																																																																																																								
Operating Environment / Compliance																																																																																																																																									
RoHS	RoHS Compliant																																																																																																																																								
Environmental Spec.	Operating Temperature: 10°C to 35°C (50°F to 95°F) Non-operating Temperature: -40°C to 70°C (-40°F to 158°F) Operating Relative Humidity: 8% to 90% (non-condensing) Non-operating Relative Humidity: 5% to 95% (non-condensing)																																																																																																																																								