


GIGA- TRIM

Giga-Trims® are tiny trimmer capacitors which provide a straight-forward technique for fine RF and microwave circuits by eliminating time consuming methods of abrasive trimming, cut and try adjustment techniques, and interchange of fixed capacitors.

The design evolved from the need for a virtually indestructible miniature trimmer with superior electrical characteristics. Giga-Trim® capacitors withstand the rigors of soldering heat, excessive tuning and rough handling. As a result of the excellent dielectric and insulation properties of the sapphire housing, high breakdown voltage is achieved. Incorporating the patented self-locking constant torque drive mechanism* which eliminates the need for external bushing slots, the new Giga-Trim® offers many improvements: a fixed length, increased Q, essentially zero tuning noise and reduced susceptibility to solder flux intrusion during installation.

A variety of mounting styles is available for vertical, printed circuit, panel, cavity and strip-line applications.



APPLICATIONS

- RF amplifier
- Impedance matching
- Crystal trimming
- Interstage coupling
- Filter tuning

CHARACTERISTICS

- Working Voltage: 500 VDC (1000 VDC Test)
- Long rotational life
- Insulation resistance: $> 10^6$ M Ω
- Temperature range: -65°C to +125°C
- RoHS compliant

CAPACITANCE RANGE	SERIES	Q @ 250 MHZ	PAGE
0.3 TO 1.2 pF	27260	> 5000	2
0.4 TO 2.5 pF	27280	> 4000	2
	47280	> 4000	3
0.3 TO 2.3 pF	47480	> 2000	3
0.6 TO 4.5 pF	17270	> 2000	3
	27270	> 3000	3
	47270	> 3000	3
	57280	> 1000**	3
0.8 TO 8.0 pF	27290	> 3000*	4
	57270	> 1000*	4
2.0 TO 6.0 pF	47470	> 1500**	4

* @ 100MHz ** @ 200 MHz

TERMINAL CONFIGURATION




0.3 to 1.2 pF

- Capacitance Range: 0.3 to 1.2 pF (>5 turns)
- Working Voltage: 500 VDC (1000 VDC Test)
- Torque: 0.1 to 1 oz. In.
- Tuning Tool: 8762 or 8762-1
- Optional Seal Cap: P4445-1 or P4446-1
- RoHS Compliant


27260

Q @ 250 MHz
>5000
Sapphire




27261

Q @ 250 MHz
>5000
Sapphire



27261SL


Q @ 250 MHz
>5000
Sapphire



27263

Q @ 250 MHz
>5000
Sapphire

Available in Tape/Reel
27263-2R2
1000 pcs/Reel




0.4 to 2.5 pF

- Capacitance Range: 0.4 to 2.5 pF (>4 turns)
- Working Voltage: 500 VDC (1000 VDC Test)
- Torque: 0.2 to 2 oz. In.
- Tuning Tool: 8766 or 8766-1
- Optional Seal Cap: P4445 or P4446
- RoHS Compliant


27280

Q @ 250 MHz
>4000
Sapphire




27281

Q @ 250 MHz
>4000
Sapphire



27281SL


Q @ 250 MHz
>4000
Sapphire



27283

Q @ 250 MHz
>4000
Sapphire

Available in Tape/Reel
27283-3R10
750 pcs/Reel



0.4 TO 2.5 pF

47283 Q @ 250 MHz >4000 Alumina Available in Tape/Reel 47283-R10 750 pcs/Reel	
47483 (0.3 to 2.3 pF) Q @ 237 MHz >2000 Alumina Available in Tape/Reel 47483-R10 750 pcs/Reel	

0.6 TO 4.5 pF

27271SL Q @ 250 MHz >3000 Sapphire	
27273 Q @ 250 MHz >3000 Sapphire Available in Tape/Reel 27273-3R5 400 pcs/Reel	

0.6 TO 4.5 pF



- Capacitance Range: 0.6 to 4.5 pF (>8 turns)
- Working Voltage: 500 VDC (1000 VDC Test)
- Torque: 0.2 to 2 oz. In.
- Tuning Tool: 8766 or 8766-1
- Optional Seal Cap: P4445 or P4446
- RoHS Compliant




27270 Q @ 250 MHz >3000 Sapphire	
27271 Q @ 250 MHz >3000 Sapphire	

17273 Q @ 250 MHz >2000 Alumina Available in Tape/Reel 17273R5 400 pcs/Reel	
47273 Q @ 250 MHz >3000 Alumina Available in Tape/Reel 47273R5 400 pcs/Reel	
57283-1 Q @ 200 MHz >1000 Zirconia Available in Tape/Reel 57283-1R10 750 pcs/Reel	

0.8 TO 8.0 pF


- Capacitance Range: 0.8 to 8.0 pF (>16 turns)
- Working Voltage: 500 VDC (1000 VDC Test)
- Torque: 0.2 to 2 oz. In.
- Tuning Tool: 8766 or 8766-1
- Optional Seal Cap: P4445 or P4446
- RoHS Compliant

27290 Q @ 100 MHz >3000 Sapphire	
27291 Q @ 100 MHz >3000 Sapphire	

27291SL Q @ 100 MHz >3000 Sapphire	
27293 Q @ 100 MHz >3000 Sapphire	
57273-1 Q @ 100 MHz >2000 Zirconia Available in Tape/Reel 57273-1R5 400 pcs/Reel	

2.0 TO 6.0 pF

- Capacitance Range: 2.0 to 6.0 pF (>6 turns)
- Working Voltage: 500 VDC (1000 VDC Test)
- Torque: 0.2 to 2 oz. In.
- Tuning Tool: 8766 or 8766-1
- RoHS Compliant

47473 Q @ 213 MHz >1500 Alumina Available in Tape/Reel 47473R5 400 pcs/Reel	
---	---

