




.079" [2.00 mm] Contact Centers, IDC Sockets, Insulation Displacement With or Without Strain Relief- SFH Series Mates with SBH21 series (See opposite page)

SPECIFICATIONS

- Centered Polarizing Key Optional
- Operating Temperature: -45°C to +105°C
- UL Flammability Rating: 94V-0
- Current Rating: 1 Amp
- Dielectric Withstanding: 500 VAC
- Insulation Resistance: 1000 Megohms



PART NUMBER OPTIONS

SERIES	SFH21 - P P P N - D 10 - ID - BK - M181	MODIFICATION (Omit for Standard)
SFH21 = IDC Socket Without Strain Relief, .079" [2.00 mm] Contact Centers by .079" [2.00 mm] Row Spacing		M181 = Without Centered Polarizing Key
SFH213 = IDC Socket With Strain Relief, .079" [2.00 mm] Contact Centers by .079" [2.00 mm] Row Spacing		COLOR
INSULATOR MATERIAL		BK = Black
P = PBT		TERMINATION TYPE
CONTACT MATERIAL		ID = Insulation Displacement
P = Phosphor Bronze		NUMBER OF CONTACT POSITIONS
CONTACT FINISH - RoHS Compliant		03 thru 13, 15, 17, 20, 22, 25, 30, 34 (SFH21)
P = Gold Flash Overall		05 thru 13, 15, 17, 20, 22, 25 (SFH213)
V = Gold Flash on Contact Surface, Nickel on Termination		NUMBER OF ROWS
		D = Dual Row
		CONTACT CENTERS
		N = .079" [2.00 mm]

DIMENSIONS For complete drawings, go to www.sullinscorp.com or e-mail techsupport@sullinscorp.com Dimensions in [] are in millimeters, all others are in inches.

