




Hover over the line on the graph above to view the runtime at any desired load


This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.

[View Enlarged Graph](#)

[View Runtime Chart](#)

Energy Use/Efficiency

Load	Efficiency
25%	97.7%
50%	98.7%
75%	99.0%
100%	99.0%



Hover over the line on the graph above to view the efficiency at any desired load

Curve fit of data measured in accordance with the ENERGY STAR Program Requirements Product Specification for Uninterruptible Power Supplies (UPSs) - Eligibility Criteria Version 1.0. All measurements taken in normal mode(s), at typical environmental conditions, with 120V/60Hz electrical input and balanced resistive load (PF = 1.0) output.

[View Enlarged Graph](#)

Communications & Management

Interface Port(s)	USB
Control panel	LED status display with On Line : On Battery : Replace Battery and Building Wiring Fault
Audible Alarm	Alarm when on battery : distinctive low battery alarm

Surge Protection and Filtering

Surge energy rating	340 Joules
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449
Data Line Protection	RJ45 10/100 Base-T Ethernet protection

Physical

Maximum Height	3.46 inches (88 mm)
----------------	---------------------

Maximum Width	7.09 inches (180 mm)
Maximum Depth	11.89 inches (302 mm)
Net Weight	13.64 lbs. (6.20 kg)
Shipping Weight	15.40 lbs. (7.00 kg)
Shipping Height	5.04 inches (128 mm)
Shipping Width	9.25 inches (235 mm)
Shipping Depth	15.47 inches (393 mm)
Master Carton Units	2.00
Master Carton Weight	31.68 lbs. (14.40 kg)
Color	Black
SCC Codes	1073130428543 1
Units per Pallet	100.00
# of Layers per Pallet	5
# of Units per Layer per Pallet	20
Environmental	
Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	5 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	5 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	45.00 dBA
Conformance	
Regulatory Approvals	CSA C22.2 No. 107.1,ENERGY STAR (USA),FCC Part 15 Class B,FCC Part 68,NOM,TUV-C,UL 1778
Standard Warranty	3 years repair or replace
Equipment protection policy	Lifetime :
Environmental Compliance	RoHS,REACH: Contains No SVHCs

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.

**The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.