

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B2	REVISED PER ECO-11-005033	24MAR11	RK	HMR



- NOTES:
- 1 MATERIAL : 66 NYLON (UL94V-0)
  - 2. PRODUCT SPEC.: 108-5408
  - 3. APPLICATION SPEC.: 114-5179
  - 4 7-179228-3 WAS OBSOLETE.
  - 5 CAVITY NUMBER LOCATED. (OPTIONAL)



7-179228-5	5-179228-5	3-179228-5	1-179228-5	15	28	30.8	32.0
7-▲	▲	▲	▲	14	26	28.8	30.0
7-▲	▲	▲	▲	13	24	26.8	28.0
7-	5-	3-	1-	12	22	24.8	26.0
7-	5-	3-	1-	11	20	22.8	24.0
7-	5-	3-	1-	10	18	20.8	22.0
6-	4-	2-		9	16	18.8	20.0
6-	4-	2-		8	14	16.8	18.0
6-	4-	2-		7	12	14.8	16.0
6-	4-	2-		6	10	12.8	14.0
6-	4-	2-		5	8	10.8	12.0
6-	4-	2-		4	6	8.8	10.0
6-	4-	2-		3	4	6.8	8.0
6-179228-2	4-179228-2	2-179228-2	179228-2	2	2	4.8	6.0
BLACK	YELLOW	BLUE	NATURAL	POS	A	B	C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	12NOV1993		TE Connectivity CRIMP TYPE II RECEPTACLE HOUSING (AMP CT CONNECTOR 2mm PITCH)
DIMENSIONS: mm		CHK	15NOV1993		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	15NOV1993		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	-		
MATERIAL		APPLICATION SPEC	-		NAME
SEE NOTE 1		WEIGHT	-		SIZE
GENERAL TOLERANCE		CUSTOMER DRAWING			CAGE CODE
0 < * ≤ 10 : ±0.2 10 < * ≤ 30 : ±0.25 30 < * ≤ 100 : ±0.3 ANGLES : ±3°		SCALE			DRAWING NO
		A300779			RESTRICTED TO
		G-179228			REV
		NTS			B2
		SHEET 1 OF 1			