

83265 Coax - 50 Ohm Coax

 For more Information
 please call

1-800-Belden1

**General Description:**

30 AWG stranded (7x38) .012" silver-plated copper-covered steel conductor, TFE Teflon® insulation, silver-plated copper braid shield (95% coverage), FEP jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	30	7x38	SPCCS - Silver Plated Copper Covered Steel	.012

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Teflon®	TFE - Tetrafluoroethylene	.033

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	SPC - Silver Plated Copper	95.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 0.071 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-70°C To +200°C
UL Temperature Rating:	90C
Bulk Cable Weight:	5 lbs/1000 ft.
Max. Recommended Pulling Tension:	12 lbs.
Min. Bend Radius/Minor Axis:	1 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Military Specification:	MIL-C-17, M17/93-RG178
Other Specification:	UL Style 1637
RG Type:	178B/U

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
50

Nom. Inductance:

Inductance (µH/ft)
0.072

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
29.0

Nominal Velocity of Propagation:

VP (%)
69.5

Nominal Delay:

Delay (ns/ft)
1.46

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
244.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
14.6

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	2.6
10	5.6
50	10.5
100	14.0
200	19.0
400	28.0
700	37.0
900	42.5
1000	46.0

Nom. Power Rating:

Freq. (MHz)	Rating (W)
50	380
100	253
200	170
400	113
700	81
900	70
1000	66

Max. Operating Voltage - UL:

Voltage	Description
30 V rms	AWM 1637

Max. Operating Voltage - Other:

Voltage	Description
Military Specification	750 V RMS

Misc. Information (Overall)**Notes (Overall)**

Notes: Military Specification (M17/93) Operating Temperature: -55C to 200C. - - - Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83265 009100	100 FT	0.800 LB	WHITE	E	M17/93-RG178
83265 0091000	1,000 FT	6.000 LB	WHITE	E	M17/93-RG178
83265 009500	500 FT	3.500 LB	WHITE	E	M17/93-RG178

Notes:

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 5 Revision Date: 09-03-2014

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.