

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

CE

16

P

LTR

DESCRIPTION

DATE

DWN

APVD

C

ECR-14-011637

22AUG2014

HZ

RZ

1

MAXIMUM CONNECTOR INSERTION LOSS IS 0,2dB PLUS
CABLE ATTENUATION OF 1,5dB/Km AT 1300nm(SEE TABLE)

2. PRODUCT AND PROCESSING MUST MEET
REQUIREMENTS OF TE STANDARD TEC-138-702

0,15 MAX

” L ”

TRACE LABEL

CABLE, 50/125um,
2.0mm JACKET

LC CONNECTOR, MM
2 PLACES

0.20	0.200+0.030/-0.000 [7.87+1.18/-0.00]	8-6374656-0
0.22	10.00±0.15 [393.70±6.00]	1-6374656-0
0.21	5.00±0.08 [196.9±3.1]	6374656-5
0.21	4.00±0.08 [157.5±3.00]	6374656-4
0.20	3.00±0.05 [118.1±2.0]	6374656-3
0.20	2.00±0.05 [78.7±2.0]	6374656-2
0.20	1.00±0.05 [39.4±2.0]	6374656-1
MAX IL(dB)1	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
METERS [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL -

DWN
C.S.VASU
15SEP05

CHK
J.DUNCAN
15SEP05

APVD
J.DUNCAN
15SEP05

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

STE

TE Connectivity

NAME
CABLE ASSEMBLY, FIBER OPTIC, 50/125um, 2.0mm
LC TO LC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-6374656

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
C

1470-19 (3/11)