



① SR




② M




③ H

④ S



⑥ D1.D2



Electrical Characteristics:

Current Rating: 1 AMPeres.

Dielectric Withstanding Voltage: AC 600V r.m.s

Insulator Resistance: 1000M min.at DC 500V.

Contact Resistance: 15Milliohm Maximum.

Operating Temperature: -55°C~+105°C.

MATERIALS:

Contacts: BRASS STRIP

1u" gold plating on contact area

80u" Ni plating on soldertails area


Insuiator: PBT, UL 94V-0 (ROHS)

FEATURES:

Accommodates 24-26 AWG solid or

Contact positions: 09,15,25,37.

⑤ C



SIZE	A±0.38	B±0.13	C±0.13	D±0.25	D1	D2
9	30.81	24.99	16.33	22.54	ø3.2	#4-40
15	39.14	33.32	24.66	30.87		
25	53.04	47.04	38.38	44.60		
37	69.32	63.50	54.84	61.06		

BOM

ITEM	DWG.NO.	TITLE	MATERIAL	QTY	ITEM	DWG.NO.	TITLE	MATERIAL	QTY
1.		SR	PBT	1	5.		Contact	Brass / GOLD vs Ni	25
2.		M	PBT	1	6.		Rivet	SPCC / Ni	2
3.		Housing	PBT	1					
4.		Steel	SPCC / Ni	1					

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO.
12408

GOLDSUN NO.

Description

DB25 RIBBON CABLE ASSEMBL
MALE TO FEMALE 4FT LENGTH

Rev.

1

UNIT:
mm

SCALE:

SHEET 1 OF 1

CAS No:
ERN No: