

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

19


(C) COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	H	REV & REDWN PER EC 0G1B--98	20-OCT-98	TB	RS	



ALTERNATE CONSTRUCTION



1. WIRE RANGE: 0.3 - 0.9 mm² (22 - 18 AWG)
2. INSULATION RANGE: 2.16 - 2.67




19.30	.760
18.16	.715
4.19	.165
4.06	.160
3.81	.150
3.18	.125
2.92	.115
2.87	.113
2.67	.105
2.54	.100
2.16	.085
1.57	.062
1.07	.042
0.32	.013
0.13	.005
MM	IN
CONVERSION TABLE	

METRIC

60951-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK	20-OCT-98	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK R. SWING	20-OCT-98		
DIMENSIONS: mm		APVD C. MARTIN	20-OCT-98	NAME SOCKET, AUTOMOTIVE MATE-N-LOK™	
		PRODUCT SPEC —			
		APPLICATION SPEC —		SIZE A3	
		WEIGHT —			
MATERIAL 0.32 BRASS	FINISH PRE-TIN			CAGE CODE 00779	DRAWING NO C- 60951
CUSTOMER DRAWING		SCALE 5:1		RESTRICTED TO —	
				SHEET 1 OF 1	
				REV H	