



PRODUCTS

INDUSTRY SOLUTIONS

CAREERS

RESOURCES

CONTACT MOLEX

FIND DISTRIBUTOR

Home: Crimp Housings >

Part Number: 22-01-2226

KK® 254 Crimp Housing, 22 Circuits



Series image - Reference only

Status:	New Business Not Supported
Replacement:	No replacement
Series:	6471
Category:	Crimp Housings
Overview:	KK® Interconnect System - Molex
Engineering/Old PN:	6471-22

CHECK DISTRIBUTOR INVENTORY [Add to My Parts](#) [Email this page](#)Go to [Part Detail](#) ▾**Mates With Part(s):**KK®254 PCB Headers [42375](#), [42377](#), [42376](#), [4030](#), [6373](#), [6410](#), [171856](#), [171857](#)**Use With Part(s):**[2759](#), [4809](#) KK® Crimp terminal**Product Environmental Compliance****EU ELV:** Not Relevant**EU RoHS:** Compliant**EU RoHS Phthalates:** Not Contained**China RoHS:** **REACH SVHC:** Not Contained Per - ED/01/2017 (12 January 2017)**Low-Halogen Status:** Low-Halogen

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****General**

Status	New Business Not Supported
Category	Crimp Housings
Series	6471
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800753740976

Physical

Circuits (maximum)	22
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	2.121/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	See Product Specification

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	3.5A, 3.75A, 3.0A, 4.0A
-------------------------------	-------------------------

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

CSA	LR19880
UL	E29179

Material Info

Engineering Number	6471-22
--------------------	---------

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

