

**Device markers**  
**LM MT DIN A5 9/11 GN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-2083  
[www.weidmueller.com](http://www.weidmueller.com)



- Adhesive polyester labels
- Suitable for DIN A4 laser printer,
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

**General ordering data**

|            |                                                                      |
|------------|----------------------------------------------------------------------|
| Order No.  | <a href="#">1964120000</a>                                           |
| Type       | LM MT DIN A5 9/11 GN                                                 |
| Version    | Device markers, Label, 11 x 9 mm, Polyester, PVC-free, Colour: Green |
| GTIN (EAN) | 4032248647200                                                        |
| Qty.       | 10 pc(s).                                                            |

**Device markers**  
**LM MT DIN A5 9/11 GN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-2083  
 www.weidmueller.com

**Technical data**
**Dimensions**

|        |       |            |       |
|--------|-------|------------|-------|
| Length | 11 mm | Width      | 9 mm  |
| Height | 9 mm  | Net weight | 5.8 g |

**Markings**

|                                   |                             |                                                |               |
|-----------------------------------|-----------------------------|------------------------------------------------|---------------|
| Adhesive                          | Permanent acrylic copolymer | Can be labelled with thermal transfer printers | No            |
| Can be printed with plotter       | Yes                         | Can be written with dot-matrix printer         | No            |
| Can be written with laser printer | Yes                         | Colour                                         | Green         |
| Conductor O.D.                    | -                           | Flammability class UL 94                       | HB            |
| Material                          | Polyester, PVC-free         | Material colour according to resistance code   | 5             |
| Number per sheet                  | 168                         | Operating temperature range, max.              | 150 °C        |
| Operating temperature range, min. | -45 °C                      | Pin can be written (STI)                       | Yes           |
| PrintJet                          | No                          | Printing method                                | Laser print   |
| Speed marking laser               | No                          | Version                                        | Self-adhesive |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 2.0   | EC001288    | ETIM 3.0   | EC001288    |
| UNSPSC     | 30-21-18-01 | eClass 4.1 | 24-19-02-18 |
| eClass 5.1 | 27-14-91-29 | eClass 6.0 | 27-14-91-29 |
| eClass 7.0 | 27-14-91-29 |            |             |