


WRAPOST RECEPTACLES

FOR .022" - .032" DIAMETER PINS (#06 CONTACT)
FOR .022" - .034" DIAMETER PINS (#16 CONTACT)

2297

2297-X-17-XX-16-XX-02-0

Press-fit in .067 mounting hole




Basic Part Number	# of Wraps	Length A
2297-2	2	.370
2297-3	3	.430

0280

0280-X-17-XX-06-XX-02-0

Press-fit in .081 mounting hole




Basic Part Number	# of Wraps	Length A
0280-2	2	.360
0280-3	3	.510

0281

0281-3-17-XX-06-XX-02-0

Press-fit in .080 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 17 - XX - XX - XX - 02 - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **15** 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **27** 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#06 or #16 CONTACT (DATA ON PAGES 255 & 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com