




FACE VIEW - MALE INSERT SCALE 2 : 1




1 BROWN
2 BLUE




1 GREEN
2 RED/BLACK
3 RED/WHITE





1 RED/BLACK
2 RED/WHITE
3 RED
4 GREEN



1 RED/WHITE
2 RED
3 GREEN
4 RED/YELLOW
5 RED/BLACK



1 RED/WHITE
2 RED
3 GREEN
4 RED/YELLOW
5 RED/BLACK
6 RED/BLUE



FINAL ASSEMBLY
1200740030 (SHOWN)

ENTER DESCRIPTION EC NO: WNA2010-0078 DRAWN BY: NKUMAR01 CHKD: 2009/08/27 APP: JFMURPHY 2009/08/28	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY NKUMAR01	DATE 26/08/09	TITLE MIC 2P MR 12IN. 1/4NPT #22 PVC				
			4 PLACES	± ---	± ---	CHECKED BY BWOODMAN	DATE 26/08/09					
			3 PLACES	± ---	± ---	APPROVED BY JFMURPHY		DATE 2009/08/27	MOLEX MOLEX INCORPORATED			
			2 PLACES	± ---	± ---							
			1 PLACE	± ---	± ---	MATERIAL NO. SEE SHEET 2		DOCUMENT NO. SD-120074-030	SHEET NO. 1 OF 2			
			ANGULAR ±1/2°									
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			REV			SIZE						
			A			C						

		MALE RECEPTACLE ASSEMBLY				
		2 POLE	3 POLE	4 POLE	5 POLE	6 POLE
Sl. No.	DESCRIPTION	QUANTITY				
1	RECEPTACLE SHELL #1/4-18 NPT	1	1	1	1	1
2	LABEL,SELF L,YELLOW(2.25X.75IN)	1	1	1	1	1
3	PIN CONT 2-4P MIC GLD #22AWG	2	3	4		
	PIN CONT 5&6P MICGLD #22AWG				5	6
4	O-RING .489 ID X .070 THK	1	1	1	1	1
5	#1/4-18IN NPS LOCKNUT	1	1	1	1	1
6	MIC 2P MALE INSERT (NYLON)	1				
	MIC 3P MALE INSERT (NYLON)		1			
	MIC 4P MALE INSERT (NYLON)			1		
	MIC 5P MALE INSERT (NYLON)				1	
	MIC 6P MALE INSERT (NYLON)					1
7	#22-1 BLU PVC WIRE UL1061	1				
	#22-1 GRN PVC WIRE UL1061		1	1	1	1
	#22-1 BRN PVC WIRE UL1061	1				
	#22-1 RED PVC WIRE UL1061			1	1	1
	#22-1 RED/WHT PVC WIRE UL1061		1	1	1	1
	#22-1 RED/BLK PVC WIRE UL1061		1	1	1	1
	#22-1 RED/BLU PVC WIRE UL1061					1
	#22-1 RED/YEL PVC WIRE UL1061				1	1

PART NUMBER	DESCRIPTION	FINISHED LENGTH
1200740030	7R2A06A19A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1200740079	7R3A06A19A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1200740140	7R4A06A19A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1200740190	7R5A06A19A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1200740241	7R6A06A19A120	12.0" +.75" -0 [0.3M +19.1MM -0]

ENTER DESCRIPTION EC NO: WNA2010-0078 DRAWN BY: NKUMAR01 CHKD: 2009/08/27 APPR: JFMURPHY 2009/08/28	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
				DRAWN BY NKUMAR01	DATE 26/08/09	TITLE MIC 2P MR 12IN. 1/4NPT #22 PVC			
				CHECKED BY BWOODMAN	DATE 26/08/09				
				APPROVED BY JFMURPHY	DATE 2009/08/27				
A	REV	ANGULAR ±1/2°		MATERIAL NO.		MOLEX INCORPORATED		SHEET NO. 2 OF 2	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		DOCUMENT NO. SD-120074-030			
				SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				