


Power Entry Modules With Filters

The Schurter power entry modules with filters come in many variations: connector, on/off switch, 1- or 2-pole fuseholder, voltage selector, standard or medical RFI filter. These units are approved at 250 V by a multitude of international agencies including UL, CSA, VDE, SEMKO and SEV.

AC Inlet, 1 and 2-Pole Fuseholder, Switch




Series KMF with RFI filter, fuseholder with EMC shield, 2-pole and On/Off switch. Order fusedrainers separately below. Other filter ratings available.

| Stock No. | Mfr.'s Type  | Filter (Amps)  | Leakage Current | Fuseholder       | EACH  |       |
|-----------|--------------|----------------|-----------------|------------------|-------|-------|
|           |              |                |                 |                  | 1-24  | 25-Up |
| 509-8001  | KMF1.1211.11 | 1 A, Standard  | <0.5 mA         | 1-Pole 5 × 20 mm | 17.29 | 16.89 |
| 509-8002  | KMF1.1261.11 | 6 A, Standard  | <0.5 mA         | 1-Pole 5 × 20 mm | 17.29 | 16.89 |
| 509-8003  | KMF1.1291.11 | 10 A, Standard | <0.5 mA         | 1-Pole 5 × 20 mm | 17.29 | 16.89 |
| 509-8004  | KMF1.1111.11 | 1 A, Standard  | <0.5 mA         | 2-Pole 5 × 20 mm | 19.15 | 18.75 |
| 509-8010  | KMF1.1161.11 | 6 A, Standard  | <0.5 mA         | 2-Pole 5 × 20 mm | 19.15 | 18.75 |
| 509-8005  | KMF1.1191.11 | 10 A, Standard | <0.5 mA         | 2-Pole 5 × 20 mm | 19.15 | 18.75 |

Fusedrawer (Order Fuses Separately)

509-3304, 4301.1407, 1-pole, 5 × 20 mm with voltage selector, black.....EACH 1.91  
509-3308, 4301.1403, 2-pole, 5 × 20 mm without voltage selector, black.....EACH 3.29

AC Inlet with Line Filter, 2-Pole Fuseholder, Switch and Interchangeable Fusedrainers for 1/4" × 1 1/4" or 5 × 20 mm Fuses



Series 4303 and CD with single or double pole shocksafe fuseholder. Inlets available with or without series voltage selection. Series CD with DPST integral switch. Terminals are 4.8 mm × .8 mm quick-connect. Order fusedrainers separately below.


| Stock No. | Mfr.'s Type   | Filter (Amps)  | Leakage Current | D × H × W (mm)   | EACH  |       |
|-----------|---------------|----------------|-----------------|------------------|-------|-------|
|           |               |                |                 |                  | 1-24  | 25-Up |
| 509-4000  | 4303.5021     | 1 A, Standard  | <0.5 mA         | 69.5 × 58.0 × 30 | 19.71 | 17.74 |
| 509-4002  | 4303.5022     | 2 A, Standard  | <0.5 mA         | 69.5 × 58.0 × 30 | 19.71 | 17.74 |
| 509-4004  | 4303.5023     | 4 A, Standard  | <0.5 mA         | 69.5 × 58.0 × 30 | 19.71 | 17.74 |
| 509-4006  | 4303.5024     | 6 A, Standard  | <0.5 mA         | 69.5 × 58.0 × 30 | 19.71 | 17.74 |
| 509-4007  | 4303.5025     | 10 A, Standard | <0.5 mA         | 69.5 × 58.0 × 30 | 21.17 | 17.64 |
| 509-4008  | 4303.5225     | 4 A, Medical   | <5.0 µA         | 69.5 × 58.0 × 30 | 25.82 | 23.24 |
| 509-4010  | 4303.5227     | 6 A, Medical   | <5.0 µA         | 69.5 × 58.0 × 30 | 25.82 | 23.24 |
| 509-4012  | CD14.4101.151 | 1 A, Standard  | <0.5 mA         | 69.5 × 83.5 × 30 | 28.56 | 25.71 |
| 509-4014  | CD24.4101.151 | 2 A, Standard  | <0.5 mA         | 69.5 × 83.5 × 30 | 28.56 | 25.71 |
| 509-4015  | CD34.4101.151 | 4 A, Standard  | <0.5 mA         | 69.5 × 83.5 × 30 | 28.56 | 25.71 |
| 509-4016  | CD64.4101.151 | 1 A, Medical   | <5.0 µA         | 69.5 × 83.5 × 30 | 37.40 | 33.66 |
| 509-4018  | CDA4.4101.151 | 2 A, Medical   | <5.0 µA         | 69.5 × 83.5 × 30 | 37.40 | 33.66 |

Fusedrainers

| Stock No. | Mfr.'s Type   | Voltage Selector   | Color | Fuses                | EACH |       |
|-----------|---------------|--------------------|-------|----------------------|------|-------|
|           |               |                    |       |                      | 1-24 | 25-Up |
| 509-3011  | 4303.2401     | None               | Black | 2-Pole, 5 × 20 mm    | 2.77 | 1.96  |
| 509-3012  | 4303.2902     | None               | Grey  | 2-Pole, 1/4 × 1 1/4" | 2.77 | 1.96  |
| 509-4022  | 4303.2406     | None               | Black | 1-Pole, 5 × 20 mm    | 1.94 | 1.67  |
| 509-3014  | 4303.2912     | None               | Grey  | 1-Pole, 1/4 × 1 1/4" | 6.41 | 5.32  |
| 509-3015  | 4303.2014.01  | 100, 120, 220, 240 | Black | 2-Pole, 5 × 20 mm    | 5.90 | 5.16  |
| 509-3016  | 4303.2714.01  | 100, 120, 220, 240 | Grey  | 2-Pole, 1/4 × 1 1/4" | 5.90 | 5.16  |
| 509-4030  | 4303.2114.01  | 100, 120, 220, 240 | Black | 1-Pole, 5 × 20 mm    | 4.13 | 3.62  |
| 509-4034  | 4303.2403*    | None               | Black | 2-Pole, 5 × 20 mm    | 5.30 | 4.64  |
| 509-4036  | 4303.2904*    | None               | Grey  | 2-Pole, 1/4 × 1 1/4" | 5.30 | 4.64  |
| 509-4038  | 4303.2024.01* | 100, 120, 220, 240 | Black | 2-Pole, 5 × 20 mm    | 6.55 | 5.73  |
| 509-4040  | 4303.2724.01* | 100, 120, 220, 240 | Grey  | 2-Pole, 1/4 × 1 1/4" | 6.55 | 5.73  |

\*Tool accessible only. **Note:** Fusedrainers Must Be Ordered Separately.


AC Inlet with 1-Pole Fuseholders 70°C, 10 A, 250 V



Series 5200 filtered version, series 6200 without filter. Rated up to 10 A/250 V, fuseholder is 1-Pole. Accepts 5 × 20 mm fuse.

| Stock No. | Mfr.'s Type | Filter (Amps)  | Leakage Current | Mounting           | EACH  |       |
|-----------|-------------|----------------|-----------------|--------------------|-------|-------|
|           |             |                |                 |                    | 1-24  | 25-Up |
| 509-1001  | 5200.0123.1 | 1 A, Standard  | <0.5 mA         | Flange             | 15.45 | 14.55 |
| 509-8602  | 5200.0143.1 | 1 A, Standard  | <0.5 mA         | Snap-in 0.8-3.0 mm | 14.17 | 13.15 |
| 509-1002  | 5200.0623.1 | 6 A, Standard  | <0.5 mA         | Flange             | 15.45 | 14.55 |
| 509-2000  | 5200.0643.1 | 6 A, Standard  | <0.5 mA         | Snap-in 0.8-3.0 mm | 19.18 | 16.73 |
| 509-1003  | 5200.1023.1 | 10 A, Standard | <0.5 mA         | Flange             | 19.18 | 16.74 |
| 509-1004  | 5200.1043.1 | 10 A, Standard | <0.5 mA         | Snap-in 0.8-3.0 mm | 19.18 | 16.74 |
| 509-1100  | 6200.2100   | Without        | —               | Flange             | 2.95  | 2.39  |
| 509-1105  | 6200.2200   | Without        | —               | Flange             | 2.95  | 2.39  |
| 509-1110  | 6200.2300   | Without        | —               | Flange             | 2.95  | 2.39  |
| 509-1115  | 6200.4115   | Without        | —               | Snap-in 1.5 mm     | 2.95  | 2.39  |
| 509-1120  | 6200.4215   | Without        | —               | Snap-in 1.5 mm     | 2.95  | 2.39  |
| 509-1125  | 6200.4315   | Without        | —               | Snap-in 1.5 mm     | 2.95  | 2.39  |

Line Filter with AC Connector, Series Parallel Voltage Selection and Interchangeable FuseDrawers for 1/4" × 1 1/4" or 5 × 20 mm Fuses



Series CE/CG with single or double pole shocksafe fuseholder and series parallel voltage selection. Terminals are 4.8 × 8 mm quick connect. Series CG with DPST integral switch, 70 A in-rush current (3-4 ms).

| Stock No. | Mfr.'s Type   | Filter (Amps)  | Leakage Current | D × H × W (mm) | EACH  |       |
|-----------|---------------|----------------|-----------------|----------------|-------|-------|
|           |               |                |                 |                | 1-24  | 25-Up |
| 509-4042  | CE10.6100.151 | 1 A, Standard  | <0.5 mA         | 69 × 69.5 × 30 | 26.56 | 23.91 |
| 509-4046  | CE30.6100.151 | 4 A, Standard  | <0.5 mA         | 69 × 69.5 × 30 | 26.56 | 23.91 |
| 509-4048  | CE40.6100.151 | 6 A, Standard  | <0.5 mA         | 69 × 69.5 × 30 | 26.56 | 23.91 |
| 509-4049  | CE60.6100.151 | 10 A, Standard | <0.5 mA         | 69 × 69.5 × 30 | 28.52 | 25.93 |
| 509-4050  | CEG0.6100.151 | 1 A, Medical   | <5.0 µA         | 69 × 69.5 × 30 | 34.79 | 31.32 |
| 509-4054  | CECO.6100.151 | 4 A, Medical   | <5.0 µA         | 69 × 69.5 × 30 | 34.79 | 31.31 |
| 509-4056  | CEE0.6100.151 | 6 A, Medical   | <5.0 µA         | 69 × 69.5 × 30 | 34.79 | 31.31 |
| 509-4058  | CG10.6101.151 | 1 A, Standard  | <0.5 mA         | 69 × 97.0 × 30 | 37.71 | 33.94 |
| 509-4062  | CG30.6101.151 | 4 A, Standard  | <0.5 mA         | 69 × 97.0 × 30 | 37.71 | 33.94 |
| 509-4064  | CG40.6101.151 | 6 A, Standard  | <0.5 mA         | 69 × 97.0 × 30 | 37.71 | 33.94 |
| 509-4066  | CG60.6101.151 | 10 A, Standard | <0.5 mA         | 69 × 97.0 × 30 | 40.49 | 36.81 |
| 509-4068  | CGG0.6101.151 | 1 A, Medical   | <5.0 µA         | 69 × 97.0 × 30 | 49.39 | 44.36 |
| 509-9993  | CGCO.6101.151 | 4 A, Medical   | <5.0 µA         | 69 × 97.0 × 30 | 49.39 | 44.36 |
| 509-4074  | CGL0.6101.151 | 6 A, Medical   | <5.0 µA         | 69 × 97.0 × 30 | 49.39 | 44.36 |
| 509-4076  | CGL0.6101.151 | 10 A, Medical  | <5.0 µA         | 69 × 97.0 × 30 | 52.86 | 47.47 |

Voltage Selector

| Stock No. | Mfr.'s Type  | Markings           | EACH |       |
|-----------|--------------|--------------------|------|-------|
|           |              |                    | 1-24 | 25-Up |
| 509-3027  | 4305.0048.01 | 100, 120, 220, 240 | 4.47 | 3.43  |

**Note:** Voltage Selector Must Be Ordered Separately.

Fusedrainers

| Stock No. | Mfr.'s Type | Mounting             | Color | EACH |       |
|-----------|-------------|----------------------|-------|------|-------|
|           |             |                      |       | 1-24 | 25-Up |
| 509-3023  | 4305.0001   | 2-Pole, 5 × 20 mm    | Black | 3.94 | 3.49  |
| 509-3024  | 4305.0012   | 2-Pole, 1/4 × 1 1/4" | Grey  | 3.94 | 3.49  |
| 509-3025  | 4305.0021   | 1-Pole, 5 × 20 mm    | Black | 5.06 | 4.48  |
| 509-3026  | 4305.0027   | 1-Pole, 1/4 × 1 1/4" | Grey  | 5.06 | 4.48  |

**Note:** Fusedrainers Must Be Ordered Separately.