






△ ₂	-	2.54	-	5.08	4	9.65	10	8-104477-2
	-	1.27	12.7	15.24	12	19.81	26	8-104477-1
	5.72	1.27	11.43	13.97	11	18.54	24	8-104477-0
	17.15	1.27	34.29	36.83	29	41.40	60	7-104477-9
	-	3.18	-	6.35	5	10.92	12	7-104477-8
	29.85	1.27	59.69	62.23	49	66.80	100	7-104477-7
	23.5	1.27	46.99	49.53	39	54.10	80	7-104477-6
	-	1.27	27.94	30.48	24	35.05	50	7-104477-5
	-	1.27	21.59	24.13	19	28.70	40	7-104477-4
	-	1.27	15.24	17.78	14	22.35	30	7-104477-3
△ ₁	-	1.27	8.89	11.43	9	16.00	20	7-104477-2
	20.96	1.27	41.91	44.45	35	49.02	72	7-104477-1
	-	2.54	-	5.08	4	9.65	10	6-104477-2
	-	1.27	12.7	15.24	12	19.81	26	6-104477-1
	5.72	1.27	11.43	13.97	11	18.54	24	6-104477-0
	17.15	1.27	34.29	36.83	29	41.40	60	5-104477-9
	-	3.18	-	6.35	5	10.92	12	5-104477-8
	29.85	1.27	59.69	62.23	49	66.80	100	5-104477-7
	23.5	1.27	46.99	49.53	39	54.10	80	5-104477-6
	-	1.27	27.94	30.48	24	35.05	50	5-104477-5
△ ₁	-	1.27	21.59	24.13	19	28.70	40	5-104477-4
	-	1.27	15.24	17.78	14	22.35	30	5-104477-3
	-	1.27	8.89	11.43	9	16.00	20	5-104477-2
	20.96	1.27	41.91	44.45	35	49.02	72	5-104477-1

	-	2.54	-	5.08	4	9.65	10	3-104477-2
	-	1.27	12.7	15.24	12	19.81	26	3-104477-1
	5.72	1.27	11.43	13.97	11	18.54	24	3-104477-0
	17.15	1.27	34.29	36.83	29	41.40	60	2-104477-9
	-	3.18	-	6.35	5	10.92	12	2-104477-8
	29.85	1.27	59.69	62.23	49	66.80	100	2-104477-7
	23.5	1.27	46.99	49.53	39	54.10	80	2-104477-6
	-	1.27	27.94	30.48	24	35.05	50	2-104477-5
	-	1.27	21.59	24.13	19	28.70	40	2-104477-4
	-	1.27	15.24	17.78	14	22.35	30	2-104477-3
	-	1.27	8.89	11.43	9	16.00	20	2-104477-2
	20.96	1.27	41.91	44.45	35	49.02	72	2-104477-1
	-	2.54	-	5.08	4	9.65	10	1-104477-2
	-	1.27	12.7	15.24	12	19.81	26	1-104477-1
	5.72	1.27	11.43	13.97	11	18.54	24	1-104477-0
	17.15	1.27	34.29	36.83	29	41.40	60	104477-9
	-	3.18	-	6.35	5	10.92	12	104477-8
	29.85	1.27	59.69	62.23	49	66.80	100	104477-7
	23.5	1.27	46.99	49.53	39	54.10	80	104477-6
	-	1.27	27.94	30.48	24	35.05	50	104477-5
FINISH	-	1.27	21.59	24.13	19	28.70	40	104477-4
	-	1.27	15.24	17.78	14	22.35	30	104477-3
	-	1.27	8.89	11.43	9	16.00	20	104477-2
	20.96	1.27	41.91	44.45	35	49.02	72	104477-1
	DIM_F	DIM_E	DIM_D	DIM_C	B SPACES	DIM_A	NO OF POSM	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 20NOV2017 K. SHRISHAIL CHK 20NOV2017 J. OLSON APVD 20NOV2017 J. OLSON		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P.LC ± 2 P.LC ±0.3 3 P.LC ±0.13 4 P.LC ± 6 ANGLES ±0.5° FINISH		NAME HEADER ASSEMBLY, RIGHT ANGLE, DOUBLE ROW, W/SIDE & END LATCHES, AMPMODU System 50	
		PRODUCT SPEC 108-1093 APPLICATION SPEC 114-25031		SIZE A1	
MATERIAL 		WEIGHT SEE TABLE		CASE CODE 100779	
		CUSTOMER DRAWING		DRAWING NO C-104477	
				RESTRICTED TO -	
				SCALE 6:1 SHEET 1 of 1 REV AA	