


Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet		Rosenberger
RPC-TNC	Open Circuit Jack	06K12L-000S3
		
All dimensions are in mm; tolerances according to ISO 2768 m-H		
Interface		
According to		IEC 61169-26
Documents		
Application note		AN001 "Calibration Services"
Material and plating		
Connector parts		Material
Center conductor		CuBe
Outer conductor		Stainless steel
Dielectric		PTFE / PS
		Plating
		Gold, min. 1.27 µm, over nickel
		Passivated
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Email : info@rosenberger.de
		Page 1 / 3

Electrical data

Frequency range	DC to 18 GHz
Return loss	≤ 0.50 dB, DC to 4 GHz ≤ 1.00 dB, 4 GHz to 18 GHz
Error from nominal phase ¹	$\leq 3.5^\circ$, DC to 4 GHz $\leq 5.0^\circ$, 4 GHz to 8 GHz $\leq 8.0^\circ$, 8 GHz to 18 GHz

¹ The nominal phase is defined by the Offset Delay, the Offset Loss and the Fringing Capacitances.

Mechanical data

Mating cycles	≥ 500
Maximum torque	1.70 Nm
Recommended torque	0.55 Nm
Gauge	5.18 mm to 5.28 mm

General standard definitions

For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating.

Offset Z_o / Impedance / Z_o	50 Ω
Offset Delay	58.374 ps
Length (electrical) / Offset Length	17.50 mm
Offset Loss	1.20 G Ω /s
Loss	0.0122 dB/ $\sqrt{\text{GHz}}$
Fringing Capacitances ²	

² Fringing Capacitances are determined individually for each open circuit and are documented in a Calibration Certificate.

Environmental data

Operating temperature range ³	+20 °C to +26 °C
Rated temperature range of use ⁴	0 °C to +50 °C
Storage temperature range	- 40 °C to +85 °C

RoHS	compliant
------	-----------

³ Temperature range over which these specification are valid.

⁴ This range is underneath and above the operating temperature range, within the open circuit is fully functional and could be used without damage.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger			
RPC-TNC		Open Circuit Jack		06K12L-000S3			
Declaration of calibration options Factory Calibration Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results, traceable to Rosenberger standards, national / international standards are not available. Model based standard definitions are individually optimized and reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format. Accredited Calibration Not available. For further, more detailed information see application note AN001 on the Rosenberger homepage. Calibration interval Recommendation 12 months Packing Standard Weight 1 pce in box 40 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft		Date		Approved		Date	
Herbert Babinger		02.12.04		Markus Müller		22.04.16	
Rev.		Engineering change number		Name		Date	
c00		16-s067		Marcel Panicke		22.04.16	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de						Tel. : +49 8684 18-0 Email : info@rosenberger.de	
						Page	
						3 / 3	