

| REVISIONS |         |                                              |           |     |
|-----------|---------|----------------------------------------------|-----------|-----|
| REV.      | ECO. NO | DESCRIPTION                                  | DATE      | BY  |
| C         | 985     | REDRAW/REVISE. ALL AVAILABLE MOUNTINGS ADDED | 04/12/06  | MNH |
| D         | 1346    | ADDED METRIC DIMENSIONS, TABULATED MATERIALS | 06/29/07  | ASK |
| E         | 1810    | ADD HB TERMINATION, UPDATE LAYOUT            | 9/25/2008 | ASK |

PART NUMBER CODING

MATERIAL (INSULATOR/CONTACT)

E = BLACK, PBT/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 10 SECS MAX

R = BLACK, PPS/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

G = BLACK, PA9T/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

H = BLACK, PBT/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 10 SECS MAX

A = BLACK, PPS/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +150°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

J = BLACK, PA9T/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +150°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

(CONSULT FACTORY FOR OTHER MATERIALS)

MOUNTING STYLE

D = .250" EARS, FLUSH MOUNTING

N = NO MOUNTING EARS

A = SIDE MOUNTING WITH #4-40 THREADED INSERTS

R = NO MOUNTING EARS, WITH BOARD LOCKS

S = SIDE MOUNTING

T = .250" EARS, FLUSH MOUNTING WITH #4-40 THD INSERTS

TERMINATION TYPE

HA = .100" [2.54 mm] STAGGERED DIP SOLDER, .050" CENTERS

HB = .170" [4.32 mm] STAGGERED DIP SOLDER, .050" CENTERS

NUMBER OF POSITIONS

PLATING

ALL PLATINGS ARE LEAD FREE AND HAVE .000050" NICKEL UNDERPLATE

CONTACT SURFACE


B = .000010" GOLD

C = .000030" GOLD

TERMINATION

.000100" PURE TIN, MATTE

.000100" PURE TIN, MATTE



NOTES:

1. MATERIALS:

- A. INSULATOR: SEE PART NUMBER CODING.
- B. CONTACT: SEE PART NUMBER CODING.
- C. PLATING: SEE PART NUMBER CODING.

2. THERMAL:


- A. OPERATING TEMPERATURE: SEE PART NUMBER CODING.
- B. PROCESSING TEMP: SEE PART NUMBER CODING.
- C. UL FLAMMABILITY RATING: 94V-0.

3. ELECTRICAL:

- A. DIELECTRIC WITHSTANDING VOLTAGE: MATED CONNECTOR MUST EXHIBIT NO EVIDENCE OF BREAKDOWN, FLASHOVER, OR DETERIORATION FROM AN APPLIED VOLTAGE OF 300 VAC (VALUE HAS BEEN DE-RATED), RMS 60 Hz WHEN TESTED IN ACCORDANCE WITH MIL-STD-1344, METHOD 3001. DURATION OF APPLICATION SHALL BE 5 SECS MIN.
- B. INSULATION RESISTANCE (IR): 5,000 MEGOHMS @ 500 VOLTS ±10% WHEN TESTED IN ACCORDANCE WITH MIL-STD-1344, METHOD 3003 @ 25°C.
- C. CONTACT RESISTANCE: 30 MILLIOHM MAX AT RATED CURRENT WHEN TESTED PER MIL-STD-202, METHOD 307 @ 25°C ±3°C.
- D. CURRENT RATING: 1 AMP PER CONTACT.


4. MECHANICAL:


- A. CONNECTOR IDENTIFICATION: THE PART SHALL BE MARKED WITH A LOT CODE AS A MINIMUM. IF SPACE PERMITS ALSO MARK PART WITH SULLINS WEBSITE, AND PART NUMBER.
- B. DURABILITY: 500 CYCLES MINIMUM.
- C. BOARD THICKNESS ACCOMMODATED: .062 ±.008"
- D. BOARD INSERTION FORCE: 16 OZ MAX PER CONTACT PAIR WHEN USING A .062" TEST BLADE. INTERNAL INSPECTION TO BE PER SULLIN'S WORK INSTRUCTION W17.3-01.
- E. BOARD WITHDRAWAL FORCE: 1 OUNCE MINIMUM PER CONTACT PAIR USING .062" PCB.




RoHS COMPLIANT

CUSTOMER COPY

|                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                            |          |      |                                                                                                                                         |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| <p>UNLESS OTHERWISE SPECIFIED:</p> <p>DIMENSIONS ARE IN INCHES[MM]</p> <p>TOLERANCES:</p> <p>ANGULAR: ± 30°</p> <p>.XX=± .02 [.508]</p> <p>.XXX=± .005 [.1270]</p> <p>.XXXX=± .0005 [.0127]</p> <p>SURFACE FINISH: 63 Ra</p> <p>REMOVE ALL BURRS AND SHARP EDGES .010 MAX</p><br><p>INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING</p> <p>PER: ANSI Y14.5M-1994</p> |                                                                                                                                                                                                                                            | DATE     | NAME |  <div><b>SULLINS</b><br/>CONNECTOR SOLUTIONS</div> |                             |
|                                                                                                                                                                                                                                                                                                                                                                     | DRAWN                                                                                                                                                                                                                                      | 04/12/06 | MNH  |                                                                                                                                         |                             |
|                                                                                                                                                                                                                                                                                                                                                                     | THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS. |          |      | DESCRIPTION                                                                                                                             | EDGE CARD, .050 CC, RAB     |
|                                                                                                                                                                                                                                                                                                                                                                     |                                                                  |          |      | PART NUMBER                                                                                                                             | __ B __ D __ __, (DHA, DHB) |
|                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                            |          |      | SIZE                                                                                                                                    | DWG. NO.                    |
|                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                            |          | C    | C10091                                                                                                                                  | E                           |
| SCALE: 3:1                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                            |          |      | SHEET 1 OF 3                                                                                                                            |                             |




CUSTOMER COPY



RoHS COMPLIANT


|                                        |                    |              |
|----------------------------------------|--------------------|--------------|
|                                        |                    |              |
| DESCRIPTION<br>EDGE CARD, .050 CC, RAB |                    |              |
| PART NUMBER<br>\_B\_D\_ (DHA, DHB)     |                    |              |
| SIZE<br>C                              | DWG. NO.<br>C10091 | REV<br>E     |
| SCALE: 2:1                             |                    | SHEET 2 OF 3 |

| PART NUMBER | NO OF POSITIONS | A±.005[0.13] |        | B±.005[0.13] |        | C±.015[0.38] |        | D±.010[0.25]      |        | E±.020[0.51] |        | F±.010[0.25] |        |
|-------------|-----------------|--------------|--------|--------------|--------|--------------|--------|-------------------|--------|--------------|--------|--------------|--------|
|             |                 | IN           | MM     | IN           | MM     | IN           | MM     | IN                | MM     | IN           | MM     | IN           | MM     |
| __B05D__    | 5               | 0.200        | 5.08   | 0.300        | 7.62   | 0.490        | 12.45  | 0.776             | 19.71  | 1.090        | 27.69  | 0.350        | 8.89   |
| __B06D__    | 6               | 0.250        | 6.35   | 0.350        | 8.89   | 0.540        | 13.72  | 0.826             | 20.98  | 1.140        | 28.96  | 0.400        | 10.16  |
| __B09D__    | 9               | 0.400        | 10.16  | 0.500        | 12.70  | 0.690        | 17.53  | 0.976             | 24.79  | 1.290        | 32.77  | 0.550        | 13.97  |
| __B10D__    | 10              | 0.450        | 11.43  | 0.550        | 13.97  | 0.740        | 18.80  | 1.026             | 26.06  | 1.340        | 34.04  | 0.600        | 15.24  |
| __B13D__    | 13              | 0.600        | 15.24  | 0.700        | 17.78  | 0.890        | 22.61  | 1.176             | 29.87  | 1.490        | 37.85  | 0.750        | 19.05  |
| __B14D__    | 14              | 0.650        | 16.51  | 0.750        | 19.05  | 0.940        | 23.88  | 1.226             | 31.14  | 1.540        | 39.12  | 0.800        | 20.32  |
| __B15D__    | 15              | 0.700        | 17.78  | 0.800        | 20.32  | 0.990        | 25.15  | 1.276             | 32.41  | 1.590        | 40.39  | 0.850        | 21.59  |
| __B20D__    | 20              | 0.950        | 24.13  | 1.050        | 26.67  | 1.240        | 31.50  | 1.526             | 38.76  | 1.840        | 46.74  | 1.100        | 27.94  |
| __B22D__    | 22              | 1.050        | 26.67  | 1.150        | 29.21  | 1.340        | 34.04  | 1.626             | 41.30  | 1.940        | 49.28  | 1.200        | 30.48  |
| __B25D__    | 25              | 1.200        | 30.48  | 1.300        | 33.02  | 1.490        | 37.85  | 1.776             | 45.11  | 2.090        | 53.09  | 1.350        | 34.29  |
| __B30D__    | 30              | 1.450        | 36.83  | 1.550        | 39.37  | 1.740        | 44.20  | 2.026             | 51.46  | 2.340        | 59.44  | 1.600        | 40.64  |
| __B34D__    | 34              | 1.650        | 41.91  | 1.750        | 44.45  | 1.940        | 49.28  | 2.226             | 56.54  | 2.540        | 64.52  | 1.800        | 45.72  |
| __B35D__    | 35              | 1.700        | 43.18  | 1.800        | 45.72  | 1.990        | 50.55  | 2.276             | 57.81  | 2.590        | 65.79  | 1.850        | 46.99  |
| __B40D__    | 40              | 1.950        | 49.53  | 2.050        | 52.07  | 2.240        | 56.90  | 2.526             | 64.16  | 2.840        | 72.14  | 2.100        | 53.34  |
| __B45D__    | 45              | 2.200        | 55.88  | 2.300        | 58.42  | 2.490        | 63.25  | 2.776             | 70.51  | 3.090        | 78.49  | 2.350        | 59.69  |
| __B50D__    | 50              | 2.450        | 62.23  | 2.550        | 64.77  | 2.740        | 69.60  | 3.026             | 76.86  | 3.340        | 84.84  | 2.600        | 66.04  |
| __B55D__    | 55              | 2.700        | 68.58  | 2.800        | 71.12  | 2.990        | 75.95  | 3.276             | 83.21  | 3.590        | 91.19  | 2.850        | 72.39  |
| __B60D__    | 60              | 2.950        | 74.93  | 3.050        | 77.47  | 3.240        | 82.30  | 3.526             | 89.56  | 3.840        | 97.54  | 3.100        | 78.74  |
| __B64D__    | 64              | 3.150        | 80.01  | 3.250        | 82.55  | 3.440        | 87.38  | 3.726             | 94.64  | 4.040        | 102.62 | 3.300        | 83.82  |
| __B65D__    | 65              | 3.200        | 81.28  | 3.300        | 83.82  | 3.490        | 88.65  | 3.776             | 95.91  | 4.090        | 103.89 | 3.350        | 85.09  |
| __B66D__    | 66              | 3.250        | 82.55  | 3.350        | 85.09  | 3.540        | 89.92  | 3.826             | 97.18  | 4.140        | 105.16 | 3.400        | 86.36  |
| __B70D__    | 70              | 3.450        | 87.63  | 3.550        | 90.17  | 3.740        | 95.00  | 4.026             | 102.26 | 4.340        | 110.24 | 3.600        | 91.44  |
| __B75D__    | 75              | 3.700        | 93.98  | 3.800        | 96.52  | 3.990        | 101.35 | 4.276             | 108.61 | 4.590        | 116.59 | 3.850        | 97.79  |
| __B80D__    | 80              | 3.950        | 100.33 | 4.050        | 102.87 | 4.240        | 107.70 | 4.526             | 114.96 | 4.840        | 122.94 | 4.100        | 104.14 |
| __B85D__    | 85              | 4.200        | 106.68 | 4.300        | 109.22 | 4.490        | 114.05 | 4.776             | 121.31 | 5.090        | 129.29 | 4.350        | 110.49 |
| __B90D__    | 90              | 4.450        | 113.03 | 4.550        | 115.57 | 4.740        | 120.40 | 5.026             | 127.66 | 5.340        | 135.64 | 4.600        | 116.84 |
| __B95D__    | 95              | 4.700        | 119.38 | 4.800        | 121.92 | 4.990        | 126.75 | 5.276             | 134.01 | 5.590        | 141.99 | 4.850        | 123.19 |
| __B100D__   | 100             | 4.950        | 125.73 | 5.050        | 128.27 | 5.240        | 133.10 | 5.526             | 140.36 | 5.840        | 148.34 | 5.100        | 129.54 |
| __B105D__   | 105             | 5.200        | 132.08 | 5.300        | 134.62 | 5.490        | 139.45 | 5.776             | 146.71 | 6.090        | 154.69 | 5.350        | 135.89 |
| __B108D__   | 108             | 5.350        | 135.89 | 5.450        | 138.43 | 5.640        | 143.26 | 5.926             | 150.52 | 6.240        | 158.50 | 5.500        | 139.70 |
| __B110D__   | 110             | 5.450        | 138.43 | 5.550        | 140.97 | 5.740        | 145.80 | 6.026             | 153.06 | 6.340        | 161.04 | 5.600        | 142.24 |
| __B120D__   | 120             | 5.950        | 151.13 | 6.050        | 153.67 | 6.240        | 158.50 | "N" MOUNTING ONLY |        |              |        | 6.100        | 154.94 |




\_\_B\_\_D\_\_S

2X # 4-40  
THREADED INSERTS




\_\_B\_\_D\_\_T

MOUNTING STYLES



CUSTOMER COPY



RoHS COMPLIANT

|                                        |                    |              |
|----------------------------------------|--------------------|--------------|
|                                        |                    |              |
| DESCRIPTION<br>EDGE CARD, .050 CC, RAB |                    |              |
| PART NUMBER<br>__B__D__, (DHA, DHB)    |                    |              |
| SIZE<br>C                              | DWG. NO.<br>C10091 | REV<br>E     |
| SCALE: 4:1                             |                    | SHEET 3 OF 3 |