

## KYB Series

- Low impedance, high ripple and long life from KYA series
- Newly innovative electrolyte is employed to minimize impedance
- Endurance with ripple current : 4,000 to 10,000 hours at 105°C
- Non solvent resistant type
- RoHS Compliant

KYB  
↑  
Lower Z  
KYA P150




### SPECIFICATIONS

| Items                                                  | Characteristics                                                                                                                                                                                                                                                                       |                                                           |      |      |      |      |      |      |                                                            |      |  |
|--------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------|------|------|------|------|------|------|------------------------------------------------------------|------|--|
| Category                                               | Temperature Range                                                                                                                                                                                                                                                                     |                                                           |      |      |      |      |      |      |                                                            |      |  |
| Rated Voltage Range                                    | -40 to +105°C                                                                                                                                                                                                                                                                         |                                                           |      |      |      |      |      |      |                                                            |      |  |
| Capacitance Tolerance                                  | ±20% (M) (at 20°C, 120Hz)                                                                                                                                                                                                                                                             |                                                           |      |      |      |      |      |      |                                                            |      |  |
| Leakage Current                                        | I=0.01CV or 3μA, whichever is greater.<br>Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20°C after 2 minutes)                                                                                                                         |                                                           |      |      |      |      |      |      |                                                            |      |  |
| Dissipation Factor (tan δ)                             | Rated voltage (V <sub>dc</sub> )                                                                                                                                                                                                                                                      | 6.3V                                                      | 10V  | 16V  | 25V  | 35V  | 50V  | 63V  | 80V                                                        | 100V |  |
|                                                        | tan δ (Max)                                                                                                                                                                                                                                                                           | 0.22                                                      | 0.19 | 0.16 | 0.14 | 0.12 | 0.10 | 0.09 | 0.09                                                       | 0.08 |  |
|                                                        | When nominal capacitance exceeds 1,000μF, add 0.02 to the value above for each 1,000μF increase. (at 20°C, 120Hz)                                                                                                                                                                     |                                                           |      |      |      |      |      |      |                                                            |      |  |
| Low Temperature Characteristics (Max. Impedance Ratio) | Rated voltage (V <sub>dc</sub> )                                                                                                                                                                                                                                                      | 6.3V                                                      | 10V  | 16V  | 25V  | 35V  | 50V  | 63V  | 80V                                                        | 100V |  |
|                                                        | Z(-25°C)/Z(+20°C)                                                                                                                                                                                                                                                                     | 4                                                         | 3    | 2    | 2    | 2    | 2    | 2    | 2                                                          | 2    |  |
|                                                        | Z(-40°C)/Z(+20°C)                                                                                                                                                                                                                                                                     | 8                                                         | 6    | 4    | 3    | 3    | 3    | 3    | 3                                                          | 3    |  |
| Endurance                                              | The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for the specified period of time at 105°C.                      |                                                           |      |      |      |      |      |      |                                                            |      |  |
|                                                        | Rated Voltage(V <sub>dc</sub> )                                                                                                                                                                                                                                                       | 6.3 to 10V <sub>dc</sub>                                  |      |      |      |      |      |      | 16 to 100V <sub>dc</sub>                                   |      |  |
|                                                        | Time                                                                                                                                                                                                                                                                                  | φ5: 4,000hours φ6.3 & 8: 6,000hours φ10 to 18: 8,000hours |      |      |      |      |      |      | φ5: 5,000hours φ6.3 & 8: 7,000hours φ10 to 18: 10,000hours |      |  |
|                                                        | Capacitance change                                                                                                                                                                                                                                                                    | ≤±30% of the initial value                                |      |      |      |      |      |      | ≤±25% of the initial value                                 |      |  |
|                                                        | D.F. (tan δ)                                                                                                                                                                                                                                                                          | ≤200% of the initial specified value                      |      |      |      |      |      |      | ≤200% of the initial specified value                       |      |  |
|                                                        | Leakage current                                                                                                                                                                                                                                                                       | ≤The initial specified value                              |      |      |      |      |      |      | ≤The initial specified value                               |      |  |
| Shelf Life                                             | The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 500 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4. |                                                           |      |      |      |      |      |      |                                                            |      |  |
|                                                        | Capacitance change                                                                                                                                                                                                                                                                    | ≤±25% of the initial value                                |      |      |      |      |      |      |                                                            |      |  |
|                                                        | D.F. (tan δ)                                                                                                                                                                                                                                                                          | ≤200% of the initial specified value                      |      |      |      |      |      |      |                                                            |      |  |
|                                                        | Leakage current                                                                                                                                                                                                                                                                       | ≤The initial specified value                              |      |      |      |      |      |      |                                                            |      |  |


### DIMENSIONS [mm]

- Terminal Code : E



| φD  | 5          | 6.3 | 8   | 10  | 12.5 | 16  | 18  |
|-----|------------|-----|-----|-----|------|-----|-----|
| φd  | 0.5        | 0.5 | 0.6 | 0.6 | 0.6  | 0.8 | 0.8 |
| F   | 2.0        | 2.5 | 3.5 | 5.0 | 5.0  | 7.5 | 7.5 |
| φD' | φD+0.5max. |     |     |     |      |     |     |
| L'  | L+1.5max.  |     |     |     |      |     |     |

### PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"

## ◆STANDARD RATINGS

| WV<br>(Vdc) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ωmax/100kHz) |       | Rated<br>ripple<br>current<br>(mA rms/<br>105°C,<br>100kHz) | Part No.           |
|-------------|-------------|-----------------------|----------------------------|-------|-------------------------------------------------------------|--------------------|
|             |             |                       | 20°C                       | -10°C |                                                             |                    |
| 6.3         | 180         | 5×11                  | 0.29                       | 1.2   | 340                                                         | EKYB6R3E□□181ME11D |
|             | 390         | 6.3×11                | 0.15                       | 0.60  | 540                                                         | EKYB6R3E□□391MF11D |
|             | 820         | 8×11.5                | 0.087                      | 0.35  | 840                                                         | EKYB6R3E□□821MHB5D |
|             | 1,200       | 8×15                  | 0.069                      | 0.28  | 1,050                                                       | EKYB6R3E□□122MH15D |
|             | 1,200       | 10×12.5               | 0.064                      | 0.26  | 1,050                                                       | EKYB6R3E□□122MJC5S |
|             | 1,500       | 8×20                  | 0.060                      | 0.24  | 1,210                                                       | EKYB6R3E□□152MH20D |
|             | 1,800       | 10×16                 | 0.049                      | 0.20  | 1,400                                                       | EKYB6R3E□□182MJ16S |
|             | 2,200       | 10×20                 | 0.037                      | 0.15  | 1,650                                                       | EKYB6R3E□□222MJ20S |
|             | 2,700       | 10×25                 | 0.031                      | 0.13  | 1,910                                                       | EKYB6R3E□□272MJ25S |
|             | 3,300       | 10×30                 | 0.027                      | 0.11  | 2,230                                                       | EKYB6R3E□□332MJ30S |
|             | 3,900       | 12.5×20               | 0.027                      | 0.11  | 2,230                                                       | EKYB6R3E□□392MK20S |
|             | 4,700       | 12.5×25               | 0.024                      | 0.096 | 2,530                                                       | EKYB6R3E□□472MK25S |
|             | 6,800       | 12.5×30               | 0.021                      | 0.084 | 2,860                                                       | EKYB6R3E□□682MK30S |
|             | 6,800       | 16×20                 | 0.025                      | 0.10  | 2,610                                                       | EKYB6R3E□□682ML20S |
|             | 8,200       | 12.5×35               | 0.018                      | 0.072 | 3,140                                                       | EKYB6R3E□□822MK35S |
|             | 8,200       | 18×20                 | 0.021                      | 0.084 | 3,000                                                       | EKYB6R3E□□822MM20S |
|             | 10,000      | 12.5×40               | 0.017                      | 0.068 | 3,640                                                       | EKYB6R3E□□103MK40S |
|             | 10,000      | 16×25                 | 0.020                      | 0.080 | 3,140                                                       | EKYB6R3E□□103ML25S |
|             | 12,000      | 16×31.5               | 0.016                      | 0.064 | 3,610                                                       | EKYB6R3E□□123MLN3S |
|             | 12,000      | 18×25                 | 0.017                      | 0.068 | 3,530                                                       | EKYB6R3E□□123MM25S |
|             | 15,000      | 16×35.5               | 0.014                      | 0.056 | 4,080                                                       | EKYB6R3E□□153MLP1S |
| 10          | 15,000      | 18×31.5               | 0.014                      | 0.056 | 4,220                                                       | EKYB6R3E□□153MMN3S |
|             | 18,000      | 16×40                 | 0.013                      | 0.052 | 4,220                                                       | EKYB6R3E□□183ML40S |
|             | 18,000      | 18×35.5               | 0.012                      | 0.048 | 4,280                                                       | EKYB6R3E□□183MMP1S |
|             | 22,000      | 18×40                 | 0.011                      | 0.044 | 4,700                                                       | EKYB6R3E□□223MM40S |
|             | 120         | 5×11                  | 0.29                       | 1.2   | 340                                                         | EKYB100E□□121ME11D |
|             | 330         | 6.3×11                | 0.15                       | 0.60  | 540                                                         | EKYB100E□□331MF11D |
|             | 560         | 8×11.5                | 0.087                      | 0.35  | 840                                                         | EKYB100E□□561MHB5D |
|             | 820         | 8×15                  | 0.069                      | 0.28  | 1,050                                                       | EKYB100E□□821MH15D |
|             | 1,000       | 8×20                  | 0.060                      | 0.24  | 1,210                                                       | EKYB100E□□102MH20D |
|             | 1,000       | 10×12.5               | 0.064                      | 0.26  | 1,050                                                       | EKYB100E□□102MJC5S |
|             | 1,200       | 10×16                 | 0.049                      | 0.20  | 1,400                                                       | EKYB100E□□122MJ16S |
|             | 1,800       | 10×20                 | 0.037                      | 0.15  | 1,650                                                       | EKYB100E□□182MJ20S |
|             | 2,200       | 10×25                 | 0.031                      | 0.13  | 1,910                                                       | EKYB100E□□222MJ25S |
|             | 2,700       | 10×30                 | 0.027                      | 0.11  | 2,230                                                       | EKYB100E□□272MJ30S |
|             | 2,700       | 12.5×20               | 0.027                      | 0.11  | 2,230                                                       | EKYB100E□□272MK20S |
|             | 3,900       | 12.5×25               | 0.024                      | 0.096 | 2,530                                                       | EKYB100E□□392MK25S |
|             | 4,700       | 12.5×30               | 0.021                      | 0.084 | 2,860                                                       | EKYB100E□□472MK30S |
|             | 4,700       | 16×20                 | 0.025                      | 0.10  | 2,610                                                       | EKYB100E□□472ML20S |
|             | 5,600       | 12.5×35               | 0.018                      | 0.072 | 3,140                                                       | EKYB100E□□562MK35S |
|             | 6,800       | 12.5×40               | 0.017                      | 0.068 | 3,640                                                       | EKYB100E□□682MK40S |
| 16          | 6,800       | 16×25                 | 0.020                      | 0.080 | 3,140                                                       | EKYB100E□□682ML25S |
|             | 6,800       | 18×20                 | 0.021                      | 0.084 | 3,000                                                       | EKYB100E□□682MM20S |
|             | 8,200       | 16×31.5               | 0.016                      | 0.064 | 3,610                                                       | EKYB100E□□822MLN3S |
|             | 8,200       | 18×25                 | 0.017                      | 0.068 | 3,530                                                       | EKYB100E□□822MM25S |
|             | 10,000      | 16×35.5               | 0.014                      | 0.056 | 4,080                                                       | EKYB100E□□103MLP1S |
|             | 10,000      | 18×31.5               | 0.014                      | 0.056 | 4,220                                                       | EKYB100E□□103MMN3S |
|             | 12,000      | 16×40                 | 0.013                      | 0.052 | 4,220                                                       | EKYB100E□□123ML40S |
|             | 12,000      | 18×35.5               | 0.012                      | 0.048 | 4,280                                                       | EKYB100E□□123MMP1S |
|             | 15,000      | 18×40                 | 0.011                      | 0.044 | 4,700                                                       | EKYB100E□□153MM40S |
|             | 120         | 5×11                  | 0.29                       | 1.2   | 340                                                         | EKYB160E□□121ME11D |
|             | 270         | 6.3×11                | 0.15                       | 0.60  | 540                                                         | EKYB160E□□271MF11D |
|             | 470         | 8×11.5                | 0.087                      | 0.35  | 840                                                         | EKYB160E□□471MHB5D |
|             | 680         | 8×15                  | 0.069                      | 0.28  | 1,050                                                       | EKYB160E□□681MH15D |
|             | 680         | 10×12.5               | 0.064                      | 0.26  | 1,050                                                       | EKYB160E□□681MJC5S |
|             | 820         | 8×20                  | 0.060                      | 0.24  | 1,210                                                       | EKYB160E□□821MH20D |
|             | 1,000       | 10×16                 | 0.049                      | 0.20  | 1,400                                                       | EKYB160E□□102MJ16S |
|             | 1,500       | 10×20                 | 0.037                      | 0.15  | 1,650                                                       | EKYB160E□□152MJ20S |
|             | 1,800       | 10×25                 | 0.031                      | 0.13  | 1,910                                                       | EKYB160E□□182MJ25S |
|             | 2,200       | 10×30                 | 0.027                      | 0.11  | 2,230                                                       | EKYB160E□□222MJ30S |
|             | 2,200       | 12.5×20               | 0.027                      | 0.11  | 2,230                                                       | EKYB160E□□222MK20S |
|             | 3,300       | 12.5×25               | 0.024                      | 0.096 | 2,530                                                       | EKYB160E□□332MK25S |
| 25          | 3,900       | 12.5×30               | 0.021                      | 0.084 | 2,860                                                       | EKYB160E□□392MK30S |
|             | 4,700       | 16×20                 | 0.025                      | 0.10  | 2,610                                                       | EKYB160E□□472ML20S |
|             | 5,600       | 12.5×35               | 0.018                      | 0.072 | 3,140                                                       | EKYB160E□□562MK35S |
|             | 6,800       | 12.5×40               | 0.017                      | 0.068 | 3,640                                                       | EKYB160E□□682MK40S |
|             | 6,800       | 16×25                 | 0.020                      | 0.080 | 3,140                                                       | EKYB160E□□682ML25S |
|             | 6,800       | 18×20                 | 0.021                      | 0.084 | 3,000                                                       | EKYB160E□□682MM20S |
|             | 8,200       | 16×31.5               | 0.016                      | 0.064 | 3,610                                                       | EKYB160E□□822MLN3S |
|             | 8,200       | 18×25                 | 0.017                      | 0.068 | 3,530                                                       | EKYB160E□□822MM25S |
|             | 10,000      | 16×35.5               | 0.014                      | 0.056 | 4,080                                                       | EKYB160E□□103MLP1S |
|             | 10,000      | 18×31.5               | 0.014                      | 0.056 | 4,220                                                       | EKYB160E□□103MMN3S |
|             | 12,000      | 16×40                 | 0.013                      | 0.052 | 4,220                                                       | EKYB160E□□123ML40S |
|             | 12,000      | 18×35.5               | 0.012                      | 0.048 | 4,280                                                       | EKYB160E□□123MMP1S |
|             | 15,000      | 18×40                 | 0.011                      | 0.044 | 4,700                                                       | EKYB160E□□153MM40S |
|             | 470         | 5×11                  | 0.29                       | 1.2   | 340                                                         | EKYB250E□□470ME11D |
|             | 100         | 6.3×11                | 0.15                       | 0.60  | 540                                                         | EKYB250E□□101MF11D |
|             | 180         | 8×11.5                | 0.087                      | 0.35  | 840                                                         | EKYB250E□□181MHB5D |
|             | 270         | 8×15                  | 0.069                      | 0.28  | 1,050                                                       | EKYB250E□□271MH15D |
|             | 330         | 8×20                  | 0.060                      | 0.24  | 1,210                                                       | EKYB250E□□331MH20D |
|             | 330         | 10×12.5               | 0.064                      | 0.26  | 1,050                                                       | EKYB250E□□331MJC5S |
| 35          | 470         | 10×16                 | 0.049                      | 0.20  | 1,400                                                       | EKYB250E□□471MJ16S |
|             | 680         | 10×20                 | 0.037                      | 0.15  | 1,650                                                       | EKYB250E□□681MJ20S |
|             | 820         | 10×25                 | 0.031                      | 0.13  | 1,910                                                       | EKYB250E□□821MJ25S |
|             | 1,000       | 10×30                 | 0.027                      | 0.11  | 2,230                                                       | EKYB250E□□102MJ30S |
|             | 1,000       | 12.5×20               | 0.027                      | 0.11  | 2,230                                                       | EKYB250E□□102MK20S |
|             | 1,500       | 12.5×25               | 0.024                      | 0.096 | 2,530                                                       | EKYB250E□□152MK25S |
|             | 1,800       | 12.5×30               | 0.021                      | 0.084 | 2,860                                                       | EKYB250E□□182MK30S |
|             | 1,800       | 16×20                 | 0.025                      | 0.10  | 2,610                                                       | EKYB250E□□182ML20S |
|             | 2,200       | 12.5×35               | 0.018                      | 0.072 | 3,140                                                       | EKYB250E□□222MK35S |
|             | 2,200       | 18×20                 | 0.021                      | 0.084 | 3,000                                                       | EKYB250E□□222MM20S |
|             | 2,700       | 12.5×40               | 0.017                      | 0.068 | 3,640                                                       | EKYB250E□□272MK40S |
|             | 2,700       | 16×25                 | 0.020                      | 0.080 | 3,140                                                       | EKYB250E□□272ML25S |
|             | 3,300       | 16×31.5               | 0.016                      | 0.064 | 3,610                                                       | EKYB250E□□332MLN3S |
|             | 3,300       | 18×25                 | 0.017                      | 0.068 | 3,530                                                       | EKYB250E□□332MM25S |
|             | 3,900       | 16×35.5               | 0.014                      | 0.056 | 4,080                                                       | EKYB250E□□392MLP1S |
|             | 4,700       | 16×40                 | 0.013                      | 0.052 | 4,220                                                       | EKYB250E□□472ML40S |
|             | 4,700       | 18×31.5               | 0.014                      | 0.056 | 4,220                                                       | EKYB250E□□472MMN3S |
|             | 5,600       | 18×35.5               | 0.012                      | 0.048 | 4,280                                                       | EKYB250E□□562MMP1S |
|             | 27          | 5×11                  | 0.48                       | 2.0   | 238                                                         | EKYB500E□□270ME11D |
| 50          | 56          | 6.3×11                | 0.20                       | 0.80  | 385                                                         | EKYB500E□□560MF11D |
|             | 100         | 8×11.5                | 0.12                       | 0.48  | 620                                                         | EKYB500E□□101MHB5D |
|             | 150         | 8×15                  | 0.093                      | 0.38  | 810                                                         | EKYB500E□□151MH15D |
|             | 150         | 10×12.5               | 0.10                       | 0.40  | 810                                                         | EKYB500E□□151MJC5S |

□□ : Enter the appropriate lead forming or taping code.

## ◆STANDARD RATINGS

| WV<br>(Vdc) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ωmax/100kHz) |       | Rated<br>ripple<br>current<br>(mA <sub>rms</sub> /105°C,<br>100kHz) | Part No.           |
|-------------|-------------|-----------------------|----------------------------|-------|---------------------------------------------------------------------|--------------------|
|             |             |                       | 20°C                       | -10°C |                                                                     |                    |
| 50          | 180         | 8×20                  | 0.075                      | 0.30  | 980                                                                 | EKYB500E□□181MH20D |
|             | 220         | 10×16                 | 0.069                      | 0.28  | 1,100                                                               | EKYB500E□□221MJ16S |
|             | 270         | 10×20                 | 0.055                      | 0.22  | 1,300                                                               | EKYB500E□□271MJ20S |
|             | 390         | 10×25                 | 0.043                      | 0.18  | 1,600                                                               | EKYB500E□□391MJ25S |
|             | 470         | 10×30                 | 0.038                      | 0.16  | 1,820                                                               | EKYB500E□□471MJ30S |
|             | 470         | 12.5×20               | 0.034                      | 0.14  | 1,820                                                               | EKYB500E□□471MK20S |
|             | 680         | 12.5×25               | 0.030                      | 0.12  | 2,100                                                               | EKYB500E□□681MK25S |
|             | 820         | 12.5×30               | 0.025                      | 0.10  | 2,450                                                               | EKYB500E□□821MK30S |
|             | 820         | 16×20                 | 0.028                      | 0.12  | 2,350                                                               | EKYB500E□□821ML20S |
|             | 1,000       | 12.5×35               | 0.021                      | 0.084 | 2,800                                                               | EKYB500E□□102MK35S |
|             | 1,000       | 18×20                 | 0.025                      | 0.10  | 2,600                                                               | EKYB500E□□102MM20S |
|             | 1,200       | 12.5×40               | 0.019                      | 0.076 | 3,100                                                               | EKYB500E□□122MK40S |
|             | 1,200       | 16×25                 | 0.024                      | 0.096 | 2,750                                                               | EKYB500E□□122ML25S |
|             | 1,500       | 16×31.5               | 0.019                      | 0.076 | 3,150                                                               | EKYB500E□□152MLN3S |
|             | 1,500       | 18×25                 | 0.021                      | 0.084 | 2,890                                                               | EKYB500E□□152MM25S |
|             | 1,800       | 16×35.5               | 0.016                      | 0.064 | 3,550                                                               | EKYB500E□□182MLP1S |
|             | 2,200       | 16×40                 | 0.014                      | 0.056 | 3,900                                                               | EKYB500E□□222ML40S |
|             | 2,200       | 18×31.5               | 0.014                      | 0.056 | 3,800                                                               | EKYB500E□□222MMN3S |
|             | 2,700       | 18×35.5               | 0.013                      | 0.052 | 4,100                                                               | EKYB500E□□272MMP1S |
| 63          | 18          | 5×11                  | 0.50                       | 2.0   | 220                                                                 | EKYB630E□□180ME11D |
|             | 33          | 6.3×11                | 0.25                       | 1.0   | 350                                                                 | EKYB630E□□330MF11D |
|             | 56          | 8×11.5                | 0.16                       | 0.64  | 530                                                                 | EKYB630E□□560MHB5D |
|             | 82          | 8×15                  | 0.12                       | 0.48  | 700                                                                 | EKYB630E□□820MH15D |
|             | 120         | 8×20                  | 0.085                      | 0.34  | 880                                                                 | EKYB630E□□121MH20D |
|             | 120         | 10×12.5               | 0.11                       | 0.44  | 725                                                                 | EKYB630E□□121MJC5S |
|             | 180         | 10×16                 | 0.073                      | 0.30  | 1,050                                                               | EKYB630E□□181MJ16S |
|             | 220         | 10×20                 | 0.055                      | 0.22  | 1,300                                                               | EKYB630E□□221MJ20S |
|             | 330         | 10×25                 | 0.045                      | 0.18  | 1,550                                                               | EKYB630E□□331MJ25S |
|             | 390         | 10×30                 | 0.040                      | 0.16  | 1,780                                                               | EKYB630E□□391MJ30S |
|             | 390         | 12.5×20               | 0.036                      | 0.15  | 1,780                                                               | EKYB630E□□391MK20S |
|             | 560         | 12.5×25               | 0.030                      | 0.12  | 2,100                                                               | EKYB630E□□561MK25S |
|             | 680         | 12.5×30               | 0.026                      | 0.11  | 2,415                                                               | EKYB630E□□681MK30S |
|             | 680         | 16×20                 | 0.028                      | 0.12  | 2,250                                                               | EKYB630E□□681ML20S |
|             | 820         | 12.5×35               | 0.022                      | 0.088 | 2,700                                                               | EKYB630E□□821MK35S |
|             | 820         | 18×20                 | 0.028                      | 0.12  | 2,500                                                               | EKYB630E□□821MM20S |
|             | 1,000       | 12.5×40               | 0.020                      | 0.080 | 3,000                                                               | EKYB630E□□102MK40S |
|             | 1,000       | 16×25                 | 0.025                      | 0.10  | 2,730                                                               | EKYB630E□□102ML25S |
|             | 1,200       | 16×31.5               | 0.020                      | 0.080 | 3,000                                                               | EKYB630E□□122MLN3S |
|             | 1,200       | 18×25                 | 0.022                      | 0.088 | 2,800                                                               | EKYB630E□□122MM25S |
| 80          | 12          | 5×11                  | 0.80                       | 3.2   | 163                                                                 | EKYB800E□□120ME11D |
|             | 22          | 6.3×11                | 0.43                       | 1.8   | 267                                                                 | EKYB800E□□220MF11D |
|             | 39          | 8×11.5                | 0.18                       | 0.72  | 462                                                                 | EKYB800E□□390MHB5D |
|             | 56          | 8×20                  | 0.11                       | 0.44  | 735                                                                 | EKYB800E□□560MH20D |
|             | 56          | 10×12.5               | 0.14                       | 0.56  | 624                                                                 | EKYB800E□□560MJC5S |
|             | 82          | 10×16                 | 0.10                       | 0.40  | 780                                                                 | EKYB800E□□820MJ16S |
|             | 100         | 10×20                 | 0.075                      | 0.30  | 1,040                                                               | EKYB800E□□101MJ20S |
|             | 120         | 10×25                 | 0.060                      | 0.24  | 1,170                                                               | EKYB800E□□121MJ25S |
|             | 150         | 10×30                 | 0.053                      | 0.22  | 1,350                                                               | EKYB800E□□151MJ30S |
|             | 180         | 12.5×20               | 0.048                      | 0.20  | 1,430                                                               | EKYB800E□□181MK20S |
|             | 220         | 12.5×25               | 0.039                      | 0.16  | 1,620                                                               | EKYB800E□□221MK25S |
|             | 270         | 12.5×30               | 0.033                      | 0.14  | 1,950                                                               | EKYB800E□□271MK30S |
|             | 270         | 16×20                 | 0.036                      | 0.15  | 1,750                                                               | EKYB800E□□271ML20S |
|             | 330         | 16×25                 | 0.028                      | 0.12  | 2,250                                                               | EKYB800E□□331ML25S |
|             | 390         | 12.5×35               | 0.026                      | 0.11  | 2,250                                                               | EKYB800E□□391MK35S |
|             | 390         | 18×20                 | 0.032                      | 0.13  | 2,100                                                               | EKYB800E□□391MM20S |
|             | 470         | 12.5×40               | 0.024                      | 0.096 | 2,450                                                               | EKYB800E□□471MK40S |
|             | 470         | 16×31.5               | 0.022                      | 0.088 | 2,400                                                               | EKYB800E□□471MLN3S |
|             | 560         | 16×35.5               | 0.020                      | 0.080 | 2,600                                                               | EKYB800E□□561MLP1S |
|             | 560         | 18×25                 | 0.027                      | 0.11  | 2,270                                                               | EKYB800E□□561MM25S |
| 100         | 6.8         | 5×11                  | 0.80                       | 3.2   | 163                                                                 | EKYB101E□□6R8ME11D |
|             | 15          | 6.3×11                | 0.43                       | 1.8   | 267                                                                 | EKYB101E□□150MF11D |
|             | 27          | 8×11.5                | 0.18                       | 0.72  | 462                                                                 | EKYB101E□□270MHB5D |
|             | 39          | 8×15                  | 0.14                       | 0.56  | 585                                                                 | EKYB101E□□390MH15D |
|             | 56          | 8×20                  | 0.11                       | 0.44  | 735                                                                 | EKYB101E□□560MH20D |
|             | 56          | 10×12.5               | 0.14                       | 0.56  | 624                                                                 | EKYB101E□□560MJC5S |
|             | 82          | 10×16                 | 0.10                       | 0.40  | 780                                                                 | EKYB101E□□820MJ16S |
|             | 100         | 10×20                 | 0.075                      | 0.30  | 1,040                                                               | EKYB101E□□101MJ20S |
|             | 120         | 10×25                 | 0.060                      | 0.24  | 1,170                                                               | EKYB101E□□121MJ25S |
|             | 150         | 10×30                 | 0.053                      | 0.22  | 1,350                                                               | EKYB101E□□151MJ30S |
|             | 180         | 12.5×20               | 0.048                      | 0.20  | 1,430                                                               | EKYB101E□□181MK20S |
|             | 220         | 12.5×25               | 0.039                      | 0.16  | 1,620                                                               | EKYB101E□□221MK25S |
|             | 270         | 12.5×30               | 0.033                      | 0.14  | 1,950                                                               | EKYB101E□□271MK30S |
|             | 270         | 16×20                 | 0.036                      | 0.15  | 1,750                                                               | EKYB101E□□271ML20S |
|             | 330         | 16×25                 | 0.028                      | 0.12  | 2,250                                                               | EKYB101E□□331ML25S |
|             | 390         | 12.5×35               | 0.026                      | 0.11  | 2,250                                                               | EKYB101E□□391MK35S |
|             | 390         | 18×20                 | 0.032                      | 0.13  | 2,100                                                               | EKYB101E□□391MM20S |
|             | 470         | 12.5×40               | 0.024                      | 0.096 | 2,450                                                               | EKYB101E□□471MK40S |
|             | 470         | 16×31.5               | 0.022                      | 0.088 | 2,400                                                               | EKYB101E□□471MLN3S |
|             | 560         | 16×35.5               | 0.020                      | 0.080 | 2,600                                                               | EKYB101E□□561MLP1S |
|             | 560         | 18×25                 | 0.027                      | 0.11  | 2,270                                                               | EKYB101E□□561MM25S |
|             | 680         | 16×40                 | 0.018                      | 0.072 | 2,900                                                               | EKYB101E□□681ML40S |
|             | 680         | 18×31.5               | 0.020                      | 0.080 | 2,550                                                               | EKYB101E□□681MMN3S |
|             | 820         | 18×35.5               | 0.018                      | 0.072 | 3,050                                                               | EKYB101E□□821MMP1S |
|             | 1,000       | 18×40                 | 0.017                      | 0.068 | 3,510                                                               | EKYB101E□□102MM40S |

□□ : Enter the appropriate lead forming or taping code.

## ◆RATED RIPPLE CURRENT MULTIPLIERS

## ●Frequency Multipliers

| Capacitance (μF) | Frequency (Hz) |      |      |      |
|------------------|----------------|------|------|------|
|                  | 120            | 1k   | 10k  | 100k |
| 6.8 to 180       | 0.40           | 0.75 | 0.90 | 1.00 |
| 220 to 560       | 0.50           | 0.85 | 0.94 | 1.00 |
| 680 to 1,800     | 0.60           | 0.87 | 0.95 | 1.00 |
| 2,200 to 3,900   | 0.75           | 0.90 | 0.95 | 1.00 |
| 4,700 to         | 0.85           | 0.95 | 0.98 | 1.00 |

The endurance of capacitors is reduced with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise. When long life performance is required in actual use, the rms ripple current has to be reduced.