

f

PLATING

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
- 4 = 2µm TIN MIN FULL PLATED
- 5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
- 8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
- G = 0.76µm FULL GXT
- S = 0.38µm FULL GXT
- T = 2µm TIN MIN FULL PLATED INCLUDED PIN TYP
 - 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS


RETENTION FEATURES :

- PART NUMBER 77311-XXXXXXLF: DIM "Z"=(0.99)
PART NUMBER 77311-XXXCXXLF: DIM "Z"= 1.05MIN -1.15MAX
- PINS "A" AND "B" USED FOR RETENTION.
- DIRECTION OF RETENTION SHOWN BY ARROWS.
- ON 4 TO 36 POSITIONS HEADER; RETENTION IS IN MID POSITION OF HEADER (4 CENTRAL PINS)
- FOR RETENTION OPTION , SOLDER TAIL LENGTH TO BE 2.9 MIN UP TO 3.5 MAX.
- HOUSING MATERIAL FOR P/N 77311-4AJC03LF & 77311-TAJC03LF HIGH TEMPERATURE THERMOPLASTIC UL94V-0 COLOR : NATURAL

PLATING SPECIFICATIONS :

- ONLY FOR PLATING 1XX, 8.0MM GOLD / GXT PLATING AREA FROM PIN TYPE ON MATING SIDE

RETENTION FEATURES



mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK				
ltr	ecn no	dr	date	tolerances unless otherwise specified					title					
BU	B-20596	AMA	15.03.30	angles	linear					UNSHR.HEADER STR SR TMT				
BV	F-22085	LMU	15.10.05											
BW	F-22100	AMA	15.10.08											
BX	F-26241	LMU	17.03.01	dr	D.LE	01.01.24		scale N/A		dwg no		sheet 2 of 3	size	
				enrg	JM.C	01.01.24		Amphenol FCI		77311		A3		
BS	B-20169	BVE	15.02.12	chr	JM.C	01.01.24								
BT	B-20497	BVE	15.03.18	appd	JF.N	01.01.24		type		CUSTOMER		Drawing		
sheet index	revision sheet													

PRODUCTS SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	OAL
01		5.84	2.41	10.8
02		5.84	3.42	11.8
03		5.72	5.09	13.35
05		5.72	10.14	18.4
08		5.72	17.78	26.04
15		8.51	2.55	13.6
18		5.84	3.05	11.43
19		12.83	3.03	18.4
20		15.37	3.04	20.95
22		7.75	3.05	13.35
24		6.75	2.9	12.2
25		8.51	3.18	14.22
27		6.6	2.65	11.8
26		15.57	2.84	20.95
29		17.5	3.46	23.5
32		10.3	3.05	15.9
38		5.84	3.82	12.2
39		11.2	3.05	16.8
46		8.08	2.98	13.6
54		8.08	3.81	14.43
58		14.47	3.05	20.06
62		13.5	3.05	19.09
70		6.54	3.50	12.57
83		20.46	3.00	26.00
85		5.72	8.51	16.76
87		6.98	3.05	12.57
91		5.6	10.21	18.35
92		5.65	12.76	20.95
93		6.00	4.81	13.35
94		15.60	3.20	21.25
95		10.00	8.45	20.95
96		10.95	3.05	16.55
97		9.00	3.55	15.09
98		3.00	1.35	6.84
99		24.00	3.05	29.50
AA		5.72	15.24	23.50
AB		N/A		

NOTE 7

PRODUCTS SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	OAL
AC		7.21	3.05	12.80
AD		17.53	3.43	23.50
AE		4.99	2.80	10.33
AF		5.72	3.05	11.30
AG		5.84	4.95	13.33
AH		14.31	3.20	20.05
AJ		8.90	3.40	14.85
AK		25.06	3.00	30.80
AL		3.30	3.30	9.14
AM		9.26	3.05	14.85
AN		7.60	4.40	14.47
AP		7.80	3.30	13.60
AR		18.86	2.41	23.81
AS		11.91	1.45	15.90
AT		4.60	4.60	11.61
AU		12.10	3.10	17.70
AV		6.30	6.30	15.10
AW		9.16	1.80	13.50
AX		5.08	2.43	10.05
AY		7.49	3.47	13.50
BA		8.08	2.75	13.37
BB		10.80	2.15	15.50
BC		8.08	3.81	14.43
BD		10.10	2.16	14.80
BE		13.65	2.41	18.60
BF		2.54	5.32	10.40
BG		4.98	1.85	9.23
BH		4.69	2.41	9.50
BJ		7.21	6.15	15.90
BK		6.86	2.65	12.05
BL		17.70	3.25	23.50
BM		10.96	3.70	16.20
BN		19.46	3.00	25.00
BP		8.80	3.20	14.50
BR		19.46	4.00	26.00

NOTE 6

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
H	F-29484	DDE	18.03.08	angles	linear			 mm		UNSHR.HEADER STR SR TMT			
C	F-24496	AMA	16.07.13					scale N/A					
D	F-25890	LMU	17.01.11	dr	A.MA	15.10.08			dwg no 77311 sheet 3 of 3 size A3				
E	F-26241	LMU	17.03.01	enr	L.MU	15.10.08							
F	F-28243	DDE	17.09.21	chr	J.CO	15.10.08							
G	F-28445	DDE	17.11.10	appd	A.SO	15.10.08							
sheet index	revision sheet												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[77311-103-08LF](#) [77311-103-06LF](#) [77311-115-12LF](#) [77311-115-15LF](#) [77311-146-11LF](#) [77311-146-16LF](#) [77311-102S02LF](#) [77311-102S03LF](#) [77311-102S07LF](#) [77311-102S10LF](#) [77311-102S13LF](#) [77311-102S20LF](#) [77311-102T02LF](#) [77311-102T03LF](#) [77311-102T05LF](#) [77311-102T08LF](#) [77311-102T12LF](#) [77311-102T17LF](#) [77311-118R12LF](#) [77311-120-17LF](#) [77311-120-20LF](#) [77311-129-07LF](#) [77311-146-04LF](#) [77311-170-16LF](#) [77311-415-16LF](#) [77311-811-07LF](#) [77311-846-16LF](#) [77311-852-05LF](#) [77311-891-36LF](#) [77311-892-36LF](#) [77311-415-14LF](#) [77311-103-16LF](#) [77311-487-02LF](#) [77311-487-08LF](#) [77311-146-06LF](#) [77311-883-20LF](#) [77311-194-04LF](#) [77311-439-06LF](#) [77311-439-05LF](#) [77311-197-03LF](#) [77311-132-20LF](#) [77311-195-14LF](#) [77311-487-05LF](#) [77311-483-04LF](#) [77311-SAE-36LF](#) [77311-4AJC03LF](#) [77311-139-12LF](#) [77311-1AA-36LF](#) [77311-446-03LF](#) [77311-170-01LF](#) [77311-185-03LF](#) [77311-105-04LF](#) [77311-420-02LF](#) [77311-462K03LF](#) [77311-1AG-36LF](#) [77311-494-12LF](#) [77311-GAE-36LF](#) [77311-146R16LF](#) [77311-420-36LF](#) [77311-103-05LF](#) [77311-419-36LF](#) [77311-418-01LF](#) [77311-826-04LF](#)