




REV	DESCRIPTION	DET	DATE
C	REWROTE NOTES: ADDED .453, CENTER TO EDGE DIMENSION	MK	11/19/09
D	128538C WAS 128647C. ADDED 128488	JJC	08/02/12

NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-3 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128647C ASSEMBLY CONSISTS OF 128538C COLLET AND 128488 DRAWBAR.

(D)	128488	1	drawbaar	9
	126748-3	1	UNITIZED DEFLECTOR	8
(D)	128538C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	12727-1	1	BARBED RETAINER	4
	122725	1	UNITIZED CHUCK JAW	3
	127582-1	1	TOP GUARD	2
	128306C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:		HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401	
ECCN: EAR99		NOSE ASSEMBY -04 MGP STRADDLE	
SCH B#: 8467.99.0190		DET: MJK	CK: DATE: 10/26/06 SCALE: 2:1
HTS: 8467.99.0190		B	99-3748-1C