






MATERIALS		SPECIFICATIONS	
BODY: Phenolic, UL94 V-0		FUNCTION: 1P1T OFF-ON	
ACTUATOR: Nickel Plated Brass		RATINGS: ANSI/UL1054 and CAN/CSA C22.2 No.55 (E194579): 20A 125VAC [cURus] 15A 277VAC [cURus] 2HP 125/277VAC [cURus]	
BUSHING: Nickel Plated Brass		CONTACT RESISTANCE: Initial: 10mΩ Max.	
HOUSING: Nickel Plated Steel		INSULATION RESISTANCE: 10MΩ Min.	
HARDWARE: Nickel Plated Brass		DIELECTRIC STRENGTH: 1,500VAC for 1 Minute	
SPACER PLATE: Epoxy Board		OPERATING LIFE: 6,000 Cycles [cURus]	
SPRING: Steel		TEMPERATURE: Operating: 0°C to 85°C [cURus]	
ACTUATOR PLUNGER: Phenolic, UL94 V-0		APPROVALS:	
MOBILE CONTACT BAR: Silver Plated Copper		 ROHS COMPLIANT	
CENTER PIVOT: Silver Plated Copper			
CONTACTS: Silver Alloy Clad Copper			
TERMINALS: Brass			



ACTUATOR	B	10/06/10	CAB
BODY	B	10/06/10	CAB
MATERIALS	B	10/06/09	CAB
SPECIFICATIONS	B	10/06/09	CAB
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSMITTED

B	19133	10/06/10	CAB
A	19133	10/06/09	CAB
REV.	DESCRIPTION	DATE	DRAWN BY

INCHES [MILLIMETERS]	SCALE	PROJECTION
±0.008 [±0.2] / ±1'	SCALE	PROJECTION
DRAWING NOT TO SCALE		

 E-SWITCH		 LAMB INDUSTRIES	
TITLE		DATE	
ST141D00		JUNE 10, 2010	
DRAWING NUMBER		REVISION	
34-ST141D00		B	