Features

Regulated Converters

- UL/ RAILWAYS Certified Constant Current **LED Driver**
- Wide Input and Output Voltage Range
- Digital PWM and Analogue Voltage Dimming
- **Short Circuit Protected**
- Pinned or Wired Versions
- IP67 rated for /W Version
- 96% Efficiency
- 5 year Warranty

Description

The RCD series is a step-down constant current source designed for driving high power white LEDs. Standard output currents available are 300mA, 350mA, 500mA, 600mA, 700mA, 1000mA and 1200mA to make this driver compatible with a wide range of LEDs applications. Despite its compact size, the RCD series is fully featured with very high efficiency, wide input voltage range, high ambient operating temperature and two means of dimming: PWM/digital control and analogue voltage dimming. Both dimming controls are independent and can be combined. The driver is also designed to be as reliable as the LEDs it is driving, even at the full operating temperature. Options include an IP67-rated wired version (/W) and a version with built-in reference output voltage (/Vref) to power sensors or for easy analogue dimming.

Selection Guide)					
Part	Input	Output	Output	Dimming	Options	Mounting
Number	Range	Current	Voltage	Control		Style
	(VDC)	(mA)	(Vmin-Vmax)			
RCD-24-0.30 ^{(a)(b)}	4.5-36V	0-300	2-35	Digital + Analogue	Vref	Pins or Wired
RCD-24-0.35 ^{(a)(b)}	4.5-36V	0-350	2-35	Digital + Analogue	Vref	Pins or Wired
RCD-24-0.50 ^{(a)(b)}	4.5-36V	0-500	2-35	Digital + Analogue	Vref	Pins or Wired
RCD-24-0.60 ^{(a)(b)}	4.5-36V	0-600	2-35	Digital + Analogue	Vref	Pins or Wired
RCD-24-0.70 ^{(a)(b)}	4.5-36V	0-700	2-35	Digital + Analogue	Vref	Pins or Wired
RCD-24-1.00 ^(b)	6-36V	0-1000	3-31	Digital + Analogue		Pins or Wired
RCD-24-1.20 ^(b)	6-36V	0-1200	3-31	Digital + Analogue		Pins or Wired
(-\/f-\ O: I II						

⁽a)(b) Standard is no suffix with PCB Pins.





Constant Current LED Driver





EN-50121-3-2 Certified EN-60950-1 Certified **UL-60950-1** Certified




Specifications (typical at 25°C, nominal input voltage, rated output current unless otherwise specified)

Input Voltage (absolute maximum)		40VDC max
Recommended Input Voltage	300mA-700mA	5V min. / 24V typ. / 36VDC max
	1000mA-1200mA	6V min. / 24V typ. / 36VDC max
Input Filter		Capacitor
Output Current Accuracy	300mA-700mA	±1% typ, ±3% max.
(Vin = 24DC)	1000mA-1200mA	$\pm 2\%$ typ, $\pm 5\%$ max.
Internal Power Dissipation	Worst case load of 5 LEDs	800mW max
Output Current Stability	Vin=36V, Vout =1-9 LEDs	±1% max
Output Ripple and Noise (20MHz BW)	300mA-700mA	150mVp-p max
Vin=36V, Vout =1-9 LEDs	1000mA-1200mA	300mVp-p max
Temperature Coefficient	-40°C to +85°C ambient	±0.015%/°C max
Maximum Capacitive Load		100μF
Operating Frequency	300mA-700mA	210kHz min/ 250kHz typ/ 280kHz max
	1000mA-1200mA	350kHz min/ 450kHz typ/ 550kHz max
Efficiency at Full Load		96% max.
Short Circuit Protection		Regulated at rated output current

continued on next page

Derating-Graph

(Ambient Temperature)



Refer to Application Notes

⁽a) Add suffix /Vref for pinned version with Vref output and analogue dimming

⁽b) Add suffix /W for wired version without dimming control (four wires)

⁽b) Add suffix /W/X1 for wired version with analogue dimming control (five wires)

⁽b) Add suffix /W/X2 for wired version with PWM dimming control (five wires)

⁽b) Add suffix /W/X3 for wired version with both analogue and PWM dimming controls (six wires)

⁽a) Add suffix /W/Vref for wired version with Vref output and analogue dimming (six wires)



Snecifications (typica	I at 25°C, nominal input voltag	ie rated output current unle	ess otherwise specified)
		300mA-350mA	
Operating Temperature F	Range		-40°C to +85°C
(free air convection)		500mA	-40°C to +80°C
		600mA	-40°C to +75°C
		700mA-1000mA	-40°C to +71°C
O. T		1200mA	-40°C to +65°C
Storage Temperature Ra			-55°C to +125°C
Maximum Case Tempera	ature	N 1 10 1'	100°C
Thermal Impedance	1AP 11/ ' \	Natural Convection	55°C/Watt
Case Material (Pinned or		Non Co	onductive Black Plastic
Potting Material (Pinned	or wired versions)	Discos and AMissand	Epoxy (UL94-V0)
Dimensions		Pinned/Wired	22.1 x 12.6 x 8.5mm
Weight Caldering Desfile		Pinned/Wired	4.5g/6.8g
Soldering Profile		Pinned Namiana	265°C/10 sec. max
Packing Quantities	5.la!\	Pinned Versions	39pcs per Tube
(Refer to App Notes for T		Wired Versions	5pcs per Bag
PWM Dimming and ON/		ot used - do not tie to +Vin	,
Remote ON/OFF	DC/DC ON	300mA-700mA	Open or OV <vr<0.6v< td=""></vr<0.6v<>
Threshold Voltages	DO (DO 055 (O) 11)	1000mA-1200mA	Open or 0V <vr<0.8v< td=""></vr<0.8v<>
	DC/DC OFF (Standby)	300mA-700mA	0.6 <vr<2.9v< td=""></vr<2.9v<>
		1000mA-1200mA	1.4 <vr<2.2v< td=""></vr<2.2v<>
	DC/DC OFF (Shutdown)	300mA-700mA	2.9V <vr<6v< td=""></vr<6v<>
		1000mA-1200mA	2.2V <vr<15v< td=""></vr<15v<>
Remote Pin Drive Curren		Vr=5V	1mA max
Quiescent Input Current	in Shutdown Mode	Vin=36V	200µA max
Maximum PWM Frequer	псу	For Linear Operation	200Hz max.
		Frequency Limit	1000Hz max.
Analogue Dimming Cont	rol (leave open if not used - o	do not tie to +Vin)	
Input Voltage Limits		Standard	-0.3V - 15V
		Vref Version	-0.3V - 5V
Control Voltage Range		Full On	$0.13V \pm 50mV$
(see Graphs)		300, 700, 1200mA: Full 0	Off $4.2V \pm 150$ mV
		1000mA: Full Off	$4.35V \pm 100mV$
		Vref Version: Full Off	$2.6V \pm 100 \text{mV}$
Analogue Pin Drive Curre	ent	Vc=5V	0.2mA max.
Vref Version		Vref Voltage	3.3V± 70mV
		Vref Output Current	5mA
		Vref Output Short Circuit (Current 18mA typ.
Environmental			
Relative Humidity		5% to 95%	% RH, non-condensing
/W Versions			IP67
Shock / Vibration		EN61373	
EMC Railways		EN50121-3-2:2006	
Conducted Emissions	(with filter, see note)	EN55022	Class B
Radiated Emissions	(all series except >700mA)	EN55022	Class B
ESD	, , , , , , , , , , , , , , , , , , , ,	EN61000-4-2	Criterion A
Radiated Immunity		EN61000-4-3	Criterion A
Fast Transient		EN61000-4-4	Criterion A
Conducted Immunity		EN61000-4-6	Criterion A
MTBF (RCD-24-0.70, No	ominal Vin Full Load\	+25°C	605 x 10 ³ hours
using MIL-HDBK 217F	Jimilai viii, i uii Luauj	+71°C	516 x 10 ³ hours
Safety Standards	EN General Safety	Report: SPCLVD1109081	
oaibly olalidalds	LIN UGITGIAI SAIGLY	Descrit 4040004055 0	LINOUSOU- I ZIIU EUIIIOII

Note:


1. Requires an input filter to meet EN55022 Class B conducted emissions - see next page

EMC Railway

UL General Safety

All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.

Digital Dimming




Output Current (LED appears dim)



PWM Digital Control Signal




Output Current (LED appears bright)




Analogue Dimming


Standard Version:



Vref Version:



Combined PWM and Analogue Dimming



^{*} Max output current can also be set using Analogue input

EN50121-3-2

CSA C22.2 No 60950-1-03

UL60950-1

Report: 12A082105E-C


Report: E358085-A3


+LED


LIGHTLINE DC/DC-Converter

RCD-24 Series


Typical Characteristics








Standard Application Circuit (no external components required for normal use)






CLASS B

6

EMI Filter Suggestions






 $C1=1\mu F MLCC$ $L1=22\mu H$ **RCD-24-1.00 - RCD-24-1.20** C1=2.2µF MLCC

 $L1 = 47 \mu H$

C2* C1 =RCD-24-xxx 2.2µF C2 **LED Driver** Elect. Low ESR -Vin \bigcirc --LED 5 C3 C4 C5 C6 C7 C8

Recommended Class B PCB Layout for Pinned Version



RCD-24-0.30 - RCD-24-0.70 RCD-24-1.00 - RCD-24-1.20

L1

+Vin (

Other caps not required Analogue Dimming used:

 $L1 = 120\mu H$ C2 = C7 = 10


C2 = C7 = 10nF MLCC Other caps not required L1 = 220μH C2 = 10nF C3 = C5 = 2.2nF C4 = C6 = C7 = C8 = 100nF

All capacitors MLCC


 $C2^*$ = optional 2µ2 MLCC only if L1 starts to resonate with the back ripple current.

Application Examples


LED DRIVER with 0-10V Interface



LED DIMMER for up to 10 white LEDs




MULTIPLE LED DRIVER (up to 20 LEDS)



Driving Two Strings of 350mA LEDs with one 700mA Driver using a current mirror

LED DIMMER with high frequency PWM control




Note:

It is not possible to parallel the drivers to increase the current.

LED Temperature Monitoring


Automatic LED Overtemperature Protection




*Typically, choose R so that R=Rptc @ 85°C and R>660 Ohm.

RGB Driver

SIMPLE RGB Mixer




Typical Response Curve (PTC = 500 0hm @ 70°C)







Package Style and Pinning


Pinned Version





Leave >1mm space arround case on PCB for air circulation







Recommended Footprint Details


Pin Conn	ections RCD-	-24 Series
Pin#	Out	Comments
1	+Vin	DC Supply
2	Analogue Dimming	Leave open if not used
3	PWM/ON/OFF	Leave open if not used
(3	Vref	Vref Version only)
4	GND	Do not connect to -Vout
5	-Vout	LED Cathode Connection
6	+Vout	LED Anode Connection

 $\begin{array}{l} \text{XX.X} & \pm 0.5 \text{ mm} \\ \text{XX.XX} & \pm 0.25 \text{ mm} \\ \text{Pin Tolerance} & \pm 0.1 \text{ mm} \end{array}$



Wired Versions





Wire Connections		RCD-24/W Series
Wire #	Function	Comments
1 (Red)	+Vin	DC Supply
4 (Black)	GND	Do not connect to -Vout
5 (Brown)	-Vout	LED Cathode Connection
6 (Yellow)	+Vout	LED Anode Connection

Wire length = 100mm + 10mm stripped & tinned = 110mm total

Wire outside diameter = 1.6 mm


Wire core diameter = 0.75 mm


Wire is UL/CSA listed/ 22AWG / 300V Rated



Package Style and Pinning

Wired Versions





Wire #	Function	Comments	
2 (Green)	Ana Dimming	/X1	
3 (Blue)	PWM Dimming	/X2	
2 + 3 (Green + Blue)	Ana + PWM Dimming	/X3	
2 + 3 (Green + Yellow)	Ana Dimming + Vref	/Vref	
Wire length = 100mm + 10mm stripped & tinned = 110mm total Wire outside diameter = 1.6mm Wire core diameter = 0.75mm Wire is UL/CSA listed/ 22AWG / 300V Rated			

Wired Versions are packed in bags - 5pcs per bag.

Warning: Do not connect or disconnect the LED load while the converter is powered on. This may damage or reduce the lifetime of the LED.