

BCP68; BC868; BC68PA

20 V, 2 A NPN medium power transistors

Rev. 8 — 18 October 2011

Product data sheet

1. Product profile

1.1 General description

NPN medium power transistor series in Surface-Mounted Device (SMD) plastic packages.

Table 1. Product overview

Type number ^[1]	Package			PNP complement
	Nexperia	JEITA	JEDEC	
BCP68	SOT223	SC-73	-	BCP69
BC868	SOT89	SC-62	TO-243	BC869
BC68PA	SOT1061	-	-	BC69PA

[1] Valid for all available selection groups.

1.2 Features and benefits

- High current
- Two current gain selections
- High power dissipation capability
- Exposed heatsink for excellent thermal and electrical conductivity (SOT89, SOT1061)
- Leadless very small SMD plastic package with medium power capability (SOT1061)
- AEC-Q101 qualified

1.3 Applications

- Linear voltage regulators
- Low-side switches
- Battery-driven devices
- Power management
- MOSFET drivers
- Amplifiers

1.4 Quick reference data

Table 2. Quick reference data

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_{CEO}	collector-emitter voltage	open base	-	-	20	V
I_C	collector current		-	-	2	A
I_{CM}	peak collector current	single pulse; $t_p \leq 1$ ms	-	-	3	A







Table 2. Quick reference data ...continued

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
h_{FE}	DC current gain	$V_{CE} = 1\text{ V}; I_C = 500\text{ mA}$ [1]	85	-	375	
	h_{FE} selection -25	$V_{CE} = 1\text{ V}; I_C = 500\text{ mA}$ [1]	160	-	375	

[1] Pulse test: $t_p \leq 300\text{ }\mu\text{s}$; $\delta = 0.02$.

2. Pinning information

Table 3. Pinning

Pin	Description	Simplified outline	Graphic symbol
SOT223			
1	base		 sym016
2	collector		
3	emitter		
4	collector		
SOT89			
1	emitter		 sym042
2	collector		
3	base		
SOT1061			
1	base	 Transparent top view	 sym021
2	emitter		
3	collector		

3. Ordering information

Table 4. Ordering information

Type number ^[1]	Package		
	Name	Description	Version
BCP68	SC-73	plastic surface-mounted package with increased heatsink; 4 leads	SOT223
BC868	SC-62	plastic surface-mounted package; exposed die pad for good heat transfer; 3 leads	SOT89
BC68PA	HUSON3	plastic thermal enhanced ultra thin small outline package; no leads; 3 terminals; body 2 × 2 × 0.65 mm	SOT1061

[1] Valid for all available selection groups.

4. Marking

Table 5. Marking codes

Type number	Marking code
BCP68	BCP68
BCP68-25	BCP68/25
BC868	CAC
BC868-25	CDC
BC68PA	AR
BC68-25PA	AS


5. Limiting values

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).


Symbol	Parameter	Conditions	Min	Max	Unit
V _{CBO}	collector-base voltage	open emitter	-	32	V
V _{CEO}	collector-emitter voltage	open base	-	20	V
V _{EBO}	emitter-base voltage	open collector	-	5	V
I _C	collector current		-	2	A
I _{CM}	peak collector current	single pulse; t _p ≤ 1 ms	-	3	A
I _B	base current		-	0.4	A
I _{BM}	peak base current	single pulse; t _p ≤ 1 ms	-	0.4	A
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C			
	BCP68		[1] -	0.65	W
			[2] -	1.00	W
			[3] -	1.35	W
	BC868		[1] -	0.50	W
			[2] -	0.95	W
			[3] -	1.35	W
	BC68PA		[1] -	0.42	W
			[2] -	0.83	W
			[3] -	1.10	W
			[4] -	0.81	W
			[5] -	1.65	W
T _j	junction temperature		-	150	°C
T _{amb}	ambient temperature		-55	+150	°C
T _{stg}	storage temperature		-65	+150	°C

- [1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.
- [2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 1 cm².
- [3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 6 cm².
- [4] Device mounted on an FR4 PCB, 4-layer copper, tin-plated and standard footprint.
- [5] Device mounted on an FR4 PCB, 4-layer copper, tin-plated, mounting pad for collector 1 cm².




- (1) FR4 PCB, mounting pad for collector 6 cm²
- (2) FR4 PCB, mounting pad for collector 1 cm²
- (3) FR4 PCB, standard footprint

Fig 1. Power derating curves SOT223



- (1) FR4 PCB, mounting pad for collector 6 cm²
- (2) FR4 PCB, mounting pad for collector 1 cm²
- (3) FR4 PCB, standard footprint

Fig 2. Power derating curves SOT89



- (1) FR4 PCB, 4-layer copper, mounting pad for collector 1 cm²
- (2) FR4 PCB, single-sided copper, mounting pad for collector 6 cm²
- (3) FR4 PCB, single-sided copper, mounting pad for collector 1 cm²
- (4) FR4 PCB, 4-layer copper, standard footprint
- (5) FR4 PCB, single-sided copper, standard footprint

Fig 3. Power derating curves SOT1061

6. Thermal characteristics

Table 7. Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit	
R _{th(j-a)}	thermal resistance from junction to ambient	in free air					
	BCP68	[1]	-	-	192	K/W	
		[2]	-	-	125	K/W	
		[3]	-	-	93	K/W	
	BC868	[1]	-	-	250	K/W	
		[2]	-	-	132	K/W	
		[3]	-	-	93	K/W	
	BC68PA	[1]	-	-	298	K/W	
		[2]	-	-	151	K/W	
		[3]	-	-	114	K/W	
		[4]	-	-	154	K/W	
		[5]	-	-	76	K/W	
	R _{th(j-sp)}	thermal resistance from junction to solder point					
		BCP68		-	-	16	K/W
BC868			-	-	16	K/W	
BC68PA			-	-	20	K/W	


[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 1 cm².

[3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 6 cm².


[4] Device mounted on an FR4 PCB, 4-layer copper, tin-plated and standard footprint.

[5] Device mounted on an FR4 PCB, 4-layer copper, tin-plated, mounting pad for collector 1 cm².




FR4 PCB, standard footprint

Fig 4. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT223; typical values




FR4 PCB, mounting pad for collector 1 cm²

Fig 5. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT223; typical values




FR4 PCB, mounting pad for collector 6 cm²

Fig 6. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT223; typical values




FR4 PCB, standard footprint

Fig 7. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT89; typical values




FR4 PCB, mounting pad for collector 1 cm²

Fig 8. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT89; typical values




FR4 PCB, mounting pad for collector 6 cm²

Fig 9. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT89; typical values




FR4 PCB, single-sided copper, standard footprint

Fig 10. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT1061; typical values




FR4 PCB, single-sided copper, mounting pad for collector 1 cm²

Fig 11. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT1061; typical values




FR4 PCB, single-sided copper, mounting pad for collector 6 cm²

Fig 12. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT1061; typical values



FR4 PCB, 4-layer copper, standard footprint

Fig 13. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT1061; typical values



FR4 PCB, 4-layer copper, mounting pad for collector 1 cm²

Fig 14. Transient thermal impedance from junction to ambient as a function of pulse duration for SOT1061; typical values


7. Characteristics

Table 8. Characteristics

$T_{amb} = 25\text{ }^{\circ}\text{C}$ unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
I_{CBO}	collector-base cut-off current	$V_{CB} = 25\text{ V}; I_E = 0\text{ A}$	-	-	100	nA
		$V_{CB} = 25\text{ V}; I_E = 0\text{ A}; T_j = 150\text{ }^{\circ}\text{C}$	-	-	10	μA
I_{EBO}	emitter-base cut-off current	$V_{EB} = 5\text{ V}; I_C = 0\text{ A}$	-	-	100	nA
h_{FE}	DC current gain	$V_{CE} = 10\text{ V}$				
		$I_C = 5\text{ mA}$	50	-	-	
	DC current gain	$V_{CE} = 1\text{ V}$				
		$I_C = 500\text{ mA}$	[1] 85	-	375	
		$I_C = 1\text{ A}$	[1] 60	-	-	
		$I_C = 2\text{ A}$	[1] 40	-	-	
	DC current gain	$V_{CE} = 1\text{ V}$				
	h_{FE} selection -25	$I_C = 500\text{ mA}$	[1] 160	-	375	
V_{CEsat}	collector-emitter saturation voltage	$I_C = 1\text{ A}; I_B = 100\text{ mA}$	[1] -	-	0.5	V
		$I_C = 2\text{ A}; I_B = 200\text{ mA}$	[1] -	-	0.6	V
V_{BE}	base-emitter voltage	$V_{CE} = 10\text{ V}; I_C = 5\text{ mA}$	[1] -	-	0.7	V
		$V_{CE} = 1\text{ V}; I_C = 1\text{ A}$	[1] -	-	1	V
C_c	collector capacitance	$V_{CB} = 10\text{ V}; I_E = i_e = 0\text{ A}; f = 1\text{ MHz}$	-	22	-	pF
f_T	transition frequency	$V_{CE} = 5\text{ V}; I_C = 50\text{ mA}; f = 100\text{ MHz}$	40	170	-	MHz


[1] Pulse test: $t_p \leq 300\text{ }\mu\text{s}$; $\delta = 0.02$.



$V_{CE} = 1$ V


- (1) $T_{amb} = 100$ °C
- (2) $T_{amb} = 25$ °C
- (3) $T_{amb} = -55$ °C

Fig 15. DC current gain as a function of collector current; typical values



$T_{amb} = 25$ °C


Fig 16. Collector current as a function of collector-emitter voltage; typical values



$V_{CE} = 1$ V

- (1) $T_{amb} = -55$ °C
- (2) $T_{amb} = 25$ °C
- (3) $T_{amb} = 100$ °C

Fig 17. Base-emitter voltage as a function of collector current; typical values



$I_C/I_B = 10$

- (1) $T_{amb} = 100$ °C
- (2) $T_{amb} = 25$ °C
- (3) $T_{amb} = -55$ °C

Fig 18. Collector-emitter saturation voltage as a function of collector current; typical values

8. Test information

8.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q101 - Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

9. Package outline




Fig 19. Package outline SOT223 (SC-73)




Fig 20. Package outline SOT89 (SC-62/TO-243)




Fig 21. Package outline SOT1061 (HUSON3)

10. Packing information

Table 9. Packing methods

The indicated -xxx are the last three digits of the 12NC ordering code.^[1]

Type number ^[2]	Package	Description	Packing quantity		
			1000	3000	4000
BCP68	SOT223	8 mm pitch, 12 mm tape and reel	-115	-	-135
BC868	SOT89	8 mm pitch, 12 mm tape and reel; T1 ^[3]	-115	-	-135
		8 mm pitch, 12 mm tape and reel; T3 ^[4]	-146	-	-
BC68PA	SOT1061	4 mm pitch, 8 mm tape and reel	-	-115	-

[1] For further information and the availability of packing methods, see [Section 14](#).

[2] Valid for all available selection groups.

[3] T1: normal taping

[4] T3: 90° rotated taping

11. Soldering




Fig 22. Reflow soldering footprint SOT223 (SC-73)




Fig 23. Wave soldering footprint SOT223 (SC-73)




Fig 24. Reflow soldering footprint SOT89 (SC-62/TO-243)





Fig 25. Wave soldering footprint SOT89 (SC-62/TO-243)



12. Revision history

Table 10. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BCP68_BC868_BC68PA v.8	20111018	Product data sheet	-	BC868 v.7 BCP68 v.4
Modifications: • The format of this document has been redesigned to comply with the new identity guidelines of NXP Semiconductors. • Legal texts have been adapted to the new company name where appropriate. • Type number BC68PA added • Section 1 “Product profile”: updated • Section 2 “Pinning information”: updated • Section 3 “Ordering information”: updated • Section 4 “Marking”: updated • Section 8 “Test information”: added • Section 9 “Package outline”: updated • Section 10 “Packing information”: added • Section 11 “Soldering”: added • Table 6, 7 and 8: updated according to latest measurements • Figure 1, 2, 6, 8, 15 to 18: updated • Figure 3, 4, 5, 7, 9, 10 to 13: added				
BC868 v.7	20041108	Product specification	-	BC868 v.6
BC868 v.6	20031202	Product specification	-	BC868 v.5
BC868 v.5	19990408	Product specification	-	BC868 v.4
BC868 v.4	19980716	Product specification	-	BC868_CNV v.3
BC868_CNV v.3	19970319	Product specification	-	BC868_CNV v.2
BC868_CNV v.2	19970307	Product specification	-	-
BCP68 v.4	20031125	Product specification	-	BCP68 v.3
BCP68 v.3	19990408	Product specification	-	BCP68_CNV v.2
BCP68_CNV v.2	19970409	Product specification	-	-

13. Legal information

13.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nexperia.com>.

13.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

13.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or

malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia accepts no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

13.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

14. Contact information

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: salesaddresses@nexperia.com

15. Contents

1 Product profile 1

1.1 General description 1

1.2 Features and benefits 1

1.3 Applications 1

1.4 Quick reference data 1

2 Pinning information 2

3 Ordering information 3

4 Marking 3

5 Limiting values 4

6 Thermal characteristics 6

7 Characteristics 13

8 Test information 15

8.1 Quality information 15

9 Package outline 15

10 Packing information 16

11 Soldering 17

12 Revision history 20

13 Legal information 21

13.1 Data sheet status 21

13.2 Definitions 21

13.3 Disclaimers 21

13.4 Trademarks 22

14 Contact information 22

15 Contents 23