



## SHPX2-18-3GR

**0.6 m | 2 ft Sentinel® High Performance Antenna, dual-polarized, 17.700–19.700 GHz, UBR flange, gray antenna, gray polymer radome without flash, standard pack—one-piece reflector**

### Replaced By

SHPX2-18-3WH/B

0.6 m | 2 ft Sentinel® High Performance Antenna, dual-polarized, 17.7–19.7 GHz, UBR flange, white antenna, white radome

## General Specifications

Antenna Type	SHPX - Sentinel® High Performance Antenna, dual-polarized
Diameter, nominal	0.6 m   2 ft
Packing	Standard pack
Radome Color	Gray
Radome Material	Polymer
Reflector Construction	One-piece reflector
Antenna Input	UBR220
Antenna Color	Gray
Antenna Type	SHPX - Sentinel® High Performance Antenna, dual-polarized
Diameter, nominal	0.6 m   2 ft
Flash Included	No
Polarization	Dual

## Electrical Specifications

Operating Frequency Band	17.700 – 19.700 GHz
Beamwidth, Horizontal	2.1 °
Beamwidth, Vertical	2.1 °
Cross Polarization Discrimination (XPD)	30 dB
Electrical Compliance	Brazil Anatel Class 2   Canada SRSP 317.8 Part A   ETSI 302 217 Class 4   US FCC Part 101A
Front-to-Back Ratio	70 dB
Gain, Low Band	38.4 dBi
Gain, Mid Band	38.9 dBi
Gain, Top Band	39.1 dBi
Operating Frequency Band	17.700 – 19.700 GHz
Radiation Pattern Envelope Reference (RPE)	7256A
Return Loss	17.7 dB
VSWR	1.30

## Mechanical Specifications

Fine Azimuth Adjustment	±15°
Fine Elevation Adjustment	±15°

SHPX2-18-3GR

Mounting Pipe Diameter	50 mm–115 mm   2.0 in–4.5 in
Net Weight	11 kg   24 lb
Side Struts, Included	0
Side Struts, Optional	0
Wind Velocity Operational	200 km/h   124 mph
Wind Velocity Survival Rating	250 km/h   155 mph

## Wind Forces At Wind Velocity Survival Rating

Angle $\alpha$ for MT Max	0 °
Axial Force (FA)	1290 N   290 lbf
Side Force (FS)	384 N   86 lbf
Twisting Moment (MT)	479 N•m
Weight with 1/2 in (12 mm) Radial Ice	34 kg   74 lb
Zcg with 1/2 in (12 mm) Radial Ice	194 mm   8 in
Zcg without Ice	143 mm   6 in

SHPX2-18-3GR

## Wind Forces At Wind Velocity Survival Rating Image




## Packed Dimensions

Gross Weight, Packed Antenna	13.1 kg		28.9 lb
Height	670.0 mm		26.4 in
Length	710.0 mm		28.0 in
Volume	0.0 m <sup>3</sup>		
Width	710.0 mm		28.0 in

SHPX2-18-3GR

Antenna Dimensions And Mounting Information



Dimensions in Inches (mm)					
Antenna size, ft (m)	A	B	C	D	E
2 (0.6)	26 (662)	14.6 (372)	17 (434)	3.5 (89.5)	17.8 (451)

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and or distributed under this quality management system

Included Products

SHPX2-18 (Product Component—not orderable) — 0.6 m | 2 ft Sentinel® High Performance Antenna, dual-polarized, 17.700–19.700 GHz

\* Footnotes

Axial Force (FA)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Cross Polarization Discrimination (XPD)	The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.
Front-to-Back Ratio	Denotes highest radiation relative to the main beam, at 180° ±40°, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.
Gain, Mid Band	For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by

SHPX2-18-3GR

	computer integration of the measured antenna patterns.
Operating Frequency Band	Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.
Packing	Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.
Radiation Pattern Envelope Reference (RPE)	Radiation patterns determine an antenna's ability to discriminate against unwanted signals under conditions of radio congestion. Radiation patterns are dependent on antenna series, size, and frequency.
Return Loss	The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.
Side Force (FS)	Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Twisting Moment (MT)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
VSWR	Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.
Wind Velocity Operational	The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.
Wind Velocity Survival Rating	The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.