

DATA SHEET

SKY13386-000: 0.1-4.0 GHz SP3T Switch

Applications


- WLAN b/g

Features

- Broadband frequency range: 0.1 GHz to 4.0 GHz
- Positive control voltages: 2.7 V to 3.6 V
- Low insertion loss: 0.50 dB typical @ 2.5 GHz
- High isolation: 25 dB typical @ 2.5 GHz
- IP0.5dB: +29 dBm typical @ 3 V
- Small CSP (8-bump, 650 x 650 μ m) 200 μ m ball pitch package




Skyworks Green™ products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green™*, document number SQ04-0074.



S2414a

Figure 2. SKY13386-000 Pinout – 8-Bump CSP (Top View, Bumps Down)



S1923a

Figure 1. SKY13386-000 Block Diagram

Description

The SKY13386-000 is a GaAs pHEMT Single-Pole, Triple-Throw (SP3T) switch designed for 2.4 GHz WLAN applications.

The SKY13386-000 is manufactured in a compact, 650 x 650 μ m, 8-bump Chip Scale Package (CSP). The small footprint provides the industry's smallest PCB area needed to implement an integrated SP3T switch.

A functional block diagram is shown in Figure 1. The pin configuration and package are shown in Figure 2. Signal pin assignments and functional pin descriptions are provided in Table 1.

Table 1. SKY13386-000 Signal Descriptions

Pin #	Name	Description	Pin #	Name	Description
1	VC2	Switch logic control 2 (see Table 4)	5	GND	Ground
2	RF1	RF output port 1. Must be DC blocked for proper operation.	6	RF2	RF output port 2. Must be DC blocked for proper operation.
3	VC1	Switch logic control 1 (see Table 4)	7	VC3	Switch logic control 3 (see Table 4)
4	RF3	RF output port 3. Must be DC blocked for proper operation.	8	RFC	Antenna. Must be DC blocked for proper operation.

Table 2. SKY13386-000 Absolute Maximum Ratings

Parameter	Symbol	Minimum	Maximum	Units
Control voltage	VC1, VC2, VC3		6	V
RF input power	P _{IN}		+35	dBm
Operating temperature	T _{OP}	−40	+85	°C
Storage temperature	T _{STG}	−40	+125	°C

Note: Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

CAUTION: Although this device is designed to be as robust as possible, Electrostatic Discharge (ESD) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be used at all times.

Technical Description

Switching is controlled by three control voltage inputs (VC1, VC2, and VC3). Depending on the logic voltage level applied to the control pins, the RFC pin is connected to one of three switched RF outputs (RF1, RF2, or RF3) using a low insertion loss path, while maintaining a high isolation path to the alternate ports.

DC blocking capacitors are required on all four RF ports for proper operation and to determine the lower frequency operation of the switch.

Electrical and Mechanical Specifications

The absolute maximum ratings of the SKY13386-000 are provided in Table 2. Electrical specifications are provided in Table 3.

The state of the SKY13386-000 is determined by the logic provided in Table 4.

Typical performance characteristics for the SKY13386-000 are illustrated in Figures 3 to 7.

Table 3. SKY13386-000 Electrical Specifications (Note 1)**(VC1 = VC2 = VC3 = 3/0 V, P_{IN} = 0 dBm, T_{OP} = +25 °C, Characteristic Impedance [Z₀] = 50 Ω, Unless Otherwise Noted)**

Parameter	Symbol	Test Condition	Min	Typical	Max	Units
RF Specifications						
Insertion Loss	IL	0.1 to 1.0 GHz		0.50	0.65	dB
		1.0 to 2.4 GHz		0.65	0.75	dB
		2.4 to 2.5 GHz		0.70	0.80	dB
		2.5 to 4.0 GHz		0.80	1.00	dB
Isolation	Iso	0.1 to 1.0 GHz	26	30		dB
		1.0 to 2.4 GHz	25	38		dB
		2.4 to 2.5 GHz	22	25		dB
		2.5 to 4.0 GHz	19	22		dB
Port-to-Port Isolation		RF1 to RF2, 2.4 to 2.5 GHz	25	29		dB
		RF1 to RF3, 2.4 to 2.5 GHz	23	25		dB
		RF2 to RF3, 2.4 to 2.5 GHz	23	25		dB
Input Return Loss	S11	0.1 to 4.0 GHz	20	25		dB
0.5 dB Input Compression Point	IP0.5dB	2.4 to 2.5 GHz, RFC to RF1/RF2/RF3		+29		dBm
3 rd Order Input Intercept Point	IIP3	2.4 to 2.5 GHz, ΔF = 1 MHz, PIN = +17 dBm/tone		+54		dBm
Harmonics	2fo, 3fo	2.4 to 2.5 GHz		−70		dBc
Switching Speed: 50% control voltage to 90/10% RF 90/10% RF or 10/90% RF				50		ns
				40		ns
DC Specifications						
Control Voltage: High Low	VHIGH		+2.7	+3	+3.6	V
	VLOW		−0.2	0	+0.2	V
Control current	ICTL			5		μA

Note 1: Performance is guaranteed only under the conditions listed in this Table.**Table 4. SKY13386-000 Truth Table**

VC1 (Pin 3)	VC2 (Pin 1)	VC3 (Pin 7)	RF1 (Pin 2)	RF2 (Pin 6)	RF3 (Pin 4)
1	0	0	On	Off	Off
0	1	0	Off	On	Off
0	0	1	Off	Off	On

Note: "0" = -0.2 V to +0.2 V. "1" = +2.7 V to +3.6 V. "On" = Insertion loss state. "Off" = Isolation state. Any state other than described in this Table places the switch into an undefined state. An undefined state will not damage the device.

Typical Performance Characteristics

($V_{C1} = V_{C2} = V_{C3} = 3/0\text{ V}$, $P_{IN} = 0\text{ dBm}$, $T_{OP} = +25\text{ }^{\circ}\text{C}$, Characteristic Impedance $[Z_0] = 50\text{ }\Omega$, Unless Otherwise Noted)




Figure 3. Insertion Loss vs Frequency




Figure 4. Input Return Loss vs Frequency




Figure 5. Output Return Loss vs Frequency




Figure 6. Isolation vs Frequency




Figure 7. Port-to-Port Isolation vs Frequency

Evaluation Board Description

The SKY13386-000 Evaluation Board is used to test the performance of the SKY13386-000 SP3T Switch. An Evaluation Board schematic diagram is provided in Figure 8. An assembly drawing for the Evaluation Board is shown in Figure 9.

Package Dimensions

Package dimensions for the 8-bump CSP are shown in Figure 10.

Package and Handling Information

Since the package is sensitive to moisture absorption, it is baked and vacuum packed before shipping. Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped on film frame.






Figure 8. SKY13386-000 Evaluation Board Schematic



S2415a

Figure 9. SKY13386-000 Evaluation Board Assembly Diagram



All measurements are in millimeters.

S2553a

Figure 10. SKY13386-000 8-Bump CSP Package Dimensions

Ordering Information

Model Name	Manufacturing Part Number	Evaluation Board Part Number
SKY13386-000 SP3T Switch	SKY13386-000	SKY13386-000-EVB

Copyright © 2011 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.