

SERVO cable FACAB EFK SERVO-CP acc. to Siemens Standard 6FX8008+




FACAB 10605 EFK SERVO CP 6FX8008-1BA21 4G2



Specification/standard:	UL/CSA
conductor material:	bare copper
conductor construction:	fine stranded class 6
insulation:	polypropylen
screen:	Cu-braid, tinned
screen coverage:	85 %
sheathing material:	polyurethan
colour of outer sheath:	orange RAL 2003 (DESINA)
flame retardant:	VDE 0482-332-1-2/IEC 60332-1
halogen free:	DIN EN 50267/IEC 60754
oil resistant:	EN 60811-2-1
max. operating temperature,	-50 - +80 °C
fixed:	
temperature, moved/during	-40 - +80 °C
installation:	
bending radius, fixed	5 x DA
installation:	
bending radius, moved	7,5 x DA
application:	
Bending cycles, max.:	5 Mio.
Moving distance, max.:	100 m
nominal voltage U_o:	600 V
nominal voltage U:	1 kV
test voltage:	4 kV
core identification:	acc. to Siemens specification

Application: Low capacity connection cable between servo controller and frequency driven motor. For application in machine tools and drag chains with medium mechanical stress. Please pay attention to our instructions for the use of drag-chain cables.

Additional information: Siemens part numbers (6FX...) are registered trade marks of Siemens AG and used only as reference.



The products and information presented here are for technical calculation only. They are subject to technical progress and in no way represent the ability of shipment. Outer diameters are approximately.

Table: Technical characteristics FACAB EFK SERVO-CP Siemens

p/n	part name	D _A [mm]	G [kg]	Cu [kg/km]	p/n	part name	D _A [mm]	G [kg]	Cu [kg/km]
035285	[4G1,5] 0,6/1 kV OR cUL - 6FX8008-1BB11	9	159	90	035288	[4G6] 0,6/1 kV OR cUL - 6FX8008-1BB411	14,7	464	315
035286	[4G2,5] 0,6/1 kV OR cUL - 6FX8008-1BB21	10,6	235	135	035289	[4G10] 0,6/1 kV OR cUL - 6FX8008-1BB51	17,5	672	488
035287	[4G4] 0,6/1 kV OR cUL - 6FX8008-1BB31	11,9	323	205,5	035290	[4G16] 0,6/1 kV OR cUL - 6FX8008-1BB61	21,6	1089	769

p/n	part name	D _A [mm]	G [kg]	Cu [kg/km]
035291	[4G25] 0,6/1 kV OR cUL - 6FX8008-1BB25	25,4	1523	1100
035292	[4G35] 0,6/1 kV OR cUL - 6FX8008-1BB35	28,6	2080	1510
035293	[4G50] 0,6/1 kV OR cUL - 6FX8008-1BB50	33,4	2710	2130
035294	[4G70] 0,6/1 kV OR cUL - 6FX8008-1BB70	42,5	4123	3025
035295	[4G1,5+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA116FX8008-1BA1	11,6	244	163,5
035296	[4G2,5+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA21 6FX8008-1BA21	13,4	310	189
035297	[4G4+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA316FX8008-1BA3	14,8	408	260,5

DA	outer diameter
G	weight
Cu	copper

p/n	part name	D _A [mm]	G [kg]	Cu [kg/km]
035298	[4G6+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA41	16,8	540	365
035299	[4G10+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA516FX8008-1BA5	19,9	782	560
035300	[4G16+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA616FX8008-1BA6	22,5	1101	816
035301	[4G25+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA256FX8008-1BA2	26,2	1490	1172
035302	[4G35+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA356FX8008-1BA3	29,8	2015	1595
035303	[4G50+(2X1,5)] 0,6/1 kV OR cUL - 6FX8008-1BA50	34	2754	2214