



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

## REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1885	A	RELEASED	BYF	02/03/06	HO	2/6/06	JWM	2/6/06

**Description:** A medium power silicon, PNP transistor in a TO-220 type package designed for switching and amplifier applications. This device is especially designed for series and shunt regulators and as a driver and output stage of high-fidelity amplifiers.

### Features:

- Low Saturation Voltage

### Absolute Maximum Ratings:

- Collector-Base Voltage,  $V_{CBO} = 100V$
- Collector-Emitter Voltage,  $V_{CEO} = 60V$
- Emitter-Base Voltage,  $V_{EBO} = 5V$
- Continuous Collector Current,  $I_C = 3A$
- Base Current,  $I_B = 0.4A$
- Total Device Dissipation ( $T_C = +25^\circ C$ ),  $P_D = 30W$   
Derate above  $25^\circ C = 0.24mW/^\circ C$
- Total Device Dissipation ( $T_C = +25^\circ C$ ),  $P_D = 2W$   
Derate above  $25^\circ C = 0.016mW/^\circ C$
- Operating Junction Temperature Range,  $T_J = -65^\circ C$  to  $+150^\circ C$
- Storage Temperature Range,  $T_{stg} = -65^\circ C$  to  $+150^\circ C$
- Thermal Resistance, Junction-to-Case,  $R_{thJC} = 4.167^\circ C/W$
- Thermal Resistance, Junction-to-Ambient,  $R_{thJA} = 62.5^\circ C/W$

## Electrical Characteristics: ( $T_C = +25^\circ C$ unless otherwise specified)


Parameter	Symbol	Test Conditions	Min	Max	Unit
<b>OFF Characteristics</b>					
Collector-Emitter Breakdown Voltage (Note 1)	$V_{(BR)CEO}$	$I_C = 30mA, I_B = 0$	60	—	V
Collector Cut-Off Current	$I_{CEO}$	$V_{CB} = 30V, I_B = 0$	—	0.3	mA
Emitter Cut-Off Current	$I_{EBO}$	$V_{EB} = 5V, I_C = 0$	—	1	mA
<b>ON Characteristics (Note 1)</b>					
DC Current Gain	$h_{FE}$	$V_{CE} = 4V, I_C = 0.2A$	40	—	—
		$V_{CE} = 4V, I_C = 1A$	15	75	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 1A, I_B = 125mA$	—	0.7	V
Base-Emitter On Voltage	$V_{BE(on)}$	$I_C = 1A, V_{CE} = 4V$	—	1.3	V
<b>Small-Signal Characteristics</b>					
Current Gain-Bandwidth Product	$f_T$	$V_{CE} = 10V, I_C = 200mA, f = 1MHz$	3	—	MHz
Small-Signal Current Gain	$h_{fe}$	$V_{CE} = 10V, I_C = 200mA, f = 1kHz$	20	—	—

Note 1. Pulsed: Pulse Duration = 300 $\mu s$ , Duty Factor = 0.018.

Dimensions	A	B	C	D	E	F	G	H	J	K	L	M	N	O
Min.	14.42	9.63	3.56	—	1.15	3.75	2.29	2.54	—	12.70	2.80	2.03	—	7*
Max.	16.51	10.67	4.83	0.90	1.40	3.88	2.79	3.43	0.56	14.73	4.07	2.92	31.24	





RoHS  
Compliant



### Pin Configuration:

- Base
- Collector
- Emitter
- Collector



DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

### TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
BASAM YOUSIF	02/03/06
CHECKED BY:	DATE:
HISHAM ODISH	2/6/06
APPROVED BY:	DATE:
JEEF MCVICKER	2/6/06

DRAWING TITLE: Medium Power Transistor, Silicon, TO-220, PNP			
SIZE A	DWG. NO. TIP30A	ELECTRONIC FILE 01H1004.DWG	REV A
SCALE: NTS	U.O.M.: MILLIMETERS	SHEET: 1 OF 1	