

4 and 5-Pin Receptacles, Front Mount, Leads and Solder Cups

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 250 V, 4 A



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p>FK ..</p> <p>Typical panel cutout is 15.2 mm.</p>	FK 4.4	FS 4.4	105°C, Solder Cup, mates with 4-pin cordsets, PG 9 Threads	<p>Female</p> <p>Male</p>
<p>FS ..</p> <p>Typical panel cutout is 15.2 mm.</p>	FK 4.5	FS 4.5	105°C, Solder Cup, 250 V, 4 A, mates with 5-pin cordsets, PG 9 Threads	<p>Female</p> <p>Male</p>
<p>FS ../14.5</p> <p>Typical panel cutout is 21 mm.</p>		FS 4.4/14.5	105°C, Solder Cup, 250 V, 4 A, mates with 4-pin cordsets, 1/2-14NPSM Threads	<p>Male</p>
		FS 4.5/14.5	105°C, Solder Cup, 250 V, 4 A, mates with 5-pin cordsets, 1/2-14NPSM Threads	<p>Male</p>

Receptacles

* Length in meters. Standard lead length is 0.5 Meters. Consult factory for other lengths.
Standard housing material is nickel plated brass "FS.."; "FSV.." indicates stainless steel.
To specify PVC jacketed cable, add "/S717" to the end of the part number.