




PART NO.

P88FB50

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Jagan	22/10/09	Sreejesh	22/10/09	Farnell	05/11/09



Dimensions : Millimetres

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

Jagan

DATE:

22/10/09

CHECKED BY:

Sreejesh

DATE:

22/10/09

APPROVED BY:

Farnell

DATE:

05/11/09

DRAWING TITLE:

RJ45 Plug - Modular, 8/8

SIZE
A

DWG NO.

M10002407

ELECTRONIC FILE
9657371-DWGREV
A

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 2



PART NO.

P88FB50

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Jagan	22/10/09	Sreejesh	22/10/09	Farnell	05/11/09

Specifications:

Material:

Housing : Polycarbonate (PC).

Contact : Phosphor bronze.

Fine gold plated (1.27μm/50μ-inch).

Cover : Nickel.

Mechanical:

Minimum cable to tensile strength : 20lbs.

Minimum durability : 200 mating cycles.

Electrical:

Maximum UL applications : 250 volts ac at 2 amperes.

Dielectric withstanding voltage : 500 volts ac.

Insulation resistance : 500MΩ.

Maximum termination resistance : 35mΩ after environmental testing.

Part Number Table

Description	Part Number
Plug, RJ45, Modular, 8/8	P88FB50

<http://www.farnell.com><http://www.newark.com><http://www.cpc.co.uk>

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

Jagan

DATE:

22/10/09

CHECKED BY:

Sreejesh

DATE:

22/10/09

APPROVED BY:

Farnell

DATE:

05/11/09

DRAWING TITLE:

RJ45 Plug - Modular, 8/8

SIZE
A

DWG NO.

M10002407

ELECTRONIC FILE

9657371-DWG

REV

A

SCALE: NTS

U.O.M.: mm

SHEET: 2 OF 2