

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	Redrawn in Autcad	JAP	11/25/91				
1199	B	Redrawn and Renamed	JWM	11/8/01	JC	11/26/01	JC	11/26/01


Notes:

Material: Electro-tin plated Copper

Insulating Material: Vinyl (PVC) UL94V-0

Voltage Rating: 600V

Operating Temp: -40°F to 221°F (-40°C ~ 105°C)



SPC Part Number	Wire Range (AWG)	Stud Size	S	W	T	M	Color	Seam
CBS-TV-1406	16 ~ 14	#6 (.138)	.148					
CBS-TV-1408	16 ~ 14	#8 (.164)	.174	.30	.090	.170	Blue	Butted Seam
CBS-TV-1410	16 ~ 14	#10 (.190)	.200					
CBS-TV-1804	22 ~ 18	#4 (.112)	.120	.25				
CBS-TV-1806	22 ~ 18	#6 (.138)	.148		.070	.145	Red	Butted Seam
CBS-TV-1808	22 ~ 18	#8 (.164)	.174	.30				
CBS-TV-1810	22 ~ 18	#10 (.190)	.200					
CBS-ZV-1406	16 ~ 14	#6 (.138)	.148					Brazed Seam
CBS-ZV-1408	16 ~ 14	#8 (.164)	.174	.30	.090	.170	Blue	
CBS-ZV-1410	16 ~ 14	#10 (.190)	.200					
CBS-ZV-1806	22 ~ 18	#6 (.112)	.148					Brazed Seam
CBS-ZV-1808	22 ~ 18	#8 (.138)	.174	.30	.070	.145	Red	
CBS-ZV-1810	22 ~ 18	#10 (.164)	.200					

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE SUBSEALER, THE USER, OR THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY



ES8918



LR22190M6

OSHA
Acceptable

Tolerances: Unless
Otherwise Specified:

.X = ±.015

.XX = ±.010
.XXX = ±.005

DRAWN BY:

DATE:

DRAWING TITLE:

Insulated Block Fork Terminals

JC

3/7/91

CHECKED BY:

DATE:

SIZE DWG. NO.

REV

JOHN COLE

11/27/91

A

TA-441

ELECTRONIC FILE

TA-441.dwg

B

APPROVED BY:

DATE:

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1