











THIS DRAWING IS A CONTROLLED DOCUMENT. DWG NO 1583000	USED ON _____												
	TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 				CONTACT DESCRIP.	APPLIC. SPECIF.
								LOOSE PIECE 		STRIP FORM 			
	91500-1 91500-3 91500-4 	0.5 - 0.9 [20-18] 1.2 - 2.1 [16-14]	1.52 - 3.30 [.060 - .130]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.27 ± 0.05 [.050 ± .002]	350547-[] 350550-[] 350669-[] 350705-[]	350218-[] 350536-[] 350654-[] 350687-[]	Univ. MATE-N-LOK Contacts	114-1010 & 114-1011		
							1.60 ± 0.05 [.063 ± .002]	770250-[] 770251-[] 770254-[]	770007-[] 770008-[] 770193-[]	Univ. MATE-N-LOK 2 Contacts	114-1043		
	91506-1 91506-3	1.21 - 2.1 [16-14]	3.3 - 5.1 [.130 - .200]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.60 ± 0.05 [.063 ± .002]	350551-[] 350552-[] 350707-[] 350919-[] 350918-[] 770249-[] 770248-[] 770255-[]	350537-[] 350538-[] 350700-[] 350874-[] 350873-[] 770006-[] 770005-[] 770194-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043		
	91508-1 91508-3	0.5 - 0.9 [20-18]	3.3 - 5.1 [.130 - .200]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.24 ± 0.05 [.049 ± .002]	350551-[] 350552-[] 350707-[] 350919-[] 350918-[] 770249-[] 770248-[] 770255-[]	350537-[] 350538-[] 350700-[] 350874-[] 350873-[] 770006-[] 770005-[] 770194-[]	Univ. MATE-N-LOK Contacts Univ MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043		
	91510-1 91510-3	0.2 - 0.38 [24-22] 0.5 - 0.9 [20-18]	1.02 - 2.54 [.040 - .100]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.02 ± 0.05 [.040 ± .002]	350689-[] 350690-[] 350706-[] 640347-[]	350570-[] 350561-[] 350699-[] 350851-[]	Univ MATE-N-LOK Contacts	114-1010 & 114-1011		
							1.17 ± 0.05 [.046 ± .002]	770252-[] 770253-[]	770009-[] 770010-[]	Univ MATE-N-LOK 2 Contacts	114-1043		
	91522-1 91522-3	0.32 - 0.6 [22-20]	1.50 - 2.2 [.059 - .087]	YES	NO	3.45 ± 0.25 [.136 ± .010]	0.79 ± 0.05 [.031 ± .002]	170364-[] 170366-[]	170360-[] 170362-[]	Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017		
		(1 wire) 0.8-0.9 [18] (2 wire) 0.31-0.38 [22]	(1 wire) 1.54-2.4 [.059-.095] (2 wire) 1.5-1.7 [.059-.067]			(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.7 ± 0.2 [.146 ± .008]	1.04 ± 0.05 [.041 ± .002]	794228-[] 794229-[]	794220-[] 794221-[]	Mini-Univ. MATE-N-LOK 2 Contacts	114-13089		
								770987-[] 770988-[]	770903-[] 770904-[]				
	91529-1 91529-3	0.12 - 0.24 [26-24] 0.32 - 0.38 [22]	1.2 - 1.75 [.047 - .069]	YES	YES	3.45 ± 0.25 [.136 ± .010]	0.69 ± 0.05 [.027 ± .002]	170363-[] 170365-[]	170359-[] 170361-[] 794136-[]	Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017		
							0.79 ± 0.05 [.031 ± .002]	794226-[] 794227-[]	794218-[] 794219-[]	Mini-Univ. MATE-N-LOK 2 Contacts	114-1111		
									770985-[] 770986-[]	770901-[] 770902-[]		114-13089	
	91536-1 91536-3	0.5 - 0.9 [20-18] (1 wire) 1.2-1.4 [16] (2 wire) 0.5-0.6 [20]	2.0 - 3.0 [.079 - .118] (1 wire) 2.5-3.2 [.098-.126] (2 wire) 2.0-2.4 [.079-.094]	YES	NO	3.45 ± 0.25 [.136 ± .010] (1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.07 ± 0.05 [.042 ± .002] 1.27 ± 0.05 [.050 ± .002]	171638-[] 171639-[]		171636-[] 171637-[]		Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017
91594-1 91594-3	0.50-0.89 [20-18] 0.50-1.42x2 [16-20x2]	2.00-3.20 [.079-.126] 2.26-3.20 [.098-.126]	YES	NO	(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.07 ± 0.05 [.042 ± .002] 1.29 ± 0.05 [.051 ± .002]	794230-[] 794231-[]		794222-[] 794223-[]		Mini-Univ. MATE-N-LOK 2 Contacts	114-1111	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS NOT TO BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION OF TE CONNECTIVITY. ANY VIOLATION OF THIS NOTICE SHALL BE SUBJECT TO LEGAL ACTION.

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.

 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED


 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN	21FEB2012	MATERIAL	-	HEAT TREAT	-
CHK	22FEB2012				
APVD	22FEB2012				
NAME					
CERTI-CRIMP II TOOL DATA SHEET					
UNIVERSAL MATE-N-LOK CONTACT FAMILY					
SCALE	SIZE	DRAWING NO	SHEET	REV	
-	A1	1583000	1	of 2	C1

0	PLC	±	-
1	PLC	±	-
2	PLC	±	-
3	PLC	±	-
4	PLC	±	-

ANGLES±	-
SURFACE TEXTURE	









LOC
A
DIST
00

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER AND NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT AUTHORIZATION FROM TE CONNECTIVITY.

THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO. 1583000

LOC
A
DIST
00

3308-B (3/11)

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPT.	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
 91574-1	0.20-0.56 [24-20]	1.52-2.54 [.060-.100]	YES	NO ☐	5.16 ± 0.38 [.203 ± .015]	1.05 ± 0.08 [.041 ± .003]	350689-[]	350570-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
	0.75-0.89 [18]					1.27 ± 0.08 [.050 ± .003]	350690-[]	350561-[]		
 91575-1 91575-3	0.50-0.89 [20-18]	2.54-3.31 [.100-.130]	YES	NO ☐	5.16 ± 0.38 [.203 ± .015]	1.29-1.45 [.051-.057]	350547-[]	350218-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
	0.75+0.75 OR 0.75+1.25 [18+18 OR 18+16]					1.60-1.75 [.063-.069]	350669-[]	350564-[]		
1976176-1	18 GA SOLID	1.02-2.54 [.040-.100]	YES	NO ☐	4.37-0.38 [.172-.015]	1.118 ± .025 [.044 ± .001]	350689-[] 350550-[] 350690-[] 350547-[]	350851-[] 350536-[] 350561-[] 350218-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.



 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED

 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: 21FEB2012	MATERIAL: -	HEAT TREAT: -				
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -		CHK: 22FEB2012	 TE Connectivity					
ANGLES: ± -		SURFACE TEXTURE: 		APVD: 22FEB2012						
P	LTR	REVISION RECORD	DATE	DWN	APVD	SCALE: -	SIZE: A1	DRAWING NO: 1583000	SHEET: 2 of 2	REV: C1