

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

42410-9082

Status:

Active

Overview:

Modular Plugs - Jacks

Description:

Modular Jack, Vertical, 8/4

Documents:

3D Model

Drawing (PDF)

Product Specification PS-42410 (PDF)

Test Summary TS-42878-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

42410

Comments

Flush Mount|Flangeless|2 PCB Thick

Component Type

PCB Jack

Magnetic

No

Overview

Modular Plugs - Jacks

Performance Category

3

Power over Ethernet (PoE)

N/A

Product Name

RJ45

UPC

800753820838

Physical

Color - Resin

Black

Durability (mating cycles max)

500

Flammability

94V-0

Inverted / Top Latch

N/A

Jack Height

16.38mm

Lightpipes/LEDs

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

Polyester

Orientation

Vertical (Top Entry)

PCB Retention

Yes

PCB Thickness - Recommended

3.20mm

Packaging Type

Tray

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Ports

1

Positions / Loaded Contacts

8/4

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40°C to +80°C

Termination Interface: Style

Through Hole

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact

1.5A

Shielded

No

Voltage - Maximum

125V

Solder Process Data

Duration at Max. Process Temperature (seconds)

5




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

42410Series

Mates With

FCC 68 Plugs

Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Product Specification	PS-42410
Sales Drawing	SDA-42410-****
Test Summary	TS-42878-001

This document was generated on 10/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[42410-9082](#)