

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	PN 215298-4 AND 1-215298-3 REACTIVATED	13NOV2017	KJK	PS




POS.	L	PART NUMBER	
-	-	-	
2	5.08	215 298-2	
3	7.62	-3	OBSOLETE
4	10.16	-4	
5	12.70	-5	
6	15.24	-6	
7	17.78	-7	
8	20.32	-8	
9	22.86	-9	OBSOLETE
10	25.40	1-	OBSOLETE
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3
14	35.56	1-	-4
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6
27	68.58	2-	-7
28	71.12	2-	-8
29	73.66	2-	-9
30	76.20	3-	-0
31	78.74	3-	-1
32	81.28	3-	-2
33	83.82	3-	-3
34	86.36	3-	-4
35	88.90	3-	-5
36	91.44	3- 215 298-6	

NOTES:

- TO DETERMINE DIMENSIONS TAKE N = NO. OF POS.  
FOR EXAMPLE: 10 POS.: N x 2,54 = 25,4 mm.  
FOR ORDER NO. USE BASIC NO. + NO. OF POS.  
FOR EXAMPLE: 2 POS.= 215 298-2 (SHORTEST VERSION)  
36 POS.= 3-215 298-6 (LONGEST VERSION)
- HOUSING MATERIAL: GREEN GLASSFILLED POLYESTER,  
UL 94V-0  
CONTACT MATERIAL: PHOSPHOR BRONZE.
- PLATING: 2.5-4.0µm TIN OVER MIN 0.5µm NICKEL
- MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
- CONTACT-POINT.
- RECOMMENDED P.C.BOARD-THICKNESS: 1,6mm.
- RETENTION FEATURE.
- RETENTION FORCE MUST BE MIN. 5N PER CONTACT
- HV100 CONNECTOR PACKED IN ANTISTATIC BLISTER TRAY



P.C.-BOARD HOLE-PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HO 24.02.89	 TE Connectivity		
		CHK M.SCHAARSCHMIDT 24.02.89			
		APVD G.FELDMEIER -	NAME		
DIMENSIONS: mm		PRODUCT SPEC 108-19056	HV 100 VERTICAL CONNECTOR SINGLE ROW, 7,0mm HEIGHT, TOP ENTRY, TIN, MAX, 36 POS		
		APPLICATION SPEC -			
MATERIAL SEE NOTES		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-215298
		FINISH SEE NOTES	RESTRICTED TO -		
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1
				REV E2	