

Customer Information Sheet

DRAWING No.: SI751-XXR


IF IN DOUBT - ASK

©





NOT TO SCALE

THIRD ANGLE PROJECTION



ALL DIMENSIONS IN mm



RECOMMENDED PAD LAYOUT
TOLERANCE ± 0.05 mm



SPECIFICATIONS:
MATERIAL = BRASS
FINISH:
46 = 4 μ m 100% TIN
ELECTRICAL:
CURRENT RATING = 2A MAX
CONTACT RESISTANCE = 20m Ω MAX
ENVIRONMENTAL:
OPERATING TEMPERATURE = -55°C TO +125°C



- NOTES:
- QUANTITY PER REEL = 2,500.
 - THIS PRODUCT IS TAPED AND REELED IN ACCORDANCE WITH EIA-481-2-A (ELECTRONIC INDUSTRIES ASSOCIATION).
 - FOR LOOSE COMPONENTS, SEE SI751-XX.

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ± 1 mm
X.X = ± 0.50 mm
X.XX = ± 0.20 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
SURFACE MOUNT TEST TERMINAL
(TAPE AND REELED)
DRAWING NUMBER:
SI751-XXR
SHT 2 OF 2

LW	10	15.02.23	32287
NAME	ISS.	DATE	CN/CO
APPROVED:		L. WALKER	
CHECKED:		A. BOXALL	
DRAWN:		W. J. BOURNE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

ORDER CODE	FINISH
SI751-46R	100% TIN