

f	6	6	6	6	6	6	6	6	6	6				6	6	6	6	6	6	6	6	6	6	6		
e	6	5	5	5	5	5	5	5	5	5				5	5	5	5	5	5	5	5	5	5	5	6	
d	6	5	5	5	5	5	5	5	5	5				5	5	5	5	5	5	5	5	5	5	5	6	
c	6	6	6	6	6	6	6	6	6	6				6	6	6	6	6	6	6	6	6	6	6	6	
b	5	5	5	5	5	5	5	5	5	5				5	5	5	5	5	5	5	5	5	5	5	5	
a	6	5	5	5	5	5	5	5	5	5				5	5	5	5	5	5	5	5	5	5	5	6	
z	6	6	6	6	6	6	6	6	6	6				6	6	6	6	6	6	6	6	6	6	6	6	
P	0					0					1					1					2					2
O	1					5					0					5					0					5
S																										

Technical drawing showing two types of connectors, labeled 5 and 6, with their dimensions and a seating plane.

Connector 5 dimensions:

- Overall length: 9.70
- Seating plane to tip distance: 3.70

Connector 6 dimensions:

- Overall length: 11.20
- Seating plane to tip distance: 3.70

A vertical line indicates the SEATING PLANE FOR CONNECTOR.

Technical drawing of a perforated metal plate. The plate has a total width of 40.00 (20.00 + 8.00 + 20.00) and a total height of 12.00. The left section (20.00 wide) has a 2.00 wide edge and a 2.00 wide gap between the first and second rows of holes. The right section (20.00 wide) has a 4.00 wide gap between the first and second rows of holes and a 2.00 wide edge. The holes are arranged in a grid. A detail callout shows a hole with a diameter of $\phi 2.00$ and a depth of $+0.05$ to -0 .

LEAD FREE INDICATOR : LF = LEAD FREE
(DIGIT 15 & 16)

PLATING CODE (DIGIT 13 AND 14)
(REF DRW NO. BS,C , 201844 , 003)

1. THIS PRODUCT IS CSA APPROVED.
2. THIS PRODUCT IS UL RECOGNIZED.
3. MEASURED AT THE BOTTOM.
4. MATERIAL CONTACT: PHOSPHORBRONZE
HOUSING: CREAM WHITE GLASS FILLED POLYESTER UL-94V0
5. CONNECTOR PRINTED WITH P/N AND DATE CODE.
6. FOR ACTUAL CONTACT LOADINGS, SEE LOADING PATTERN MATING SIDE.
7. SHAPE OF CONNECTOR HOUSING CAN ALTER DEPENDING ON
PRODUCTION LOCATION
8. THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008
9. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BS, A , 201572 , 001

CATALOG NO: HM2P07PDW2N1----

[illegible]