

PROVISIONAL

PD - 94239

International
IR Rectifier


IRGPS60B120KD

INSULATED GATE BIPOLAR TRANSISTOR
WITH ULTRAFAST SOFT RECOVERY DIODE

Motor Control CoPack IGBT

Features

- Low $V_{CE(on)}$ Non Punch Through IGBT Technology
- Low Diode V_F
- 10 μ s Short Circuit Capability
- Square RBSOA
- Ultrasoft Diode Reverse Recovery Characteristics
- Positive $V_{CE(on)}$ Temperature Coefficient
- Super-247 Package



$$V_{CES} = 1200V$$

$$V_{CE(on) \text{ typ.}} = 2.5V$$

$$@V_{GE} = 15V, I_C = 60A$$

$$T_J = 25^\circ C$$

Benefits

- Benchmark Efficiency for Motor Control
- Rugged Transient Performance
- Low EMI
- Excellent Current Sharing in Parallel Operation



Super-247™

Absolute Maximum Ratings

	Parameter	Max.	Units
V_{CES}	Collector-to-Emitter Voltage	1200	V
$I_C @ T_C = 25^\circ C$	Continuous Collector Current	120	A
$I_C @ T_C = 100^\circ C$	Continuous Collector Current	60	
I_{CM}	Pulsed Collector Current	240	
I_{LM}	Clamped Inductive Load Current	240	
$I_F @ T_C = 25^\circ C$	Diode Continuous Forward Current	120	
$I_F @ T_C = 100^\circ C$	Diode Continuous Forward Current	60	
I_{FM}	Diode Maximum Forward Current	240	V
V_{GE}	Gate-to-Emitter Voltage	± 20	
$P_D @ T_C = 25^\circ C$	Maximum Power Dissipation	595	W
$P_D @ T_C = 100^\circ C$	Maximum Power Dissipation	238	
T_J	Operating Junction and	-55 to +150	$^\circ C$
T_{STG}	Storage Temperature Range		
	Soldering Temperature, for 10 sec.	300 (0.063 in. (1.6mm) from case)	

Thermal Resistance

	Parameter	Min.	Typ.	Max.	Units
$R_{\theta JC}$	Junction-to-Case - IGBT	—	—	0.21	$^\circ C/W$
$R_{\theta JC}$	Junction-to-Case - Diode	—	—	0.41	
$R_{\theta CS}$	Case-to-Sink, flat, greased surface	—	0.24	—	
$R_{\theta JA}$	Junction-to-Ambient, typical socket mount	—	—	40	
Wt	Weight	—	6.0	—	g (oz)
L_E	Internal Emitter Inductance	—	13	—	nH

PROVISIONAL

IRGPS60B120KD

International
IR Rectifier

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ	Max	Units	Conditions	Ref. Fig.
V _{(BR)CES}	Collector-to-Emitter Breakdown Voltage	1200			V	V _{GE} = 0V, I _C = 500 μA	
ΔV _{(BR)CES} / ΔT _J	Temperature Coeff. of Breakdown Voltage		0.4		V/°C	V _{GE} = 0V, I _C = 1 mA (25 -125 °C)	
V _{CE(on)}	Collector-to-Emitter Saturation Voltage		2.33		V	I _C = 50A, V _{GE} = 15V	
			2.50	2.75		I _C = 60A, V _{GE} = 15V	
			2.79			I _C = 50A, V _{GE} = 15V, T _J = 125°C	
			3.04	3.50		I _C = 60A, V _{GE} = 15V, T _J = 125°C	
V _{GE(th)}	Gate Threshold Voltage	4.0	5.0	6.0	V	V _{CE} = V _{GE} , I _C = 250 μA	
	Temperature Coeff. of Threshold Voltage		-12		mV/°C	V _{CE} = V _{GE} , I _C = 1 mA (25 -125 °C)	
g _{fe}	Forward Transconductance		34.4		S	V _{CE} = 50V, I _C = 60A, PW = 80μs	
I _{CES}	Zero Gate Voltage Collector Current		20		μA	V _{GE} = 0V, V _{CE} = 1200V	
			650			V _{GE} = 0V, V _{CE} = 1200V, T _J = 125°C	
V _{FM}	Diode Forward Voltage Drop		1.82		V	I _F = 50A	
			1.93	2.30		I _F = 60A	
			1.96			I _F = 50A, T _J = 125°C	
			2.13	2.50		I _F = 60A, T _J = 125°C	
I _{GES}	Gate-to-Emitter Leakage Current			±100	nA	V _{GE} = ±20V	

Switching Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions	Ref. Fig.
Q _g	Total Gate charge (turn-on)		340		nC	I _C = 60A	
Q _{ge}	Gate - Emitter Charge (turn-on)		40			V _{CC} = 400V	
Q _{gc}	Gate - Collector Charge (turn-on)		165			V _{GE} = 15V	
E _{on}	Turn-On Switching Loss		3214		μJ	I _C = 60A, V _{CC} = 600V	
E _{off}	Turn-Off Switching Loss		4783			V _{GE} = 15V, R _g = 4.7Ω, L=200μH, L _S =150nH	
E _{tot}	Total Switching Loss		8000			T _J = 25°C, Energy losses include tail and diode reverse recovery	
td(on)	Turn - on delay time		76		ns	I _C = 60A, V _{CC} = 600V	
tr	Rise time		46			V _{GE} = 15V, R _g = 4.7Ω, L=200μH, L _S =150nH	
td(off)	Turn - off delay time		320			T _J = 25°C,	
tf	Fall time		37				
E _{on}	Turn-on Switching Loss		5032		μJ	I _C = 60A, V _{CC} = 600V	1
E _{off}	Turn-off Switching Loss		7457			V _{GE} = 15V, R _g = 4.7Ω, L=200μH, L _S =150nH	2
E _{tot}	Total Switching Loss		12500			T _J = 125°C, Energy losses include tail and diode reverse recovery	3
td(on)	Turn - on delay time		80		ns	I _C = 15A, V _{CC} = 600V	
tr	Rise time		48			V _{GE} = 15V, R _g = 4.7Ω, L=200μH, L _S =150nH	
td(off)	Turn - off delay time		340			T _J = 125°C,	
tf	Fall time		47				
C _{ies}	Input Capacitance		4400		pF	V _{GE} = 0V	
C _{oes}	Output Capacitance		420			V _{CC} = 30V	
C _{res}	Reverse Transfer Capacitance		170			f = 1.0 MHz	
RBSOA	Reverse bias safe operating area	FULL SQUARE				T _J = 150°C, I _C = 240A V _{CC} = 1000V, V _P = 1200V R _g = 4.7Ω, V _{GE} = +15V to 0 V	
SCSOA	Short Circuit Safe Operating Area	10	----	----	μs	T _J = 150°C V _{CC} = 900V, V _P = 1200V R _g = 22Ω, V _{GE} = +15V to 0 V	
E _{rec}	Reverse recovery energy of the diode		3780		μJ	T _J = 125°C	
t _{rr}	Diode Reverse recovery time		165		ns	V _{CC} = 600V, I _F = 60A	
I _{rr}	Peak Reverse Recovery Current		51		A	V _{GE} = 15V, R _g = 4.7Ω, L=200μH, L _S =150nH	







Fig.3 - Switching Loss Circuit



IRGPS60B120KD

Super-247™ Package Outline



Data and specifications subject to change without notice.
This product has been designed and qualified for the Industrial market.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903
Visit us at www.irf.com for sales contact information.6/01