


HIGH VOLTAGE SCHOTTKY BARRIER DIODE

■ Outline drawings, mm




■ Features

- High voltage
- Low V_F
- Super high speed switching
- High reliability by planer design

■ Applications

- High speed switching

■ Marking



■ Maximum ratings and characteristics

- Absolute maximum ratings ($T_c=25^\circ\text{C}$ Unless otherwise specified)






Item	Symbol	Conditions	Rating	Unit
Repetitive peak reverse voltage	V_{RRM}		150	V
Average forward current	I_{FAV}	Square wave duty=1/2 $T_l=102^\circ\text{C}$	4.0	A
Non-repetitive forward surge current	I_{FSM}	Sine wave 10ms, 1shot	110	A
Operating junction temperature	T_j		150	$^\circ\text{C}$
Storage temperature	T_{stg}		-40 to +150	$^\circ\text{C}$

- Electrical characteristics ($T_c=25^\circ\text{C}$ Unless otherwise specified)

Item	Symbol	Conditions	Max.	Unit
Forward voltage	V_F	$I_{FM}=4.0\text{A}$	0.9	V
Reverse current	I_R	$V_R=V_{RRM}$	150	μA

- Mechanical characteristics

Approximate mass	1.2	g
------------------	-----	---

■ Characteristics**Forward Characteristic (typ.)****Reverse Characteristic (typ.)****Forward Power Dissipation (max.)****Reverse Power Dissipation (max.)****Current Derating ($I_{F(AV)}-T_L$) (max.)****Junction Capacitance Characteristic (typ.)**