




PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 mΩ MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : 10⁴ MΩ MIN

NOTES

1. " " LEAD FREE INDICATOR :LF=LEAD FREE
" " PERFORMANCE LEVEL INDICATION (REF DWG NO.BSC .201844.003)
2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 00	KN	14-09-01
B	104-0114	ALEX E	27.11.04
C	DG05-0297	Kason	05-08-05
D	DG06-0254	Kason	06-27-06
E	DG10-0110	NZ	2010.9.3
-	-	-	-
-	-	-	-

Material			Spec ref					
Mat code			✓	tolerance	projection	MM ↔		
Heat treat				1DEC±0.2 1DEC 2DEC±0.1 2DEC ANGLE±1° HOEKEN				
Plating/Finish								
Dr	M.Fret	31-10-97	size A4			Scale 2.000		
Eng			Product family					
Chr			Model Name HM2S30PE5101			ECN		
Appr			Model Revision			REL Level		
		title	MILLIPACS 2/TYPE C(W/O LOCK.PEG) SHIELDED			dwg no	BSC201907010	Rev. E
Pro/E file		catalog no	HM2S30PE5101----			CUMSTOMER DRAWING		sheet 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[61083-161400LF](#)