

PRODUCT NUMBER
75160-YXX-XXLF

RoHS COMPLIANT & COMPATIBLE, SEE NOTE 8

TOTAL NB OF POSITIONS 02 TO 36

PIN STYLE SEE SHEET 2

PLATING:

1 = 0.76µm FULL GOLD/GXT

3 = 2µm MIN MATTE TIN FULL PLATED

8 = 0.38µm FULL GOLD/GXT

1.27µm MIN NICKEL UNDERPLATING

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC
FLAME RETARDANT PER UL94-VO, COLOR BLACK.

2. PIN MATERIAL : PHOSPHOR BRONZE.

3. DIM 1.27^{+0.03}_{-0.13} FOR MOULDED SIDE(S)
ONLY. IF SIDE(S) ARE BROKEN, DIM 1.02
TO 1.7 MAX APPLIES.

4. PIN PUSH OUT FORCE : 12N MIN.

5. PRODUCT PACKAGED IN POLY BAGS.

6. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS
EXAMPLE : 8 POS N x 2.54 = 20.32mm

7. FOR STANDARD SELECTIVE GOLD PLATED
PRODUCTS, SEE DRAWING 77311.

8. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - "LF" MEANS THE PRODUCT IS LEAD-FREE




b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface		tolerance		projection	product family		
SEE NOTES				ISO 1302 ✓		ISO 406 ISO 1101			BERGSTIK		
ltr	ecr no	dr	date	tolerances unless otherwise specified						title	
BR	F20607	LMU	03.12.03	angles	linear	.x ±0.3		scale 5:1			HEADER SR,STR 2.54mm PITCH
BS	F03079	LMU	03.04.04			.xx ±0.15					
BT	F05-0186	JCO	05.04.29			xxx ±0.05					
BU	F06-0196	LMU	06.06.20	dr	D LEGRAND	02.01.15			dwg no	sheet 1 of 2	size
BV	F08-0148	JCO	08.05.27	enr	JMC	02.01.15			75160	A3	
BW	B-19264	LMU	14.10.31	chr	COMPAGNON	02.01.15					
				appd	JMC	02.01.15			type	CUSTOMER	Drawing
sheet index	revision	BW	BK								
	sheet		2								



FCIconnect.com


Copyright FCI

form: A3

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
01		5.72	2.54	10.8
02		5.84	3.43	11.81
03		5.72	5.09	13.34
04		5.72	7.62	15.88
05		5.72	10.16	18.42
06		5.72	12.7	20.96
07		5.72	15.24	23..5
08		5.72	17.78	26.04
09		5.72	20.32	28.58
10		5.72	22.86	31.12
11		5.72	5.97	14.22
12		5.72	8.51	16.76
13		5.72	11.05	19.3
14		5.72	16.13	24.38
15		8.51	2.54	13.59
16		8.51	5.51	16.56
17		8.51	10.59	21.64
18		5.72	3.05	11.3
19		12.83	3.05	18.42
20		15.37	3.05	20.96
21		20.45	3.05	26.04
22		7.75	3.05	13.34
23		5.84	4.95	13.34
24		7.21	3.05	12.8
25		8.51	3.18	14.22
26		15.57	2.84	20.96

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
27		6.6	2.67	11.81
28		6.6	4.19	13.34
29		17.53	3.43	23.5
30		22.61	3.43	28.58
31		8.2	2.84	13.59
32		10.29	3.05	15.88
35		25.21	3.37	31.12
38		5.84	3.81	12.19
39		11.17	3.05	16.76
41		4.99	2.8	10.33
43		6.98	4.8	14.32
44		12.27	3.35	18.16
46		8.08	2.72	13.34
48		5.84	2.42	10.8
50		5.84	3.12	11.5
56		5.72	3.05	11.3
61		16.61	3.2	22.35
62		13.5	3.05	19.09
70		6.54	3.5	12.57
73		28.4	3.18	34.12
75		16.47	10.3	29.31
79		3.3	3.3	9.14
80		8.07	2.2	12.81
90		1.9	3.56	8
95		15.96	4	22.5
96		5.84	3.43	11.81

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
97		7.75	3.05	13.34
98		10.29	3.05	15.88



mat'l. code SEE P/N				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
BH	F05-0186	JCO	05.04.29	angles	.x ±0.3	mm	HEADER STR,SR. 2.54mm PITCH
BJ	F06-0196	LMU	06.06.20	linear	.xx ±0.15		
BK	B-19264	LMU	14.10.31		xxx ±0.05	scale 5:1	dwg no
	F20301	LMU	02.04.23	dr	MULIN.L	99.04.07	sheet 2 of - size
				enfr	JMC	99.04.07	75160 A3
BF	F20607	LM	03.12.03	chr			type
BG	F03079	LMU	03.04.04	appd	JMC	99.04.07	CUSTOMER Drawing
sheet	revision						
index	sheet						