

# Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

**BELDEN**  
SENDING ALL THE RIGHT SIGNALS

83002 Hook-up/Lead - UL AWM Style 1213

For more Information  
please call

1-800-Belden1



## General Description:

Stranded silver-coated copper conductor insulation with extruded TFE Teflon.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	26	7x34	SPC - Silver Plated Copper

Total Number of Conductors: 1

### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
TFE - Tetrafluoroethylene	.010

### Overall Insulation

### Overall Cable

Overall Nominal Diameter: 0.039 in.

## Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 2 lbs/1000 ft.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

UL Rating: 105°C

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Military Specification: NEMA HP3, MIL-W-16878/4

MIL Spec Rating: 600 V, 200°C

### Flame Test

UL Flame Test: VW-1

### Plenum/Non-Plenum

Plenum (Y/N): No

# Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

83002 Hook-up/Lead - UL AWM Style 1213

## Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
37.500

Max. Operating Voltage - Other:

Voltage	Description
600 Vrms	Mil-W-16878/4

Max. Recommended Current:

Description	Current
Single conductor in free air @ 30C ambient	6 amps

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83002 001100	100 FT	0.200 LB	BROWN	E	#26 STR TFE BRN
83002 001100	1,000 FT	3.000 LB	BROWN	E S	#26 7/34 STR TFE BRN
83002 002100	100 FT	0.200 LB	RED	E	#26 STR TFE RED
83002 002100	1,000 FT	3.000 LB	RED		#26 7/34 STR TFE RED
83002 003100	100 FT	0.200 LB	ORANGE	E	#26 STR TFE ORG
83002 003100	1,000 FT	3.000 LB	ORANGE	E S	#26 7/34 STR TFE ORG
83002 004100	100 FT	0.200 LB	YELLOW	E	#26 STR TFE YEL
83002 004100	1,000 FT	3.000 LB	YELLOW	E S	#26 7/34 STR TFE YEL
83002 005100	100 FT	0.200 LB	GREEN, DARK	E	#26 STR TFE GRNDK
83002 005100	1,000 FT	3.000 LB	GREEN, DARK	E S	#26 7/34 STR TFE GRNDK
83002 006100	100 FT	0.200 LB	BLUE, LIGHT	E	#26 STR TFE BLULT
83002 006100	1,000 FT	3.000 LB	BLUE, LIGHT	E S	#26 7/34 STR TFE BLULT
83002 007100	100 FT	0.200 LB	VIOLET	E	#26 STR TFE VIO
83002 007100	1,000 FT	3.000 LB	VIOLET	E	#26 7/34 STR TFE VIO
83002 008100	100 FT	0.200 LB	GRAY	E	#26 STR TFE GRY
83002 008100	1,000 FT	3.000 LB	GRAY	E S	#26 7/34 STR TFE GRY
83002 009100	100 FT	0.200 LB	WHITE	E	#26 STR TFE WHT
83002 009100	1,000 FT	3.000 LB	WHITE		#26 7/34 STR TFE WHT
83002 010100	100 FT	0.200 LB	BLACK	E	#26 STR TFE BLK
83002 010100	1,000 FT	3.000 LB	BLACK	E	#26 7/34 STR TFE BLK

**Notes:**

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

S = STRIPPING ADDERS FOR TYPES E AND EE: 123 STRIPES. MINIMUM ORDER 10

Revision Number: 2 Revision Date: 05-13-2013

© 2013 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable](#):

[83002 0061000](#) [83002 0041000](#) [83002 0101000](#) [83002 0011000](#) [83002 0051000](#)