

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

83267 Coax - 75 Ohm Coax

For more Information
please call

1-800-Belden1



Description:

75 ohm, 30 AWG stranded (7x38) .012" silver-plated copper-covered steel conductor, TFE Teflon® insulation, silver-plated copper braid shield (95% coverage), TFE tape jacket.

Physical Characteristics (Overall)

Conductor

AWG:

#	Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1		30	7x38	SPCCS - Silver Plated Copper Covered Steel	.012

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Teflon®	TFE - Tetrafluoroethylene	.063

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	SPC - Silver Plated Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Teflon®	TFE - Tetrafluoroethylene

Overall Cable

Overall Nominal Diameter: 0.105 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Non-UL Temperature Rating: 200°C

Bulk Cable Weight: 10 lbs/1000 ft.

Max. Recommended Pulling Tension: 18 lbs.

Min. Bend Radius/Minor Axis: 1 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

83267 Coax - 75 Ohm Coax

MII Order #39 (China RoHS):	Yes
Military Specification:	MIL-C-17D
RG Type:	187A/U

Flame Test

UL Flame Test:	VW-1
----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75.000

Nom. Inductance:

Inductance (μ H/ft)
0.10

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
19.5

Nominal Velocity of Propagation:

VP (%)
69.5

Nominal Delay:

Delay (ns/ft)
1.44

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
244

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
8.6

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	3.0
10	5.3
50	8.5
100	10.0
200	12.5
400	16.0
700	19.7
900	22.3
1000	24.0

Max. Operating Voltage - Non-UL:

Voltage
900 V RMS

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83267 009100	100 FT	1.900 LB	WHITE	E	#30 COAX RG-187A/U
83267 0091000	1,000 FT	11.000 LB	WHITE	E	#30 COAX RG-187A/U

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

83267 Coax - 75 Ohm Coax

Notes:

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 1 Revision Date: 09-20-2012

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[83267 0091000](#)