


HC/49US (AT49) MICROPROCESSOR CRYSTAL

ABL Series

Moisture Sensitivity Level (MSL) –This product is Hermetically Sealed
and not Moisture Sensitive -MSL = N/A: Not Applicable



RoHS
Compliant



11.5 x 5.0 x 3.5 mm

FEATURES:

- High reliability & Low Cost
- Tight stability & extended temperature
- Reliable resistance welded metal package

APPLICATIONS:


- Home electronics
- Computers, modems, and communications
- Automotive and industrial
- High-precision TCXO and clock applications
- Microprocessors

STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	3.579545	-----	70		
Operation mode	3.579545	-----	24.0	MHz	Fundamental AT-cut (Standard)
	24.01	-----	70.00		3 rd OT AT-cut (Standard)
	24.01	-----	50.00		Fundamental AT-cut or BT-cut (See options)
Operating Temperature	0	-----	+70	°C	See options
Storage Temperature	-55	-----	+125	°C	-----
Frequency Tolerance	-50	-----	+50	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)	-50	-----	+50	ppm	See options
Equivalent series resistance (R1)	See table 1 below			Ω	-----
Shunt capacitance (C0)	-----	-----	7	pF	-----
Load capacitance (CL)	-----	18	-----	pF	See options
Drive Level	-----	100	1000	μW	-----
Aging @ 25°C per year	-----	-----	±5	ppm	-----
Insulation Resistance	500	-----	-----	MΩ	@ 100Vdc ± 15V
Drive Level Dependency (DLD, Minimum 7 points tested: from 1μW to 500μW)	-----	-----	±10	ppm	Δfrequency (Max – Min)
	-----	-----	25% of Max ESR	Ω	ΔESR (Max – Min)
	-----	-----	Max ESR in Table 1	Ω	Max ESR over DLD range

Table 1

Frequency (MHz)	ESR(Ω) max.
3.579 - 4.999 (Fund.)	180
5.000 - 5.999 (Fund.)	120
6.000 - 7.999 (Fund.)	100
8.000 - 8.999 (Fund.)	80
9.000 - 9.999 (Fund.)	60
10.000 - 15.999 (Fund.)	50
16.000 - 50.000 (Fund.)	40
24.01 - 31.999 (3rd O/T)	100
32.000 - 70.00 (3rd O/T)	80



HC/49US (AT49) MICROPROCESSOR CRYSTAL

ABL Series



RoHS
Compliant



11.5 x 5.0 x 3.5 mm

OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)

ABL - MHz - - - - - -

Frequency in MHz

Please specify the frequency in xx.xxxxMHz.
e.g. 14.3181MHz

Load Capacitance (pF)

Please specify CL
(Minimum 10pF) in pF or
S for series

Custom ESR if other than standard

R
: Specify a value in Ω
(e.g.: R40)

Packaging

Blank: Bulk
T: Tape & Reel
P: Foam
TRAY: Tray

Value Added

I	Insulator Tab
L2	Middle 3rd lead
QXX	Trimmed leads
Q15	for 0.15" length

Oscillation Mode

F: Fund. AT>24MHz
FB: Fund. BT>24MHz

Operating Temp.

A: -10°C ~ +60°C
B: -20°C ~ +70°C
C: -30°C ~ +70°C
N: -30°C ~ +85°C
D: -40°C ~ +85°C
J*: -40°C ~ +105°C
K*: -40°C ~ +125°C
L*: -55°C ~ +125°C

Freq. Tolerance

H5: ± 5 ppm
1: ± 10 ppm
7: ± 15 ppm
2: ± 20 ppm
3: ± 25 ppm
4: ± 30 ppm

Freq. Stability

U**: ± 10 ppm
G: ± 15 ppm
X: ± 20 ppm
W: ± 25 ppm
Y: ± 30 ppm
H: ± 35 ppm
Q: ± 100 ppm
R: ± 150 ppm

NOTE:

* Frequency stability ± 50 ppm, ± 100 ppm, ± 150 ppm only. Contact ABRACON for tighter frequency stability.

** -10 to +60C only.

ABRACON IS
ISO 9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 12.13.11

HC/49US (AT49) MICROPROCESSOR CRYSTAL

ABL Series




RoHS
Compliant



11.5 x 5.0 x 3.5 mm

OUTLINE DRAWING:




L	Packaging
12.8mm Min	Bulk
20.0 $\pm$ 0.5mm	Tape & Reel

Dimensions: inch (mm)

TAPE & REEL:

T= Tape and reel (1,000pcs/reel)



Dimensions: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO 9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 12.13.11