

PANDUIT PART NUMBER	WIRE RANGE mm (AWG)	COLOR CODE	DIMENSIONS mm		STRIP LENGTH +0,8 (+1/32) -0 (-0)
			A ± ^{0,8} (.03)	B	
DMV1-63MB-3K	0,5-1,5 (22-18)	RED	22,9 (.90)	3,9 (.16)	7,1 (9/32)
DMV2-63MB-3K	1,5-2,5 (16-14)	BLUE	22,9 (.90)	4,5 (.18)	7,1 (9/32)
* DMV6-63M-2K	4,0-6,0 (12-10)	YELLOW	24,4 (.96)	6,1 (.24)	8,7 (11/32)

1. CSA CERTIFIED FOR :
 - A. 600 V MAX. VOLTAGE RATING
 - B. 90°C (194°F) MAX. TEMP. RATING OF INSULATION
 - C. STRANDED AWG COPPER WIRE ONLY
2. MATERIAL :
 - A. STAMPING - 0,8 (.03) THK COPPER, TIN PLATED
 - B. HOUSING - VINYL
3. DIMENSIONS IN BRACKETS ARE IN INCHES
- 4) PACKAGE QUANTITY: 3K= 3000 PCS, 2K= 2,000 PCS



Technical drawing of a terminal assembly. The drawing shows a cross-section of the assembly with the following dimensions and labels:

- Dimensions:**
 - Top width: 7,4 (.29)
 - Inner width: 6,4 (.25)
 - Overall height: A
 - Bottom width: B MAX
- Labels:**
 - TERMINAL**: Points to the top cylindrical part of the assembly.
 - HOUSING**: Points to the central cylindrical part of the assembly.
 - CARRIER STRIP (CONFIGURATION MAY VARY)**: Points to the bottom part of the assembly.
 - FUNNEL WIRE ENTRY**: Points to the bottom part of the assembly.
 - WIRE INSUL DIA**: Points to the bottom part of the assembly.

		PANDUIT PRESS					
		CP-851 <i>DISCONTINUED</i>	CP-860 <i>DISCONTINUED</i>	CP-861	CP-862	CP-871 <i>60HZ</i>	CP-871/E <i>50HZ</i>
APPLICATORS	CA-800		X	X			
	CA-800EZ	X				X	X
	CA9				X	X	X

								 TINLEY PARK, ILLINOIS			
01	3/06	DAW	DAW	ADDED PANDUIT PRESS & APPLICATOR CHART	TR00083			REELSMART™, DISCO™ 2 PC. METRIC VINYL INSULATED, 6,3 X 0,8 MALE TAB			
00	9/97	TM	WJB	RELEASED	6192	LA	DBH				
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	PM	DRAWN BY TSM	CHK'D	SCALE NONE	DRAWING NO. A41629