

71918-YXXZZLF

71918-YXXZZLF

RoHS COMPATIBLE, SEE NOTE 10

- S= SPECIFIC CUSTOMER PLATING OPTION.

— COLOR OPTION, SEE NOTE 1

- TOTAL NB OF POSITIONS, SEE SHEET 2

-LATCHING





0= WITHOUT LATCH

1= STANDARD LATCH

2= LOW PROFILE LATCH

NOTES:

- 1 - HOUSING MATERIAL: GLASS FILLED THERMOPLASTIC UL94V-0  
= STANDARD COLOR GREY  
B = OPTION COLOR BLACK
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES
- 4 - 40N MIN LATCH RETENTION FORCE  
AT FIRST EXTRACTION
- 5 - TO DETERMINE DIMENSIONS :  
N = NUMBER OF POSITIONS PER ROW  
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 6 - NO CENTRAL SLOT ON POSITIONS 6 & 8
- 7 - NO LEFT POLARIZATION ON POSITIONS 06, 08, 10, 14.
- 8 - NO GROOVE ON POSITIONS 06, 08, 10, 14, 30, 34
- 9 - 4.5mm SOLDER TAIL  
ORDER 71918-4XX (WITH STANDARD LATCH ONLY)
- 10 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
  - a - PLATING:
    - "LF" MEANS THE PRODUCT IS LEAD-FREE,  
2µm MINIMUM MATTE TIN OVER 1.27µm  
MINIMUM NICKEL UNDERPLATE.
  - b - MANUFACTURING PROCESS COMPATIBILITY
    - THE HOUSING WILL WITHSTAND EXPOSURE TO  
260°C ±5°C SOLDER BATH TEMPERATURE FOR  
5 SECONDS IN A WAVE SOLDER APPLICATION  
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
  - c - LABELING:
    - MEETS PACKAGING SPECS AS PER GS-14-920
  - d - LEGAL STATEMENT: SEE GS-47-0004.

[illegible]

| PRODUCT NUMBER | SIZE | LATCHING AVAILABILITY | MISSING PIN POSITIONS |
|----------------|------|-----------------------|-----------------------|
| 71918-X06(B)LF | 2x3  | 0/1/2                 |                       |
| 71918-X08(B)LF | 2x4  | 0/1/2                 |                       |
| 71918-X10(B)LF | 2x5  | 0/1/2                 |                       |
| 71918-X14(B)LF | 2x7  | 0/1/2                 |                       |
| 71918-X16(B)LF | 2x8  | 0/1/2                 |                       |
| 71918-X18(B)LF | 2x9  | 0/1/2                 |                       |
| 71918-X20(B)LF | 2x10 | 0/1/2                 |                       |
| 71918-X26(B)LF | 2x13 | 0/1/2                 |                       |
| 71918-X27(B)LF | 2x13 | 0/1/2                 | PIN 21 & 22           |
| 71918-X28(B)LF | 2x13 | 0/1/2                 | PIN 5 to 12           |
| 71918-X30(B)LF | 2x15 | 0/1/2                 |                       |
| 71918-X34(B)LF | 2x17 | 0/1/2                 |                       |
| 71918-X35(B)LF | 2x17 | 0/1/2                 | PIN 2 & 3             |
| 71918-X40(B)LF | 2x20 | 0/1/2                 |                       |
| 71918-X44(B)LF | 2x22 | 0/1/2                 |                       |
| 71918-X50(B)LF | 2x25 | 0/1/2                 |                       |
| 71918-X51(B)LF | 2x25 | 0/1/2                 | PIN 39 to 46          |
| 71918-X60(B)LF | 2x30 | 0/1/2                 |                       |
| 71918-X64(B)LF | 2x32 | 0/1/2                 |                       |

PLATING :


- 0.76µm GOLD/GXT (PdNi WITH GOLD FLASH) ON CONTACT AREA
- 2µm MIN MATTE TIN ON TAIL
- UNDERPLATE : 1.27µm Ni MIN

PIN 4    PIN POSITION INDICATION FOR POLARIZED VERSIONS

PIN 2


PIN 1

PIN 3



WHEN THE CONNECTORS NEED TO BE FIXED ON THE PCB'S  
THE STAINLESS SCREWS REF TC POZI DIN7981 Ø2.9 X 6.5MM  
TO BE USED

LATCHING FEATURES :



|             |          |       |     |          |                                       |            |                             |                       |
|-------------|----------|-------|-----|----------|---------------------------------------|------------|-----------------------------|-----------------------|
| mat'l. code |          |       |     | surface  | tolerance                             | projection | product family              |                       |
|             |          |       |     | ISO 1302 | ISO 406 ISO 1101                      |            | QUICKIE                     |                       |
| ltr         | ecn      | no    | dr  | date     | tolerances unless otherwise specified |            | title                       |                       |
| R           | F07      | -0195 | LMU | 07.05.25 | angles                                | .X ±0.3    | SHR.EL.HEADER<br>STR DR TMT |                       |
| S           | F08      | -0146 | YOV | 08.04.11 | linear                                | .XX ±0.15  |                             |                       |
| T           | F12      | -0011 | LMU | 12.02.06 |                                       | .XXX ±0.05 |                             |                       |
| U           | F12      | -0838 | LMU | 12.12.06 | dr                                    | D.LE       | 01.01.24                    | sheet 2 of - size     |
| V           | B-       | 16776 | LMU | 14.01.23 | engr                                  | JM.C       | 01.01.24                    | 71918 A3              |
| W           | B-       | 19091 | LMU | 14.10.16 | chr                                   | JF.N       | 01.01.24                    |                       |
| X           | B-       | 20412 | BVE | 15.03.10 | appd                                  | JM.C       | 01.01.24                    | type CUSTOMER Drawing |
| sheet       | revision |       |     |          |                                       |            |                             |                       |
| index       | sheet    |       |     |          |                                       |            |                             |                       |

