





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1888	B	Drawing Updated	JWM	7/7/06	HO	7/7/06	HO	7/7/06
1931	C	Dimension added	DCM	2/21/07	JWM	2/21/07	JWM	2/21/07



Max. Rating: 10A @ 250 VAC
Contact Resistance: <10 milliohm
Insulation Resistance: >1,000 Megohm
A.C. Breakdown: Pole-Pole 4.5 kV Pole-Accessible 4 kV
Operataing Temp: -40°C to 70°C
Withdrawal Force: 10N (Min), 50N (Max)
Material:
Moulding: Nylon, flammability rating UL94V-0
Contacts: Brass, Nickel Plated
Approvals: UL, CSA, VDE, SEV, BSI, SEMKO, SETI, and IMQ
For use with 18 AWG cordage

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	1/9/98
CHECKED BY:	DATE:
JOHN COLE	2/4/98
APPROVED BY:	DATE:
BRETT BRAATZ	2/5/98

DRAWING TITLE:

Rewirable Plug Assembly

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	2160	92N4163.dwg	C
SCALE: NTS		U.O.M.: IMillimeters	SHEET: 1 OF 1