



SAW Components

Data Sheet M 3568 M

Data Sheet



EPCOS

SAW Components
M 3568 M
IF Filter for Quasi/Split Sound Applications
45,75 MHz
Data Sheet
Standard
Plastic package SIP5K



- M/N

Features

- TV IF filter for quasi/split sound applications (separate picture and sound channel)
- Picture channel with Nyquist slope and sound suppression, symmetrical output
- Customized group delay predistortion
- Sound channel with passband for sound carrier only

Terminals


- Tinned CuFe alloy



Dimensions in mm, approx. weight 1,0 g

Pin configuration

1	Input
2	Chip carrier - ground
3	Output - sound
4	Output - picture
5	Output - picture



Type	Ordering code	Marking and package according to	Packing according to
M 3568 M	B39458-M3568-M201	C61157-A1-A15	F61074-V8067-Z000

Maximum ratings

Operable temperature range	T_A	-25/+65	°C	
Storage temperature range	T_{stg}	-40/+85	°C	
DC voltage	V_{DC}	12	V	between any terminals
AC voltage	V_{pp}	10	V	between any terminals



SAW Components	M 3568 M
IF Filter for Quasi/Split Sound Applications	45,75 MHz

Data Sheet

Characteristics of picture channel

Reference temperature: $T_A = 25 \text{ (45)}^\circ\text{C}$

Terminating source impedance: $Z_S = 50 \Omega$

Terminating load impedance: $Z_L = 2 \text{ k}\Omega \parallel 3 \text{ pF}$

		min.	typ.	max.	
Insertion attenuation	α				
Reference level for the following data	44,06 (44,00) MHz	12,3	13,8	15,3	dB
Relative attenuation	α_{rel}				
Picture carrier	45,81 (45,75) MHz	4,9	5,9	6,9	dB
Color carrier	42,23 (42,17) MHz	1,4	2,4	3,4	dB
Sound carrier	41,31 (41,25) MHz	34,0	43,0	—	dB
Adjacent picture carrier	39,81 (39,75) MHz	50,0	65,0	—	dB
Adjacent sound carrier	47,31 (47,25) MHz	42,0	52,0	—	dB
Lower sidelobe	35,06 ... 39,81 (35,00 ... 39,75) MHz	41,0	45,0	—	dB
Upper sidelobe	47,31 ... 55,06 (47,25 ... 55,00) MHz	36,0	42,0	—	dB
Reflected wave signal suppression					
1,2 μs ... 6,0 μs after main pulse (test pulse 250 ns, carrier frequency 44,06 MHz)		42,0	52,0	—	dB
Feedthrough signal suppression					
1,3 μs ... 1,2 μs before main pulse (test pulse 250 ns, carrier frequency 44,06 MHz)		50,0	56,0	—	dB
Group delay predistortion	$\Delta\tau$				
(reference frequency 45,75 MHz)					
	42,23 (42,17) MHz	—	50	—	ns
Group delay ripple (p-p)					
43,06 ... 45,81 (43,00 ... 45,75) MHz	$\Delta\tau$	—	40	—	ns
Impedance at 44,06 MHz					
Input: $Z_{\text{IN}} = R_{\text{IN}} \parallel C_{\text{IN}}$		—	1,1 \parallel 19,1	—	$\text{k}\Omega \parallel \text{pF}$
Output: $Z_{\text{OUT}} = R_{\text{OUT}} \parallel C_{\text{OUT}}$		—	1,6 \parallel 3,1	—	$\text{k}\Omega \parallel \text{pF}$
Temperature coefficient of frequency	TC_f	—	-72	—	ppm/K



SAW Components	M 3568 M
IF Filter for Quasi/Split Sound Applications	45,75 MHz

Data Sheet

Characteristics of sound channel

Reference temperature: $T_A = 25 (45) ^\circ\text{C}$

Terminating source impedance: $Z_S = 50 \Omega$

Terminating load impedance: $Z_L = 2 \text{ k}\Omega \parallel 3 \text{ pF}$

		min.	typ.	max.	
Insertion attenuation	α				
Reference level for the following data	41,31 (41,25) MHz	10,2	11,7	13,2	dB
Relative attenuation	α_{rel}				
Picture carrier	45,81 (45,75) MHz	38,0	50,0	—	dB
Color carrier	42,23 (42,17) MHz	13,0	16,0	—	dB
Adjacent picture carrier	39,81 (39,75) MHz	32,0	37,0	—	dB
Adjacent sound carrier	47,31 (47,25) MHz	40,0	50,0	—	dB
Lower sidelobe	35,06 ... 39,81 (35,00 ... 39,75) MHz	32,0	40,0	—	dB
Upper sidelobe	47,31 ... 55,06 (47,25 ... 55,00) MHz	38,0	42,0	—	dB
Impedance at 41,31 MHz	Output: $Z_{\text{OUT}} = R_{\text{OUT}} \parallel C_{\text{OUT}}$	—	3,3 \parallel 2,6	—	$\text{k}\Omega \parallel \text{pF}$
Temperature coefficient of frequency	TC_f	—	-72	—	ppm/K

SAW Components



M 3568 M

IF Filter for Quasi/Split Sound Applications

45,75 MHz

Data Sheet

Frequency response of picture channel



SAW Components


M 3568 M

IF Filter for Quasi/Split Sound Applications


45,75 MHz

Data Sheet

Frequency response of picture channel



Time domain response of picture channel





SAW Components


M 3568 M

IF Filter for Quasi/Split Sound Applications

45,75 MHz

Data Sheet

Frequency response of sound channel





SAW Components	M 3568 M
IF Filter for Quasi/Split Sound Applications	45,75 MHz

Data Sheet

Published by EPCOS AG
Surface Acoustic Wave Components Division, SAW CE MM PD
P.O. Box 80 17 09, D-81617 München

© EPCOS AG 2001. All Rights Reserved.

As far as patents or other rights of third parties are concerned, liability is only assumed for components per se, not for applications, processes and circuits implemented within components or assemblies.

The information describes the type of component and shall not be considered as assured characteristics.

Terms of delivery and rights to change design reserved.

For questions on technology, prices and delivery please contact the sales offices of EPCOS AG or the international representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our sales offices.