






	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

Female



- NOTES:**
- MATERIAL**
1. Insulator Material: Glass-Filled Thermoplastic PBT, UL 94V-0
 2. Contact Material : Copper alloy
 3. Shell : SPC
 4. Plating : Selective Gold Flash
- ELECTRICAL**
1. Current Rating : 3 AMP
 2. Voltage Rating : 250 V AC/rms 60 Hz
 3. Contact Resistance: 20mΩ max at 1 AMP DC
 4. Insulation Resistance: 1000MΩ at 500 VDC
 5. Withstand Voltage : 1000V AC/rms 60Hz for 1 minute
 6. Wire Spec: 26 AWG-28 AWG
 7. Operating temperature: -55 °C+105°C
- UL E No #E198287

Cover



Strain Relief

Dimensions						
Positions	A	B	D	E	F	
9	30.61	24.99	16.33	11.08	10.16	
15	39.20	33.30	24.70	19.39	17.78	
25	53.05	47.04	38.40	33.24	30.48	
37	69.40	63.50	54.80	49.86	45.72	

Without Insulator Support

RoHS compliant

Unit: mm

	RoHS compliant Unit: mm												
G	Scale	Free	⑦	Update the dimension & shape of cover	09.07.2014	Winnie		Date	Name	Customer-No. ASSMANN WSW-No. A-DXF xx LP III/Z			
	TOLERANCE		⑥	Update the operating temperature	05.06.2014	Winnie	Drawn	15.08.2012	Lucas				
	X.	±0.38	⑤	Correct the UL-File number	03.04.2014	Winnie	Approved	09.07.2014	Winnie				
	X.X	±0.25	④	Update 17.58&17.28 into 17.40&17.10mm	07.03.2014	Winnie							
	X.XX	±0.13	③	Update the wire specification	28.06.2013	Winnie	ASSMANN WSW components						
	DIM	TOL	②	Add the wire specification	06.03.2013	Winnie							
	X.°	±3°											
	X.X°	±1.0°											
		Angle	TOL	Id.	Modification	Date	Name				Drawing-No. ASS 4891 CO	rev07	H
								Replace					
H							Sheet 2/2						

ASSMANN
components

ASS 4891 CO

rev07

Drawing-No.

A-DXF XX LP III/Z

Replace

Sheet 2/2