

D

D

C

C

B

B

A

A

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT

By


ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J	—					
		E6	REVISED	ECR-16-000439	31AUG07	TS
						KB





- 注記:
- △ -A- 面より2mmの範囲で測定のこと。
 - △ 相手ハウジングと所定の機能を満たしてかん合できること。
 - △ フードの反りは0.2以内。
 - 4 推奨取付けねじ: JIS B 1115 又は、1122 タッピンねじ
なべ1種又は2種、呼び径3長さ6mm以下。
(締め付けトルク: 0.4N・m 以下)
 - 5 適用製品規格 No.108-5093
 - 6 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。
 - △ タブなしタイプ(表参照)回路番号下図参照のこと。

- NOTES:
- △ TO BE MEASURED WITHIN 2mm FROM -A-
 - △ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
 - △ WARPAGE 0.2 MAX.
 - 4 RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH<MAX.>
PAN HEAD, CLASS 1 AND 2 TAPPING SCREW SPRCIFIED IN JIS B1115, B1122 <TIGHTENING TORQUE 0.4N・m MAX.>
 - 5 SPEC. No. 108-5093
 - 6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX WITHOUT RECEPTACLE CONTACT
 - △ NON TAB CONTACT' S TYPE <SEE TABLE>
 - CIRCUIT NUMBER



プリント基板取付穴寸法図
(MOUNTING DIMENSIONS FOR P.C.BOARD)

- 板厚, 1.6±0.15
(P.C.B. THICKNESS, 1.6±0.15)
- 公差, ±0.1
(TORELANCE, ±0.1)



TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
0 ~ <= 10	: ±0.2
10 ~ <= 30	: ±0.25
30 ~ <= 100	: ±0.3
ANGLE 角度	: ±3°

	—//—	SELECTIVE-TIN (MATTE)		SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	2-5172039-1
	—//—	SELECTIVE-TIN (MATTE)		SELECTIVE GOLD (0.76μ m MIN.)	NATURAL	1-5172039-1
OBSOLETE	12.6	PRE-TIN			NATURAL	4-172039-1
	2.6	PRE-TIN			NATURAL	3-172039-1
OBSOLETE	↑ 					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA	31AUG07	TE Connectivity	
DIMENSIONS: 単位: 概 mm		CHK K.BETSUI	31AUG07		
		APVD K.BETSUI	31AUG07	NAME 名称 7P HORIZONTAL TYPE CAP HOUSING ASS'Y MULTI-INTERLOCK CONN. (WIRE TO P.C.B.)	
		PRODUCT SPEC 製品規格 SEE NOTE 5			
MATERIAL 材料 HSG: 66 NYLON CONTACT: BRASS		APPLICATION SPEC 取付適用規格		SIZE A2	CAGE CODE 00779
		FINISH 仕上 SEE TABLE		DRAWING NO 番号 C=172039	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 尺度 2:1	SHEET 1 OF 1
				REV E6	